

NUT HEX M5 - Nut



3003001

<https://www.phoenixcontact.com/us/products/3003001>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Nut



Commercial data

Item number	3003001
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BE64
Product key	BE64UX
GTIN	4055626122557
Weight per piece (including packing)	1.429 g
Weight per piece (excluding packing)	1.429 g
Customs tariff number	73181660
Country of origin	IN

NUT HEX M5 - Nut

3003001

<https://www.phoenixcontact.com/us/products/3003001>



Technical data

Product properties

Product type	Mounting material
--------------	-------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

NUT HEX M5 - Nut

3003001

<https://www.phoenixcontact.com/us/products/3003001>



Classifications

ECLASS

ECLASS-13.0	27141190
-------------	----------

ETIM

ETIM 9.0	EC002848
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

NUT HEX M5 - Nut

3003001

<https://www.phoenixcontact.com/us/products/3003001>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com