

NFC-USB-PROG-ADAPTER - Programming adapter



2900013

<https://www.phoenixcontact.com/us/products/2900013>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Near Field Communication (NFC) programming adapter with USB interface for the wireless configuration of NFC-capable products from Phoenix Contact with software. A separate USB driver is not required.



Product description

Near Field Communication (NFC) programming adapter with USB interface for the wireless configuration of NFC-capable products from PHOENIX CONTACT with software. No separate USB driver is required.

Commercial data

Item number	2900013
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DK112Z
GTIN	4046356913164
Weight per piece (including packing)	141.2 g
Weight per piece (excluding packing)	99.99 g
Country of origin	DE

NFC-USB-PROG-ADAPTER - Programming adapter

2900013

<https://www.phoenixcontact.com/us/products/2900013>



Technical data

Product properties

Product type	Programming adapter
--------------	---------------------

Electrical properties

Supply	
Supply voltage	5 V (via USB interface)

Connection data

PC side	
Connection method	USB type A, male connector

Adapter side	
Connection method	Micro USB type B

Interface to measuring transducer	
Connection method	NFC
Notes	in accordance with ISO 14443A and ISO 15693

Dimensions

Width	71 mm
Height	17 mm
Depth	123 mm

Material specifications

Housing material	ABS
------------------	-----

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Max. permissible relative humidity (operation)	95 % (at 25 °C)

NFC-USB-PROG-ADAPTER - Programming adapter

2900013

<https://www.phoenixcontact.com/us/products/2900013>



Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com