

# PLC-RPT- 24DC/21AU - Relay module



2900306

<https://www.phoenixcontact.com/us/products/2900306>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PLC-INTERFACE, consisting of PLC-BPT.../21 basic terminal block with Push-in connection and plug-in miniature relay with multi-layer gold contact, for mounting on DIN rail NS 35/7,5, 1 changeover contact, input voltage 24 V DC

## Your advantages

- Slim design
- Efficient connection to system cabling using V8 adapter
- RT III sealed relay
- Safe isolation between coil and contact side
- Integrated input circuit and interference suppression circuit
- Functional plug-in bridges

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2900306       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | C462          |
| Product key                          | DK62A7        |
| GTIN                                 | 4046356507028 |
| Weight per piece (including packing) | 35.15 g       |
| Weight per piece (excluding packing) | 32.717 g      |
| Customs tariff number                | 85364190      |
| Country of origin                    | DE            |

# PLC-RPT- 24DC/21AU - Relay module

2900306

<https://www.phoenixcontact.com/us/products/2900306>



## Technical data

### Product properties

|                         |                           |
|-------------------------|---------------------------|
| Product type            | Relay Module              |
| Product family          | PLC-INTERFACE             |
| Application             | Universal                 |
| Operating mode          | 100% operating factor     |
| Mechanical service life | 2x 10 <sup>7</sup> cycles |

### Data management status

|                              |            |
|------------------------------|------------|
| Date of last data management | 12.09.2025 |
|------------------------------|------------|

### Electrical properties

|   |  |
|---|--|
| Maximum power dissipation for nominal condition | 0.22 W                                   |
| Test voltage (Winding/contact)                  | 4 kV AC (50 Hz, 1 min., winding/contact) |

### Insulation characteristics: Coil/contact

|                                 |       |
|---------------------------------|-------|
| Rated insulation voltage        | 250 V |
| Rated impulse withstand voltage | 6 kV  |
| Overvoltage category            | III   |
| Degree of pollution             | 3     |

### Input data

#### Coil side

|  |  |
|--|--|
| Nominal input voltage U <sub>N</sub>                 | 24 V DC  |
| Input voltage range                                  | 18.5 V DC ... 33.6 V DC (20 °C)                        |
| Nominal voltage (plugged-in electromechanical relay) | 24 V DC  |
| Drive and function                                   | monostable   |
| Drive (polarity)                                     | polarized  |
| Typical input current at U <sub>N</sub>              | 9 mA   |
| Typical response time                                | 5 ms   |
| Typical release time                                 | 8 ms   |
| Protective circuit                                   | Reverse polarity protection; Polarity protection diode |
|  | Surge protection; Freewheeling diode                   |
| Operating voltage display                            | Yellow LED   |

### Output data

#### Switching

|                           |                         |
|---------------------------|-------------------------|
| Contact switching type    | 1 changeover contact    |
| Type of switch contact    | Single contact          |
| Contact connection type   | Signal contact          |
| Contact material          | AgSnO, hard gold-plated |
| Maximum switching voltage | 30 V AC                 |

# PLC-RPT- 24DC/21AU - Relay module

2900306

<https://www.phoenixcontact.com/us/products/2900306>



|                                       |   |
|---------------------------------------|---|
|                                       | 36 V DC                                   |
| Minimum switching voltage             | 100 mV (10 mA)                            |
| Limiting continuous current           | 50 mA                                     |
| Maximum inrush current                | 50 mA                                     |
| Min. switching current                | 1 mA (24 V)                               |
| Short-circuit current                 | 200 A (conditional short-circuit current) |
| Interrupting rating (ohmic load) max. | 1.2 W (at 24 V DC)                        |
| Output fuse                           | 4 A gL/gG NEOZED                          |

Switching: when the gold layer is destroyed

|                                       |  |
|---------------------------------------|--|
| Note                                  | the following values are applicable if a gold layer is destroyed   |
| Maximum switching voltage             | 250 V AC/DC  |
| Minimum switching voltage             | 5 V (at 100 mA)  |
| Limiting continuous current           | 6 A  |
| Min. switching current                | 10 mA (at 12 V)  |
| Interrupting rating (ohmic load) max. | 140 W (at 24 V DC)<br>20 W (at 48 V DC)<br>18 W (at 60 V DC)<br>23 W (at 110 V DC)<br>40 W (at 220 V DC)<br>1500 VA (for 250 V AC)             |
| Switching capacity                    | 2 A (at 24 V, DC13)<br>0.2 A (at 110 V, DC13)<br>0.1 A (at 220 V, DC13)<br>3 A (at 24 V, AC15)<br>3 A (at 120 V, AC15)<br>3 A (at 230 V, AC15) |

## Connection data

|                                  |   |
|----------------------------------|---|
| Connection method                | Push-in connection  |
| Stripping length                 | 10 mm   |
| Conductor cross-section rigid    | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>  |
| Conductor cross-section flexible | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup><br>0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (Single ferrule)<br>2x 0.5 mm <sup>2</sup> ... 1 mm <sup>2</sup> (TWIN ferrule) |
| Conductor cross-section AWG      | 26 ... 14   |

## Dimensions

|        |        |
|--------|--------|
| Width  | 6.2 mm |
| Height | 80 mm  |
| Depth  | 94 mm  |

## Material specifications

# PLC-RPT- 24DC/21AU - Relay module

2900306

<https://www.phoenixcontact.com/us/products/2900306>



|  |                 |
|--|-----------------|
| Color  | gray (RAL 7042) |
| Flammability rating according to UL 94 (Housing) | V0 (Housing)    |

## Environmental and real-life conditions

### Ambient conditions

|   |                                    |
|---|------------------------------------|
| Degree of protection (Relay)            | RT III (Relay)                     |
| Degree of protection (Relay base)       | IP20 (Relay base)                  |
| Ambient temperature (operation)         | -40 °C ... 70 °C (see to derating) |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C                   |

## Approvals

### CE

|             |              |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

### UKCA

|             |                |
|-------------|----------------|
| Certificate | UKCA-compliant |
|-------------|----------------|

### Shipbuilding approval

|             |            |
|-------------|------------|
| Certificate | TAE0000196 |
|-------------|------------|

### Corrosive gas test

|                |                            |
|----------------|----------------------------|
| Identification | ISA-S71.04. G3 Harsh Group |
|                | EN 60068-2-60              |

### Shipbuilding data

|             |   |
|-------------|---|
| Temperature | D   |
| Humidity    | A   |
| Vibration   | B/C   |
| EMC         | B   |
| Enclosure   | Required protection according to the Rules shall be provided upon installation on board |

## EMC data

|                               |  |
|-------------------------------|--|
| Electromagnetic compatibility | Conformance with EMC directive         |
| Low Voltage Directive         | Conformance with Low Voltage Directive |

## Standards and regulations

|                       |               |
|-----------------------|---------------|
| Standards/regulations | IEC 60947-5-1 |
|-----------------------|---------------|

## Mounting

|                   |                           |
|-------------------|---------------------------|
| Mounting type     | DIN rail mounting         |
| Assembly note     | in rows with zero spacing |
| Mounting position | any                       |

# PLC-RPT- 24DC/21AU - Relay module


2900306

<https://www.phoenixcontact.com/us/products/2900306>



## Drawings

Diagram



### Curve A

Maximum permissible continuous voltage  $U_{\max}$  with limiting continuous current on the contact side (see relevant technical data)

### Curve B

Minimum permissible operate voltage  $U_{op}$  after pre-excitation (see relevant technical data)


# PLC-RPT- 24DC/21AU - Relay module

2900306

<https://www.phoenixcontact.com/us/products/2900306>



Diagram




Limiting continuous current per contact for  $0.85 \dots 1.1 U_N$  (contact-side)

(1) Limiting continuous current for horizontal installation position without clearance

(2) Limiting continuous current for vertical installation position without clearance

Diagram



① 250 V AC, ohmic load

Electrical service life


# PLC-RPT- 24DC/21AU - Relay module

2900306

<https://www.phoenixcontact.com/us/products/2900306>



Diagram



Permissible humidity for operation and storage.


The maximum permissible ambient temperature as specified in the data sheet must be observed.

Area A: Ice buildup at ambient temperatures  $\leq 0^{\circ}\text{C}$  must be prevented

Area B: Condensation at ambient temperatures  $> 0^{\circ}\text{C}$  must be prevented

On 30 full days that are naturally distributed across an entire year, a humidity level of 95% is permissible at an ambient temperature  $\leq 25^{\circ}\text{C}$ .

Circuit diagram



# PLC-RPT- 24DC/21AU - Relay module

2900306

<https://www.phoenixcontact.com/us/products/2900306>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2900306>



**DNV GL**

Approval ID: TAE0000196



**cULus Listed**

Approval ID: E140324

# PLC-RPT- 24DC/21AU - Relay module

2900306

<https://www.phoenixcontact.com/us/products/2900306>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27371601 |
| ECLASS-15.0 | 27371601 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001437 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39122300 |
|-------------|----------|

# PLC-RPT- 24DC/21AU - Relay module

2900306

<https://www.phoenixcontact.com/us/products/2900306>



## Environmental product compliance

### EU RoHS

|   |              |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|   |         |
|---|---------|
| Environment friendly use period (EFUP)  | EFUP-50 |
| An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |         |

### EU REACH SVHC

|                                     |   |
|-------------------------------------|---|
| REACH candidate substance (CAS No.) | Hexahydromethylphthalic anhydride(CAS: n/a) |
|                                     | Lead(CAS: 7439-92-1)                        |
| SCIP                                | 6236c471-8ee4-4e32-9b77-80d935712c50        |

### EF3.0 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.486 kg CO2e |
|---------|---------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)