

VIP-2/PT/FLK50/PLC - Passive module




2903803

<https://www.phoenixcontact.com/us/products/2903803>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE interface module, with push-in connection, for 32 channels



Commercial data

Item number	2903803
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C423
Product key	DK2121
GTIN	4046356796774
Weight per piece (including packing)	218.2 g
Weight per piece (excluding packing)	218.1 g
Customs tariff number	85366990
Country of origin	US

VIP-2/PT/FLK50/PLC - Passive module



2903803

<https://www.phoenixcontact.com/us/products/2903803>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE Professional
Number of positions	50
No. of channels	32

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Max. permissible operating voltage	25 V AC
	60 V DC
Max. current carrying capacity per branch	1 A
Max. total current of voltage supply	2 A (per byte)
Rated surge voltage	0.6 kV

Supported controller SIEMENS ET 200SP HA

Suitable terminal block	6DL1193-6TP00-0BH1
	6DL1193-6TP00-0DH1
	6DL1193-6TP00-0BM1
	6DL1193-6TP00-0DM1
Suitable I/O module	6DL1131-6BL00-0PH1 (Terminal Block H1/M1)
	6DL1132-6BL00-0PH1 (Terminal Block H1/M1)

Supported controller SIEMENS S7-1500

Suitable I/O card	6ES7521-1BL00-0AB0
	6ES7521-1BL10-0AA0
	6ES7522-1BL00-0AB0
	6ES7522-1BL01-0AB0
	6ES7522-1BL10-0AA0
	6ES7523-1BL00-0AA0

Supported controller ALLEN-BRADLEY ControlLogix

Suitable I/O card	1756-IA16I
	1756-IB16D
	1756-IB16I
	1756-IB32
	1756-IH16I
	1756-OB32
	1756-IF8
	1756-IF16
	1756-HSC

VIP-2/PT/FLK50/PLC - Passive module



2903803

<https://www.phoenixcontact.com/us/products/2903803>

	1756-M02AE
	1756-IF8H
Supported controller ALLEN-BRADLEY PLC 5	
Suitable I/O card	1771 IBN
	1771 OBN
Supported controller GE-FANUC RX3i	
Suitable I/O card	IC694MDL754
	IC694MDL660
Supported controller HONEYWELL Experion PKS C200	
Suitable I/O card	TC-IDD 321
	TC-ODD 321
Supported controller MITSUBISHI MELSEC L	
Suitable I/O card	LX41C4
	LX42C4
	LY41NT1P
	LY42NT1P
	LY41PT1P
	LY42PT1P
Supported controller MITSUBISHI MELSEC Q	
Suitable I/O card	QX41
	QX41-S1
	QX42
	QX42-S1
	QX71
	QX72
	QY41P
	QY42P
	QY71
	QH42P
	QX82
	QX82-S1
	QY82P
Supported controller SCHNEIDER ELECTRIC Modicon TSX QUANTUM	
Suitable I/O card	DDI 353
	DDI 841
	DAI 453
	DDO 353

Connection data

Field level

VIP-2/PT/FLK50/PLC - Passive module



2903803

<https://www.phoenixcontact.com/us/products/2903803>

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross-section AWG	26 ... 14

Controller level

Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	50
Pitch	2.54 mm

Signaling

Status display	no
Status display present	no

Dimensions

Item dimensions

Width	107.9 mm
Height	72.1 mm
Depth	56 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Housing insulation material	Polyamide PA non-reinforced

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

VIP-2/PT/FLK50/PLC - Passive module




2903803

<https://www.phoenixcontact.com/us/products/2903803>

Drawings

Circuit diagram



VIP-2/PT/FLK50/PLC - Passive module



2903803

<https://www.phoenixcontact.com/us/products/2903803>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2903803>

 CSA Approval ID: 2122203				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	125 V	1 A	26 - 14	-

 cUL Recognized Approval ID: E238705				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	125 V	1 A	26 - 14	-

 UL Recognized Approval ID: E238705				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	125 V	1 A	26 - 14	-

 CSAus Approval ID: 2122203				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	125 V	1 A	26 - 14	-

VIP-2/PT/FLK50/PLC - Passive module



2903803

<https://www.phoenixcontact.com/us/products/2903803>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VIP-2/PT/FLK50/PLC - Passive module



2903803

<https://www.phoenixcontact.com/us/products/2903803>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com