

VIP-CAB-FLK20/0,14/ 7,0M/S - Cable



2906356

<https://www.phoenixcontact.com/us/products/2906356>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Assembled shielded round cable with additional shield connection and two molded 20-pos. socket strips (1:1 connection). The cable has two 90° punched-on connectors, cable length: 7 m



Your advantages

- 20-pos.
- 1:1 connection

Commercial data

Item number	2906356
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DK2AH2
GTIN	4055626065724
Weight per piece (including packing)	720 g
Weight per piece (excluding packing)	720 g
Country of origin	DE

VIP-CAB-FLK20/0,14/ 7,0M/S - Cable



2906356

<https://www.phoenixcontact.com/us/products/2906356>

Technical data

Product properties

Product type	System cable
Insulation characteristics: Air clearances and creepage distances	
Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation) (fixed installation)	-40 °C ... 70 °C (fixed installation)
Ambient temperature (operation) (flexible installation)	-10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

Electrical properties

Operating voltage (DC)	≤ 24 V DC
Nominal operating mode	100% operating factor
Current (Per path)	≤ 0.5 A

Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (1.2/50 µs)

Cable/line

Cable length	7 m
UL AWM Style	2464/1061
Number of positions	20
Shielded	yes
Conductor type	Assembled shielded round cable
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross section	20x 0.14 mm ²
Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	7.70 mm ±0.3 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km (at 20 °C)
Insulation resistance	≥ 20 MΩ*km (20 °C)

VIP-CAB-FLK20/0,14/ 7,0M/S - Cable



2906356

<https://www.phoenixcontact.com/us/products/2906356>

Smallest bending radius, fixed installation	80 mm
Smallest bending radius, movable installation	144 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000 (at a radius of $\geq 18x$ outside diameter)
Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable)
	VDE 0842, Part 332-1-2 (raw cable)
	IEC 60332-3-22 (raw cable)
	UL VW-1
	CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)
Cable type	Cable for one module

Connection data

Flat-ribbon cable connector

Connection in acc. with standard	IEC 60603-13
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	20
Exit angle	90 °
Insertion/withdrawal cycles	> 200
Pitch	2.54 mm

Flat-ribbon cable connector

Connection in acc. with standard	IEC 60603-13
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	20
Exit angle	90 °
Insertion/withdrawal cycles	> 200
Pitch	2.54 mm

Standards and regulations

Air clearances and creepage distances


Standards/regulations	DIN EN 50178
-----------------------	--------------

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

Drawings

Diagram



Maximum permissible current per path in uncoiled state

VIP-CAB-FLK20/0,14/ 7,0M/S - Cable



2906356

<https://www.phoenixcontact.com/us/products/2906356>

Classifications

ECLASS

ECLASS-13.0	27242220
-------------	----------

ETIM

ETIM 9.0	EC000237
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

VIP-CAB-FLK20/0,14/ 7,0M/S - Cable



2906356

<https://www.phoenixcontact.com/us/products/2906356>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com