

# A 1 - 6 - Ferrule

3200247

<https://www.phoenixcontact.com/us/products/3200247>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, Length contact range: 6 mm, sleeve length: 6 mm, color: silver-colored

## Your advantages

- The dimensions of the ferrules conform to DIN 46228-1
- The ferrules without plastic sleeve are made from soft tin-plated electrolytic copper

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3200247       |
| Packing unit                         | 1,000 pc      |
| Minimum order quantity               | 1,000 pc      |
| Sales key                            | BH34          |
| Product key                          | BH3412        |
| GTIN                                 | 4017918093891 |
| Weight per piece (including packing) | 0.044 g       |
| Weight per piece (excluding packing) | 0.044 g       |
| Customs tariff number                | 85369010      |
| Country of origin                    | DE            |

# A 1 - 6 - Ferrule

3200247

<https://www.phoenixcontact.com/us/products/3200247>



## Technical data

### Product properties


|                    |                                                                            |
|--------------------|----------------------------------------------------------------------------|
| Product type       | Cable end sleeve                                                           |
| Conductor category | stranded conductors, class 2, 5, 6 / B, C, K, M                            |
| Product property   | UL certified                                                               |
|                    | Made from soft tin-plated electrolytic copper                              |
|                    | Correspond to the requirements of DIN 46228-1 and UL 486F in terms of size |
|                    | Long/short-term temperature: +105°C/+120°C                                 |

### Connection data

#### Conductor connection

|                                       |                   |
|---------------------------------------|-------------------|
| Conductor cross-section flexible max. | 1 mm <sup>2</sup> |
| Conductor cross-section AWG max.      | 18                |
| Stripping length                      | 10 mm             |

### Dimensions

|                                           |                                                                                      |
|-------------------------------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing                       |  |
| Sleeve length                             | 6 mm                                                                                 |
| Length contact range                      | 6 mm                                                                                 |
| Maximum stripping length                  | 10 mm                                                                                |
| Ferrule diameter                          | 1.4 mm                                                                               |
| Sleeve wall thickness                     | 0.15 mm                                                                              |
| Inner dimensions of the insulating collar | 2.5 mm                                                                               |

### Material specifications

|                         |                         |
|-------------------------|-------------------------|
| Color                   | silver-colored          |
| Material                | CU-DHP                  |
| Coating                 | galvanically tin-plated |
| Surface characteristics | Tin-plated              |

### Mechanical properties

#### Technical data

|               |      |
|---------------|------|
| Sleeve length | 6 mm |
|---------------|------|

### Environmental and real-life conditions

#### Ambient conditions

# A 1 - 6 - Ferrule



3200247

<https://www.phoenixcontact.com/us/products/3200247>

|                        |        |
|------------------------|--------|
| Permanent temperature  | 105 °C |
| Short-term temperature | 120 °C |

## Standards and regulations

|                              |                        |
|------------------------------|------------------------|
| Design according to standard | DIN 46228-1, UL 486F-A |
|------------------------------|------------------------|

# A 1 - 6 - Ferrule


3200247

<https://www.phoenixcontact.com/us/products/3200247>



## Drawings

Dimensional drawing



Sleeve length (b), insulating collar inner dimension (d), sleeve diameter (k), sleeve wall thickness (j)

# A 1 - 6 - Ferrule

3200247

<https://www.phoenixcontact.com/us/products/3200247>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3200247>



**cULus Listed**

Approval ID: E488001

# A 1 - 6 - Ferrule



3200247

<https://www.phoenixcontact.com/us/products/3200247>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27400201 |
| ECLASS-15.0 | 27400201 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000005 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27121700 |
|-------------|----------|

# A 1 - 6 - Ferrule



3200247  
<https://www.phoenixcontact.com/us/products/3200247>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)