

STIO-IN 2,5/4 OG - Power terminal block



3209206

<https://www.phoenixcontact.com/us/products/3209206>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power terminal block, nom. voltage: 250 V, nominal current: 30 A, number of connections: 5, connection method: Spring-cage connection, Rated cross section: 2.5 mm², cross section: 0.08 mm² - 4 mm², mounting type: NS 35/7,5, NS 35/15, color: orange

Your advantages

- Upper level for signal wiring

Commercial data

Item number	3209206
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BE02
Product key	BE2118
GTIN	4046356182836
Weight per piece (including packing)	17.724 g
Weight per piece (excluding packing)	15.069 g
Customs tariff number	85369010
Country of origin	TR

STIO-IN 2,5/4 OG - Power terminal block



3209206

<https://www.phoenixcontact.com/us/products/3209206>

Technical data

Product properties

Product type	Sensor/actuator terminal block
Number of connections	5
Number of rows	3

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	4 kV
Maximum power dissipation for nominal condition	0.77 W

Connection data

Number of connections per level	2
Nominal cross section	2.5 mm ²
Connection method	Spring-cage connection
Stripping length	8 mm ... 10 mm
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	0.08 mm ² ... 4 mm ²
Cross section AWG	28 ... 12 (converted acc. to IEC)
Conductor cross-section flexible	0.08 mm ² ... 2.5 mm ²
Conductor cross-section, flexible [AWG]	28 ... 14 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.14 mm ² ... 2.5 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.14 mm ² ... 2.5 mm ²
Conductor cross-section flexible (2 conductors with the same cross-section, with TWIN ferrule and plastic sleeve)	0.5 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ²
Nominal current	30 A (For central infeed and 4 mm ² conductor cross-section)
	18 A (For single-sided infeed and 2.5 mm ² conductor cross-section)
Maximum load current	30 A (with 4 mm ² conductor cross-section)
Nominal voltage	250 V
Nominal cross section	2.5 mm ²

Dimensions

Width	10.4 mm
End cover width	2.2 mm
Height	92.3 mm
Depth on NS 35/7,5	44.5 mm
Depth on NS 35/15	52 mm

STIO-IN 2,5/4 OG - Power terminal block



3209206

<https://www.phoenixcontact.com/us/products/3209206>

Material specifications

Color	orange (RAL 2003)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Electrical tests

Surge voltage test

Test voltage setpoint	4.8 kV
Result	Test passed

Temperature-rise test

Requirement temperature-rise test	Increase in temperature ≤ 45 K
Result	Test passed
Short-time withstand current 4 mm ²	0.48 kA
Result	Test passed

Power-frequency withstand voltage

Test voltage setpoint	1.5 kV
Result	Test passed

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Mechanical tests

Mechanical strength

Result	Test passed
--------	-------------

Attachment on the carrier

Result	Test passed
--------	-------------

Test for conductor damage and slackening

Rotation speed	10 rpm
Revolutions	135

STIO-IN 2,5/4 OG - Power terminal block



3209206

<https://www.phoenixcontact.com/us/products/3209206>

Conductor cross-section/weight	0.08 mm ² / 0.1 kg
	0.2 mm ² / 0.2 kg
	2.5 mm ² / 0.7 kg
	4 mm ² / 0.9 kg
Result	Test passed

Environmental and real-life conditions

Aging

Temperature cycles	192
Result	Test passed

Needle-flame test

Time of exposure	30 s
Result	Test passed

Oscillation/broadband noise

Specification	EN 50155:2021-07
Spectrum	Long life test category 2, bogie-mounted
Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$
ASD level	6.12 (m/s ²) ² /Hz
Acceleration	3.12g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Result	Test passed

Shocks

Pulse shape	Half-sine
Acceleration	30g
Shock duration	18 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

STIO-IN 2,5/4 OG - Power terminal block

3209206

<https://www.phoenixcontact.com/us/products/3209206>



Mounting

Mounting type	NS 35/7,5
	NS 35/15

STIO-IN 2,5/4 OG - Power terminal block

3209206

<https://www.phoenixcontact.com/us/products/3209206>



Drawings

Circuit diagram



STIO-IN 2,5/4 OG - Power terminal block

3209206

<https://www.phoenixcontact.com/us/products/3209206>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3209206>

**EAC**
Approval ID: RU C-DE.BL08.B.00644

 cULus Recognized Approval ID: E60425				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	300 V	10 A	28 - 12	-
C				
	150 V	20 A	28 - 12	-
D				
	300 V	10 A	28 - 12	-

**EAC**
Approval ID: KZ7500651131219505

STIO-IN 2,5/4 OG - Power terminal block



3209206

<https://www.phoenixcontact.com/us/products/3209206>

Classifications

ECLASS

ECLASS-13.0	27250112
ECLASS-15.0	27250112

ETIM

ETIM 9.0	EC000900
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

STIO-IN 2,5/4 OG - Power terminal block



3209206

<https://www.phoenixcontact.com/us/products/3209206>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com