

# PACT RCP-D190-10M - Coil

2910324

<https://www.phoenixcontact.com/us/products/2910324>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

600 mm long Rogowski coil. The measuring coil diameter when installed is 190 mm. The Rogowski coil is used for AC current measurement for busbars and power lines.



## Commercial data

Item number	2910324
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C444
Product key	CMMA12
GTIN	4055626437569
Weight per piece (including packing)	380.5 g
Weight per piece (excluding packing)	380.5 g
Customs tariff number	90309000
Country of origin	DE

# PACT RCP-D190-10M - Coil

2910324

<https://www.phoenixcontact.com/us/products/2910324>



## Technical data

### Product properties

Product type	Rogowski coil
Set comprises	2910327 PACT RCP-4000A-1A-D190-10M
Insulation characteristics	
Pollution degree	2

### Electrical properties

Measuring coil	
Conductor structure signal line	2x 0.22 mm (Signal (tinned))
	1x 0.22 mm (Shielding (tinned))
Insulation	double insulation
Rated insulation voltage	1000 V AC (rms CAT III)
	600 V AC (rms CAT IV)
Test voltage	10.45 kV DC (60 s)
Accuracy class	0.2 (IEC 61869-10: A1)

General	
Converter type	Rogowski coil

### Input data

Frequency	
Designation	Measuring coil
Frequency measuring range	40 Hz ... 20000 Hz

Current transformer	
Converter type	Rogowski coil

### Output data

Signal	
Designation	Measuring coil
Output signal (at 50 Hz)	100 mV (no load, at 1,000 A)
Output voltage (in no-load operation)	$V_{OUT} = M * dI/dt$
Output voltage (sinusoidal, in no-load operation)	100 mV ( $V_{OUT} = 2 * \pi * M * f * I$ ( $M = 0.318 \mu\text{H}$ ; example: At 50 Hz; $I = 1,000 \text{ A}$ ))

### Dimensions

Measuring coil	
Length	600 mm
Diameter	8.3 mm $\pm 0.2$ mm

### Measuring coil when installed

# PACT RCP-D190-10M - Coil

2910324

<https://www.phoenixcontact.com/us/products/2910324>



Diameter	190 mm
Signal line	
Length	10 m

## Material specifications

Housing material	PC
Coil material	Elastollan

## Environmental and real-life conditions

### Ambient conditions

Measuring coil degree of protection	IP54 (not assessed by UL)
Ambient temperature (operation) (Measuring coil)	-30 °C ... 80 °C (Measuring coil)
Ambient temperature (storage/transport)	-40 °C ... 80 °C (Measuring coil)
Altitude	< 2000 m
Permissible humidity (operation)	5 % ... 95 % (non-condensing)

## Approvals

UKCA	
Certificate	UKCA-compliant
CMIM	
Certificate	CMIM-compliant
UL, USA/Canada	
Identification	UL 61010 Recognized
Note	Measuring coil

## Standards and regulations

Standards/regulations	IEC 61010-2-030
	IEC 61869-10

# PACT RCP-D190-10M - Coil

2910324

<https://www.phoenixcontact.com/us/products/2910324>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2910324>



**cUL Recognized**

Approval ID: FILE E 357804



**UL Recognized**

Approval ID: FILE E 357804

# PACT RCP-D190-10M - Coil

2910324

<https://www.phoenixcontact.com/us/products/2910324>



## Classifications

### ECLASS

ECLASS-13.0	27210992
ECLASS-15.0	27210992

### ETIM

ETIM 9.0	EC002498
----------	----------

### UNSPSC

UNSPSC 21.0	39121000
-------------	----------

# PACT RCP-D190-10M - Coil

2910324

<https://www.phoenixcontact.com/us/products/2910324>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)