

# WT-UV HF 7,8X365 BK - Cable tie

3240837

<https://www.phoenixcontact.com/us/products/3240837>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binders for quick and permanent fastening, UV-resistant and weatherproof (ISO 4892\_ QUV-B 600 h)

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3240837       |
| Packing unit                         | 100 pc        |
| Minimum order quantity               | 100 pc        |
| Sales key                            | BE07          |
| Product key                          | BE7133        |
| GTIN                                 | 4046356705851 |
| Weight per piece (including packing) | 5.23 g        |
| Weight per piece (excluding packing) | 4.28 g        |
| Customs tariff number                | 39269097      |
| Country of origin                    | IT            |

# WT-UV HF 7,8X365 BK - Cable tie

3240837

<https://www.phoenixcontact.com/us/products/3240837>



## Technical data

### Product properties

|                      |           |
|----------------------|-----------|
| Product type         | Cable tie |
| Tensile strength GRP | 540 N     |

### Dimensions

|        |        |
|--------|--------|
| Width  | 7.8 mm |
| Length | 365 mm |

### Material specifications

|  |                                |
|--|--------------------------------|
| RoHS compliant                         | yes                            |
| Color                                  | black (RAL 9005)               |
| Material                               | PA 6.6                         |
| Flammability rating according to UL 94 | V2                             |
| Components                             | free from silicone and halogen |

### Cable/line

|                         |                 |
|-------------------------|-----------------|
| External cable diameter | 8 mm ... 100 mm |
| Tensile strength        | 540 N           |

### Environmental and real-life conditions

#### Ambient conditions

|   |   |
|---|---|
| Optimum ambient temperature (storage/transport) | 23.00 °C 50.00 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat. |
| Ambient temperature (operation)                 | -40 °C ... 105 °C   |
| Ambient temperature (assembly)                  | -10 °C ... 60 °C  |
| Resistance to UV radiation                      | yes   |

### Mounting

|               |                   |
|---------------|-------------------|
| Mounting type | Cannot be removed |
|---------------|-------------------|

# WT-UV HF 7,8X365 BK - Cable tie

3240837

<https://www.phoenixcontact.com/us/products/3240837>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240837>

**DNV**

Approval ID: TAE00004VK

# WT-UV HF 7,8X365 BK - Cable tie

3240837

<https://www.phoenixcontact.com/us/products/3240837>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-15.0 | 27140702 |
| ECLASS-13.0 | 27140702 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000046 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

# WT-UV HF 7,8X365 BK - Cable tie

3240837

<https://www.phoenixcontact.com/us/products/3240837>



## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)