

# UM 45-FLKS26/ZFKDS - Termination board

2968412

<https://www.phoenixcontact.com/us/products/2968412>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with three-level spring-cage connection and flat-ribbon cable connector, for mounting on NS 35/7.5, 26-pos.

## Commercial data

Item number	2968412
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C422
Product key	DK21A1
GTIN	4017918932763
Weight per piece (including packing)	108.1 g
Weight per piece (excluding packing)	74.56 g
Customs tariff number	85369010
Country of origin	DE

# UM 45-FLKS26/ZFKDS - Termination board

2968412

<https://www.phoenixcontact.com/us/products/2968412>



## Technical data

### Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	26

### Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

### Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Current (per branch)	≤ 1 A

### Air clearances and creepage distances

Rated insulation voltage	63 V
Rated surge voltage	0.6 kV (1.2/50 µs)

### Connection data

#### Connection 1 (control level)

Connection in acc. with standard	IEC 60603-13
Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	26
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

#### Connection 2 (field level)

Connection method	Spring-cage connection
Stripping length	7.5 mm
Number of positions	27
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
	0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (Ferrule without plastic sleeve)
Conductor cross-section flexible (2 conductors with same cross section)	0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (Ferrule with plastic sleeve)
Conductor cross-section AWG	24 ... 14
Pitch	5.08 mm

### Signaling

Status display present	no
------------------------	----

# UM 45-FLKS26/ZFKDS - Termination board

2968412

<https://www.phoenixcontact.com/us/products/2968412>



## Dimensions

### Item dimensions

Width	74 mm
Height	45 mm
Depth	61 mm

## Material specifications

Color	green (RAL 6021)
Housing insulation material	PVC

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (Module)	IP00
Degree of protection (Installation location)	≥ IP54
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

## Standards and regulations

### Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

# UM 45-FLKS26/ZFKDS - Termination board


2968412

<https://www.phoenixcontact.com/us/products/2968412>



## Drawings

Circuit diagram



# UM 45-FLKS26/ZFKDS - Termination board

2968412

<https://www.phoenixcontact.com/us/products/2968412>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2968412>

		cUL Recognized		
		Approval ID: E118976		
		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG
keine				
Field wiring		125 V	1 A	-

		UL Recognized		
		Approval ID: E118976		
		Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG
keine				
Field wiring		125 V	1 A	-

# UM 45-FLKS26/ZFKDS - Termination board

2968412

<https://www.phoenixcontact.com/us/products/2968412>



## Classifications

### ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

### ETIM

ETIM 9.0	EC002780
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# UM 45-FLKS26/ZFKDS - Termination board

2968412

<https://www.phoenixcontact.com/us/products/2968412>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)