

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with plug-in bases for 16 miniature switching relays with 1 changeover contact, with LED display

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 2975476                        |
| Packing unit                         | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | C429                           |
| Product key                          | DK2A9A                         |
| GTIN                                 | 4017918336493                  |
| Weight per piece (including packing) | 890 g                          |
| Weight per piece (excluding packing) | 734.8 g                        |
| Customs tariff number                | 85364190                       |
| Country of origin                    | DE                             |

## Technical data

### Notes

|                    |  |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

### Utilization restriction

|          |   |
|----------|---|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---|

### Product properties

|                         |   |
|-------------------------|---|
| Product type            | Relay Module                                |
| No. of channels         | 16  |
| Mechanical service life | > 10 <sup>7</sup> cycles                    |
| Compatible components   | Miniature switching relay, REL-MR-24DC/21HC |
| With components         | yes   |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree     | 2   |

### Input data

|  |  |
|--|--|
| Nominal input voltage U <sub>N</sub>               | 24 V DC  |
| Input voltage range in reference to U <sub>N</sub> | 0.8 ... 1.1  |
| Typical input current at U <sub>N</sub>            | 25 mA  |
| Typical response time                              | 10 ms  |
| Typical release time                               | 5 ms   |
| Protective circuit                                 | Freewheeling diode; Freewheeling diode<br>Reverse polarity protection; Polarity protection diode |
| Status display/channel                             | Yellow LED   |

### Output data

|                                       |  |
|---------------------------------------|--|
| Compatible components                 | Miniature switching relay, REL-MR-24DC/21HC              |
| <b>Switching</b>                      |  |
| Contact switching type                | Single contact, 1 changeover contact                     |
| Contact material                      | AgCdO  |
| Maximum switching voltage             | 250 V AC (Module-specific)<br>300 V DC (Module-specific) |
| Limiting continuous current           | 5 A (Module-specific)                                    |
| Maximum inrush current                | 8 A  |
| Interrupting rating (ohmic load) max. | 120 W (at 24 V DC)<br>50 W (at 48 V DC)                  |

# UM-16 RM/KSR-G24/21/SO216 - Multiple relay module

2975476

<https://www.phoenixcontact.com/us/products/2975476>



|  |                        |
|--|------------------------|
|  | 60 W (at 220 V DC)     |
|  | 1250 VA (for 250 V AC) |
| Error detection (line break / short-circuit) | no                     |

## Connection data

### Input

|                       |   |
|-----------------------|---|
| Connection method     | Flat-ribbon cable connector in acc. with IEC 60603-13 / D-SUB plug connection |
| Number of connections | 2   |
| Number of positions   | 50  |

### Output

|                                  |   |
|----------------------------------|---|
| Connection method                | Screw connection                            |
| Stripping length                 | 8 mm  |
| Screw thread                     | M3  |
| Number of connections            | 52  |
| Number of positions              | 3   |
| Conductor cross-section rigid    | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross-section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section AWG      | 24 ... 12                                   |

## Signaling

|                        |     |
|------------------------|-----|
| Status display present | yes |
|------------------------|-----|

## Dimensions

|        |          |
|--------|----------|
| Width  | 265.5 mm |
| Height | 111 mm   |
| Depth  | 68 mm    |

## Material specifications

|                             |                                    |
|-----------------------------|------------------------------------|
| Color                       | green (RAL 6021)                   |
| Housing insulation material | PVC, side panel PA non-reinforced, |

## Environmental and real-life conditions

|   |                  |
|---|------------------|
| Ambient conditions                      |                  |
| Ambient temperature (operation)         | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

## Standards and regulations

|                       |                 |
|-----------------------|-----------------|
| Standards/regulations | DIN VDE 0110    |
|                       | DIN VDE 0109-11 |

## Mounting

|                   |     |
|-------------------|-----|
| Mounting position | any |
|-------------------|-----|

## Environmental product compliance

### China RoHS

|   |         |
|---|---------|
| Environment friendly use period (EFUP)  | EFUP-50 |
| An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |         |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)