

UK 3-MVSTB-5,08-F - Accessories



3002335

<https://www.phoenixcontact.com/us/products/3002335>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Accessories, pitch: 5.08 mm, mounting type: NS 35/7,5, NS 35/15, NS 32, color: gray



Commercial data

Item number	3002335
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE12
Product key	BE1241
GTIN	4017918090241
Weight per piece (including packing)	5.149 g
Weight per piece (excluding packing)	5.079 g
Customs tariff number	85369010
Country of origin	PL

Technical data

Product properties

Product type	Flange
Product family	UK 3-MVSTB
Number of positions	1
Pitch	5.08 mm
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Maximum load current	12 A (with 4 mm ² conductor cross-section)
Rated surge voltage	4 kV

Connection data

Maximum load current	12 A (with 4 mm ² conductor cross-section)
Internal cylindrical gage	A3

Dimensions

Width	5.08 mm
End cover width	2.5 mm
Height	48 mm
Depth on NS 35/7,5	47 mm
Length	48 mm
Pitch	5.08 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V2
Insulating material group	I
Insulating material	PA
Contact surface	Tin Sn

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C (max. operating temperature see derating curve)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C

UK 3-MVSTB-5,08-F - Accessories



3002335

<https://www.phoenixcontact.com/us/products/3002335>

Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	NS 35/7,5
	NS 35/15
	NS 32

UK 3-MVSTB-5,08-F - Accessories

3002335

<https://www.phoenixcontact.com/us/products/3002335>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3002335>

 cULus Recognized Approval ID: E60425				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
F				
	250 V	10 A	30 - 12	-
D				
	300 V	10 A	30 - 12	-

UK 3-MVSTB-5,08-F - Accessories



3002335

<https://www.phoenixcontact.com/us/products/3002335>

Classifications

ECLASS

ECLASS-13.0	27250302
ECLASS-15.0	27250302

ETIM

ETIM 9.0	EC001041
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UK 3-MVSTB-5,08-F - Accessories



3002335

<https://www.phoenixcontact.com/us/products/3002335>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com