

PTMC 1,5/32-2H VDE0815 19Z - Marshalling patchboard



3270395

<https://www.phoenixcontact.com/us/products/3270395>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marshalling patchboard, Labeled from 1 - 32, nom. voltage: 500 V, nominal current: 17.5 A, connection method: Push-in connection, cross section: 0.14 mm² - 2.5 mm², mounting: Panel mounting, 19" rack, color: gray

Your advantages

- Tool-free wiring in a confined space thanks to compact size
- Clear representation of actuation and terminal points through vertical conductor routing
- High contact quality thanks to push-in technology as a replacement for Wire-Wrap®, TERMI-POINT®, etc.
- Color configuration according to VDE 0815
- For mounting in 19" racks

Commercial data

Item number	3270395
Packing unit	24 pc
Minimum order quantity	24 pc
Product key	BE6212
GTIN	4055626282558
Weight per piece (including packing)	111 g
Weight per piece (excluding packing)	111 g
Country of origin	PL

PTMC 1,5/32-2H VDE0815 19Z - Marshalling patchboard



3270395

<https://www.phoenixcontact.com/us/products/3270395>

Technical data

Notes

General	Labeled from 1 - 32
---------	---------------------

Product properties

Product type	Marshalling terminal
Number of positions	32
Number of connections	128
Number of rows	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	0.56 W

Connection data

Number of connections per level	128
Nominal cross section	1.5 mm ²
Rated cross section AWG	14
Connection method	Push-in connection
Stripping length	8 mm ... 10 mm
Internal cylindrical gage	A1
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	0.14 mm ² ... 2.5 mm ²
Cross section AWG	26 ... 14 (converted acc. to IEC)
Conductor cross-section flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross-section, flexible [AWG]	26 ... 16 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.14 mm ² ... 1.5 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.14 mm ² ... 1.5 mm ²
Nominal current	17.5 A
Maximum load current	24 A (in case of a 2.5 mm ² conductor cross-section, the maximum load current must not be exceeded by the total current of all connected conductors.)
	12 A (in case of a 2.5 mm ² conductor cross-section, the maximum load current must not be exceeded by the total current of all connected conductors.)
Nominal voltage	500 V

Connection cross sections directly pluggable

Conductor cross-section rigid	0.34 mm ² ... 2.5 mm ²
Conductor cross-section, rigid [AWG]	20 ... 14 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.34 mm ² ... 1.5 mm ²

PTMC 1,5/32-2H VDE0815 19Z - Marshalling patchboard



3270395


<https://www.phoenixcontact.com/us/products/3270395>

Flexible conductor cross-section (ferrule with plastic sleeve)

0.34 mm² ... 1.5 mm²

Dimensions

Dimensional drawing



Width

34.4 mm

Height

111 mm

Depth

30 mm

Material specifications

Color

gray (RAL 7042)

Flammability rating according to UL 94

V0

Insulating material group

I

Insulating material

PA

Static insulating material application in cold

-60 °C

Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))

125 °C

Relative insulation material temperature index (Elec., UL 746 B)

130 °C

Fire protection for rail vehicles (DIN EN 45545-2) R22

HL 1 - HL 3

Fire protection for rail vehicles (DIN EN 45545-2) R23

HL 1 - HL 3

Fire protection for rail vehicles (DIN EN 45545-2) R24

HL 1 - HL 3

Fire protection for rail vehicles (DIN EN 45545-2) R26

HL 1 - HL 3

Calorimetric heat release NFPA 130 (ASTM E 1354)

27,5 MJ/kg

Surface flammability NFPA 130 (ASTM E 162)

passed

Specific optical density of smoke NFPA 130 (ASTM E 662)

passed

Smoke gas toxicity NFPA 130 (SMP 800C)

passed

Electrical tests

Surge voltage test

Test voltage setpoint

7.3 kV

Result

Test passed

Temperature-rise test

Requirement temperature-rise test

Increase in temperature ≤ 45 K

Result

Test passed

Short-time withstand current 1.5 mm²

0.18 kA

Short-time withstand current 2.5 mm²

0.3 kA

Result

Test passed

PTMC 1,5/32-2H VDE0815 19Z - Marshalling patchboard



3270395

<https://www.phoenixcontact.com/us/products/3270395>

Power-frequency withstand voltage

Test voltage setpoint	1.89 kV
Result	Test passed

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Mechanical tests

Mechanical strength

Result	Test passed
--------	-------------

Attachment on the carrier

DIN rail/fixing support	NS 35
Test force setpoint	1 N
Result	Test passed

Test for conductor damage and slackening

Rotation speed	10 rpm
Revolutions	135
Conductor cross-section/weight	0.14 mm ² / 0.2 kg
	1.5 mm ² / 0.4 kg
	2.5 mm ² / 0.7 kg
Result	Test passed

Environmental and real-life conditions

Aging

Temperature cycles	192
Result	Test passed

Needle-flame test

Time of exposure	30 s
Result	Test passed

Oscillation/broadband noise

Specification	DIN EN 50155 (VDE 0115-200):2008-03
Spectrum	Long life test category 1, class B, body mounted
Frequency	f ₁ = 5 Hz to f ₂ = 150 Hz
ASD level	0.964 (m/s ²) ² /Hz
Acceleration	0.58g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Result	Test passed

Shocks

PTMC 1,5/32-2H VDE0815 19Z - Marshalling patchboard



3270395

<https://www.phoenixcontact.com/us/products/3270395>

Specification	DIN EN 50155 (VDE 0115-200):2008-03
Pulse shape	Half-sine
Acceleration	5g
Shock duration	30 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C ()
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

Mounting

Mounting type	Panel mounting
	19" rack

PTMC 1,5/32-2H VDE0815 19Z - Marshalling patchboard




3270395

<https://www.phoenixcontact.com/us/products/3270395>

Drawings

Dimensional drawing




Panel cutout

PTMC 1,5/32-2H VDE0815 19Z - Marshalling patchboard

3270395

<https://www.phoenixcontact.com/us/products/3270395>

Dimensional drawing




PTMC 1,5/32-2H VDE0815 19Z - Marshalling patchboard



3270395

<https://www.phoenixcontact.com/us/products/3270395>

Circuit diagram



PTMC 1,5/32-2H VDE0815 19Z - Marshalling patchboard



3270395

<https://www.phoenixcontact.com/us/products/3270395>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3270395>



EAC

Approval ID: RU C-DE.BL08.B.00682



EAC

Approval ID: KZ7500651131219505

PTMC 1,5/32-2H VDE0815 19Z - Marshalling patchboard



3270395

<https://www.phoenixcontact.com/us/products/3270395>

Classifications

ECLASS

ECLASS-13.0	27250106
ECLASS-15.0	27250106

ETIM

ETIM 9.0	EC000897
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

3270395
<https://www.phoenixcontact.com/us/products/3270395>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com