

# UMK 22-REL 240/21-21 - Relay module



5543232

<https://www.phoenixcontact.com/us/products/5543232>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE relay module, fixed, 1PDT



## Your advantages

- Safe isolation between coil and contact side

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 5543232                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | C460                           |
| Product key                          | DK61Y2                         |
| GTIN                                 | 4046356687102                  |
| Weight per piece (including packing) | 33.33 g                        |
| Weight per piece (excluding packing) | 33.33 g                        |
| Customs tariff number                | 85364190                       |
| Country of origin                    | ID                             |

# UMK 22-REL 240/21-21 - Relay module

5543232

<https://www.phoenixcontact.com/us/products/5543232>



## Technical data

### Notes

#### Trade restriction

|         |  |
|---------|--|
| CE note | The products are offered exclusively for export outside the EU and the European Economic Area. |
|---------|--|

### Product properties

|                         |                        |
|-------------------------|------------------------|
| Product type            | Relay Module           |
| Application             | Universal              |
| Operating mode          | 100% operating factor  |
| Mechanical service life | $1 \times 10^7$ cycles |

#### Data management status

|                              |            |
|------------------------------|------------|
| Date of last data management | 12.09.2025 |
|------------------------------|------------|

### Electrical properties

|                                |  |
|--------------------------------|--|
| Test voltage (Winding/contact) | 5 kV (50/60 Hz, 1 min., winding/contact) |
|--------------------------------|--|

### Input data

#### Coil side

|                                |           |
|--------------------------------|-----------|
| Nominal input voltage $U_N$    | 220 V AC  |
| Typical input current at $U_N$ | 6 mA      |
| Typical response time          | 15 ms     |
| Typical release time           | 10 ms     |
| Operating voltage display      | Glow lamp |

### Output data

#### Switching

|                             |                       |
|-----------------------------|-----------------------|
| Contact switching type      | 2 changeover contacts |
| Contact material            | AgCdO                 |
| Maximum switching voltage   | 250 V AC (30 V DC)    |
| Minimum switching voltage   | 5 V (at 10 mA)        |
| Limiting continuous current | 5 A                   |
| Min. switching current      | 10 mA (At 5 V)        |

### Connection data

#### Coil side

|                                  |  |
|----------------------------------|--|
| Connection method                | Screw connection                             |
| Stripping length                 | 7 mm   |
| Conductor cross-section rigid    | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section flexible | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross-section AWG      | 30 ... 14                                    |

# UMK 22-REL 240/21-21 - Relay module



5543232

<https://www.phoenixcontact.com/us/products/5543232>

## Contact side

|                                  |  |
|----------------------------------|--|
| Connection method                | Screw connection                             |
| Stripping length                 | 7 mm   |
| Conductor cross-section rigid    | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section flexible | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross-section AWG      | 30 ... 14                                    |

## Dimensions

|        |         |
|--------|---------|
| Width  | 22.5 mm |
| Height | 77 mm   |
| Depth  | 50 mm   |

## Material specifications

|       |                  |
|-------|------------------|
| Color | green (RAL 6021) |
|-------|------------------|

## Environmental and real-life conditions

### Ambient conditions

|   |                  |
|---|------------------|
| Ambient temperature (operation)         | -20 °C ... 65 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

## Mounting

|                   |                           |
|-------------------|---------------------------|
| Assembly note     | in rows with zero spacing |
| Mounting position | any                       |

# UMK 22-REL 240/21-21 - Relay module

5543232

<https://www.phoenixcontact.com/us/products/5543232>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27371601 |
| ECLASS-15.0 | 27371601 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001437 |
|----------|----------|

# UMK 22-REL 240/21-21 - Relay module

5543232

<https://www.phoenixcontact.com/us/products/5543232>



## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)