




PAGE 1/2

ISSUE 05-02-19A

SERIES OCTIS

PART NUMBER OCTI957560


Packing configuration


All dimensions are in mm. Tolerances according ISO 2768 m-H.

DESCRIPTION

REP	COMPONENT	MATERIALS	PLATING
1	Protective cap	PBT GF	-
2	Interface sealing gasket	SILICONE	-
3	Lever	IXEF	-

PAGE 2/2 ISSUE 05-02-19A SERIES OCTIS PART NUMBER OCTI957560

GENERAL CHARACTERISTICS

Mechanical		
Mating endurance (cycles)	IEC 61300-2-2	100
Vibration	IEC 61300-2-1	
Weight (g)	-	6.0100
Environmental		
Protection class	IEC 60529	IP67 *
Operating temperature (°C)	IEC 61300-2-22	-40 / +85
Storage temperature (°C)	IEC 61300-2-22	-65 / +85
Humidity (damp heat) (%RH)	IEC 61300-2-19	5 / 95
Salt Mist	IEC 61300-2-26 (ISO21207 method B)	720h *
RoHS	-	Compliant
Flammability	UL 94	V0
Others:		
Equipment interface	-	For use with OCTIS™ panel interface or receptacle **
Packaging	-	Unitary in plastic bag

* Mated condition

** If the interface is to be die casted into the equipment panel, please contact Radiall for license conditions and interface definition

Installation

