


KMR Series

- Downsized 5mm in height from current snap-ins KMQ series
- Max. 50% up ripple current than same case size of KMQ series
- Endurance with ripple current : 2,000 hours at 105°C
- Rated voltage range : 160 to 450V_{dc}, Capacitance range : 100 to 3,300μF
- For inverter control, switching power supplies
- Non solvent resistant type
- RoHS2 Compliant




◆SPECIFICATIONS

Items	Characteristics			
Category Temperature Range	-25 to +105°C			
Rated Voltage Range	160 to 450V _{dc}			
Capacitance Tolerance	±20% (M)			
Leakage Current	$I \leq 3\sqrt{CV}$ Where, I : Max. leakage current (μA), C : Nominal capacitance (μF), V : Rated voltage (V)			
Dissipation Factor (tan δ)	Rated voltage (V _{dc})	160 to 250V	315 to 400V	420 & 450V
	tan δ (Max.)	0.15	0.15	0.20
Low Temperature Characteristics (Max. Impedance Ratio)	Rated voltage (V _{dc})	160 to 250V	315 to 400V	420 & 450V
	Z(-25°C)/Z(+20°C)	4	8	8
				(at 120Hz)
Endurance	The following specifications shall be satisfied when the capacitors are restored to 20°C after subjected to DC voltage with the rated ripple current is applied (the peak voltage shall not exceed the rated voltage) for 2,000 hours at 105°C.			
	Capacitance change	$\leq \pm 20\%$ of the initial value		
	D.F. (tan δ)	$\leq 200\%$ of the initial specified value		
	Leakage current	\leq The initial specified value		
Shelf Life	The following specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1,000 hours at 105°C without voltage applied. Before the measurement, the capacitor shall be preconditioned by applying voltage according to Item 4.1 of JIS C 5101-4.			
	Capacitance change	$\leq \pm 15\%$ of the initial value		
	D.F. (tan δ)	$\leq 150\%$ of the initial specified value		
	Leakage current	\leq The initial specified value		


◆DIMENSIONS [mm]

- Terminal Code : VS (φ22 to φ35) : Standard




The standard design has no plastic disc.

- Terminal Code : LI (φ35)



◆PART NUMBERING SYSTEM



Please refer to "Product code guide (snap-in type)"

KMR Series

◆ STANDARD RATINGS

WV (V _{dc})	Cap (μF)	Case size ϕD×L(mm)	Rated ripple current (Arms/105°C, 120Hz)	Part No.
160	560	22 × 25	1.58	EKMR161VSN561MP25S
	680	22 × 30	1.83	EKMR161VSN681MP30S
	820	22 × 35	2.06	EKMR161VSN821MP35S
	820	25.4 × 25	1.89	EKMR161VSN821MQ25S
	1,000	22 × 40	2.33	EKMR161VSN102MP40S
	1,000	25.4 × 30	2.15	EKMR161VSN102MQ30S
	1,000	30 × 25	1.90	EKMR161VSN102MR25S
	1,200	22 × 45	2.61	EKMR161VSN122MP45S
	1,200	22 × 50	2.69	EKMR161VSN122MP50S
	1,200	25.4 × 35	2.45	EKMR161VSN122MQ35S
	1,500	25.4 × 40	2.82	EKMR161VSN152MQ40S
	1,500	25.4 × 45	2.88	EKMR161VSN152MQ45S
	1,500	30 × 30	2.39	EKMR161VSN152MR30S
	1,500	35 × 25	2.17	EKMR161VSN152MA25S
	1,800	25.4 × 50	3.22	EKMR161VSN182MQ50S
	1,800	30 × 35	2.73	EKMR161VSN182MR35S
	1,800	30 × 40	2.82	EKMR161VSN182MR40S
	1,800	35 × 30	2.47	EKMR161VSN182MA30S
	2,200	30 × 45	3.23	EKMR161VSN222MR45S
	2,200	35 × 35	2.79	EKMR161VSN222MA35S
	2,700	30 × 50	3.66	EKMR161VSN272MR50S
	2,700	35 × 40	3.23	EKMR161VSN272MA40S
	3,300	35 × 45	3.68	EKMR161VSN332MA45S
180	470	22 × 25	1.45	EKMR181VSN471MP25S
	560	22 × 30	1.66	EKMR181VSN561MP30S
	680	22 × 35	1.87	EKMR181VSN681MP35S
	680	25.4 × 25	1.72	EKMR181VSN681MQ25S
	820	22 × 40	2.11	EKMR181VSN821MP40S
	820	25.4 × 30	1.94	EKMR181VSN821MQ30S
	1,000	22 × 45	2.38	EKMR181VSN102MP45S
	1,000	25.4 × 35	2.24	EKMR181VSN102MQ35S
	1,000	30 × 25	1.90	EKMR181VSN102MR25S
	1,200	22 × 50	2.69	EKMR181VSN122MP50S
	1,200	25.4 × 40	2.52	EKMR181VSN122MQ40S
	1,200	30 × 30	2.14	EKMR181VSN122MR30S
	1,200	35 × 25	1.94	EKMR181VSN122MA25S
	1,500	25.4 × 45	2.88	EKMR181VSN152MQ45S
	1,500	25.4 × 50	2.94	EKMR181VSN152MQ50S
	1,500	30 × 35	2.49	EKMR181VSN152MR35S
	1,800	30 × 40	2.82	EKMR181VSN182MR40S
	1,800	35 × 30	2.47	EKMR181VSN182MA30S
	2,200	30 × 45	3.23	EKMR181VSN222MR45S
	2,200	30 × 50	3.31	EKMR181VSN222MR50S
	2,200	35 × 35	2.79	EKMR181VSN222MA35S
	2,200	35 × 40	2.92	EKMR181VSN222MA40S
	2,700	35 × 45	3.33	EKMR181VSN272MA45S
200	560	22 × 30	1.66	EKMR201VSN561MP30S
	560	25.4 × 25	1.56	EKMR201VSN561MQ25S
	680	22 × 35	1.87	EKMR201VSN681MP35S
	680	25.4 × 30	1.77	EKMR201VSN681MQ30S
	820	22 × 40	2.11	EKMR201VSN821MP40S
	820	25.4 × 35	2.03	EKMR201VSN821MQ35S
	820	30 × 25	1.72	EKMR201VSN821MR25S
	1,000	22 × 50	2.45	EKMR201VSN102MP50S
	1,000	25.4 × 40	2.30	EKMR201VSN102MQ40S
	1,000	30 × 30	1.95	EKMR201VSN102MR30S
	1,200	25.4 × 45	2.58	EKMR201VSN122MQ45S
	1,200	30 × 35	2.23	EKMR201VSN122MR35S
	1,200	35 × 25	1.94	EKMR201VSN122MA25S
	1,500	25.4 × 50	2.94	EKMR201VSN152MQ50S
	1,500	30 × 40	2.58	EKMR201VSN152MR40S
	1,500	35 × 30	2.25	EKMR201VSN152MA30S
	1,800	30 × 45	2.92	EKMR201VSN182MR45S
	1,800	35 × 35	2.53	EKMR201VSN182MA35S
	2,200	30 × 50	3.31	EKMR201VSN222MR50S
	2,200	35 × 40	2.92	EKMR201VSN222MA40S
	2,700	35 × 45	3.33	EKMR201VSN272MA45S

WV (V _{dc})	Cap (μF)	Case size ϕD×L(mm)	Rated ripple current (Arms/105°C, 120Hz)	Part No.
250	330	22 × 25	1.21	EKMR251VSN331MP25S
	390	22 × 30	1.38	EKMR251VSN391MP30S
	470	22 × 35	1.56	EKMR251VSN471MP35S
	560	22 × 40	1.74	EKMR251VSN561MP40S
	560	25.4 × 30	1.61	EKMR251VSN561MQ30S
	560	30 × 25	1.42	EKMR251VSN561MR25S
	680	22 × 45	1.97	EKMR251VSN681MP45S
	680	25.4 × 35	1.85	EKMR251VSN681MQ35S
	820	25.4 × 40	2.08	EKMR251VSN821MQ40S
	820	25.4 × 45	2.13	EKMR251VSN821MQ45S
	820	30 × 30	1.77	EKMR251VSN821MR30S
	820	35 × 25	1.60	EKMR251VSN821MA25S
	1,000	25.4 × 50	2.40	EKMR251VSN102MQ50S
	1,000	30 × 35	2.03	EKMR251VSN102MR35S
	1,200	30 × 40	2.31	EKMR251VSN122MR40S
	1,200	30 × 45	2.38	EKMR251VSN122MR45S
	1,200	35 × 35	2.06	EKMR251VSN122MA35S
	1,500	30 × 50	2.73	EKMR251VSN152MR50S
	1,500	35 × 40	2.41	EKMR251VSN152MA40S
	1,800	35 × 45	2.72	EKMR251VSN182MA45S
	2,200	35 × 50	3.10	EKMR251VSN222MA50S
315	180	22 × 25	0.91	EKMR3B1VSN181MP25S
	220	22 × 30	1.06	EKMR3B1VSN221MP30S
	270	22 × 35	1.20	EKMR3B1VSN271MP35S
	270	25.4 × 25	1.15	EKMR3B1VSN271MQ25S
	330	22 × 40	1.37	EKMR3B1VSN331MP40S
	330	25.4 × 30	1.30	EKMR3B1VSN331MQ30S
	390	22 × 45	1.52	EKMR3B1VSN391MP45S
	390	25.4 × 35	1.48	EKMR3B1VSN391MQ35S
	390	30 × 25	1.39	EKMR3B1VSN391MR25S
	470	22 × 50	1.72	EKMR3B1VSN471MP50S
	470	25.4 × 40	1.67	EKMR3B1VSN471MQ40S
	470	30 × 30	1.57	EKMR3B1VSN471MR30S
	470	35 × 25	1.52	EKMR3B1VSN471MA25S
	560	25.4 × 45	1.86	EKMR3B1VSN561MQ45S
	560	30 × 35	1.78	EKMR3B1VSN561MR35S
	680	25.4 × 50	2.10	EKMR3B1VSN681MQ50S
	680	30 × 40	2.03	EKMR3B1VSN681MR40S
	680	35 × 30	1.90	EKMR3B1VSN681MA30S
	820	30 × 45	2.31	EKMR3B1VSN821MR45S
	820	35 × 35	2.13	EKMR3B1VSN821MA35S
	1,000	30 × 50	2.61	EKMR3B1VSN102MR50S
	1,000	35 × 40	2.46	EKMR3B1VSN102MA40S
	1,200	35 × 45	2.78	EKMR3B1VSN122MA45S
	1,200	35 × 50	2.86	EKMR3B1VSN122MA50S
350	150	22 × 25	0.84	EKMR351VSN151MP25S
	220	22 × 30	1.06	EKMR351VSN221MP30S
	220	25.4 × 25	1.04	EKMR351VSN221MQ25S
	270	22 × 35	1.20	EKMR351VSN271MP35S
	270	25.4 × 30	1.18	EKMR351VSN271MQ30S
	330	22 × 40	1.37	EKMR351VSN331MP40S
	330	22 × 45	1.40	EKMR351VSN331MQ45S
	330	25.4 × 35	1.36	EKMR351VSN331MQ35S
	330	30 × 25	1.28	EKMR351VSN331MR25S
	390	22 × 50	1.56	EKMR351VSN391MP50S
	390	25.4 × 40	1.52	EKMR351VSN391MQ40S
	390	30 × 30	1.43	EKMR351VSN391MR30S
	390	35 × 25	1.38	EKMR351VSN391MA25S
	470	25.4 × 45	1.71	EKMR351VSN471MQ45S
	560	25.4 × 50	1.90	EKMR351VSN561MQ50S
	560	30 × 35	1.78	EKMR351VSN561MR35S
	560	30 × 40	1.84	EKMR351VSN561MR40S
	560	35 × 30	1.72	EKMR351VSN561MA30S
	680	30 × 45	2.10	EKMR351VSN681MR45S
	680	35 × 35	1.94	EKMR351VSN681MA35S
	820	30 × 50	2.36	EKMR351VSN821MR50S

KMR Series

◆ STANDARD RATINGS

WV (V _{dc})	Cap (μ F)	Case size ϕ D×L(mm)	Rated ripple current (Arms/105°C, 120Hz)	Part No.	WV (V _{dc})	Cap (μ F)	Case size ϕ D×L(mm)	Rated ripple current (Arms/105°C, 120Hz)	Part No.
350	820	35×40	2.23	EKMR351VSN821MA40S	420	270	25.4×40	1.32	EKMR421VSN271MQ40S
	1,000	35×45	2.54	EKMR351VSN102MA45S		270	30×30	1.26	EKMR421VSN271MR30S
	1,200	35×50	2.86	EKMR351VSN122MA50S		270	35×25	1.26	EKMR421VSN271MA25S
400	120	22×25	0.75	EKMR401VSN121MP25S		330	25.4×45	1.49	EKMR421VSN331MQ45S
	180	22×30	0.96	EKMR401VSN181MP30S		330	30×35	1.45	EKMR421VSN331MR35S
	180	25.4×25	0.94	EKMR401VSN181MQ25S		390	25.4×50	1.66	EKMR421VSN391MQ50S
	220	22×35	1.09	EKMR401VSN221MP35S		390	30×40	1.63	EKMR421VSN391MR40S
	220	25.4×30	1.07	EKMR401VSN221MQ30S		390	35×30	1.58	EKMR421VSN391MA30S
	270	22×40	1.24	EKMR401VSN271MP40S		470	30×45	1.85	EKMR421VSN471MR45S
	270	22×45	1.26	EKMR401VSN271MP45S		470	35×35	1.77	EKMR421VSN471MA35S
	270	25.4×35	1.23	EKMR401VSN271MQ35S		560	30×50	2.07	EKMR421VSN561MR50S
	270	30×25	1.16	EKMR401VSN271MR25S		560	35×40	2.02	EKMR421VSN561MA40S
	330	22×50	1.44	EKMR401VSN331MP50S		680	35×45	2.29	EKMR421VSN681MA45S
	330	25.4×40	1.40	EKMR401VSN331MQ40S		820	35×50	2.59	EKMR421VSN821MA50S
	330	30×30	1.31	EKMR401VSN331MR30S	450	100	22×25	0.71	EKMR451VSN101MP25S
	330	35×25	1.27	EKMR401VSN331MA25S		120	22×30	0.82	EKMR451VSN121MP30S
	390	25.4×45	1.55	EKMR401VSN391MQ45S		150	22×35	0.94	EKMR451VSN151MP35S
	390	30×35	1.49	EKMR401VSN391MR35S		150	25.4×25	0.89	EKMR451VSN151MQ25S
	470	25.4×50	1.74	EKMR401VSN471MQ50S		180	22×40	1.05	EKMR451VSN181MP40S
	470	30×40	1.69	EKMR401VSN471MR40S		180	25.4×30	1.00	EKMR451VSN181MQ30S
	470	35×30	1.58	EKMR401VSN471MA30S		220	22×45	1.19	EKMR451VSN221MP45S
	560	30×45	1.91	EKMR401VSN561MR45S		220	25.4×35	1.16	EKMR451VSN221MQ35S
	560	35×35	1.76	EKMR401VSN561MA35S		220	30×25	1.11	EKMR451VSN221MR25S
	680	30×50	2.15	EKMR401VSN681MR50S		270	22×50	1.36	EKMR451VSN271MP50S
	680	35×40	2.03	EKMR401VSN681MA40S		270	25.4×40	1.32	EKMR451VSN271MQ40S
	820	35×45	2.30	EKMR401VSN821MA45S		270	25.4×45	1.35	EKMR451VSN271MQ45S
	820	35×50	2.37	EKMR401VSN821MA50S		270	30×30	1.26	EKMR451VSN271MR30S
	1,000	35×50	2.50	EKMR401VSN102MA50S		270	35×25	1.26	EKMR451VSN271MA25S
420	120	22×25	0.78	EKMR421VSN121MP25S		330	25.4×50	1.52	EKMR451VSN331MQ50S
	150	22×30	0.91	EKMR421VSN151MP30S		330	30×35	1.45	EKMR451VSN331MR35S
	150	25.4×25	0.89	EKMR421VSN151MQ25S		330	35×30	1.45	EKMR451VSN331MA30S
	180	22×35	1.03	EKMR421VSN181MP35S		390	30×40	1.63	EKMR451VSN391MR40S
	180	25.4×30	1.00	EKMR421VSN181MQ30S		470	30×45	1.85	EKMR451VSN471MR45S
	220	22×40	1.16	EKMR421VSN221MP40S		470	35×50	1.90	EKMR451VSN471MR50S
	220	22×45	1.19	EKMR421VSN221MP45S		470	35×35	1.77	EKMR451VSN471MA35S
	220	25.4×35	1.16	EKMR421VSN221MQ35S		560	35×40	2.02	EKMR451VSN561MA40S
	220	30×25	1.11	EKMR421VSN221MR25S		560	35×45	2.08	EKMR451VSN561MA45S
	270	22×50	1.36	EKMR421VSN271MP50S		680	35×50	2.36	EKMR451VSN681MA50S

◆ RATED RIPPLE CURRENT MULTIPLIERS

◎ Frequency Multipliers

Frequency(Hz)	50	120	300	1k	10k	50k
160 to 250V _{dc}	0.81	1.00	1.17	1.32	1.45	1.50
315 to 450V _{dc}	0.77	1.00	1.16	1.30	1.41	1.43

The deterioration of aluminum electrolytic capacitors accelerates their life due to the internal heating produced by ripple current. For details, refer to Section "5-3 Ripple Current Effect on Lifetime" in the catalog, Technical Note.

- Always read "Notes on Use" before using the product in order to enable you to use the product correctly and prevent any faults and accidents from occurring.
- Request the Product Specification on the product of NIPPON CHEMI-CON CORPORATION to refer to it as well as this brochure prior to the order of the products. Some specific notes on use of the ordered product may be described in the specifications.
- The products listed in this catalog are designed and manufactured for general electronics equipment use and are not intended for use in applications that can adversely affect human life; where the malfunction of equipment may cause damage to life or property. In addition, our products are not intended to be used in specific applications that may cause a major social impact. Please consult with us in advance of usage of our products in the following listed applications. ① Aerospace equipment ② Power generation equipment such as thermal power, nuclear power etc. ③ Medical equipment ④ Transport equipment (automobiles, trains, ships, etc.) ⑤ Transportation control equipment ⑥ Disaster prevention / crime prevention equipment ⑦ Highly publicized information processing equipment ⑧ Submarine equipment ⑨ Other applications that are not considered general-purpose applications.
- The circuits described as examples in this catalog and the "delivery specifications" are featured in order to show the operations and usage of our products, however, this fact does not guarantee that the circuits are available to function in your equipment systems. We are not in any case responsible for any failures or damage caused by the use of information contained herein. You should examine our products, of which the characteristics are described in the "delivery specifications" and other documents, and determine whether or not our products suit your requirements according to the specifications of your equipment systems. Therefore, you bear final responsibility regarding the use of our products.
Please make sure that you take appropriate safety measures such as use of redundant design and malfunction prevention measures in order to prevent fatal accidents and/or fires in the event any of our products malfunction.
- We strongly recommend our customers to purchase Nippon Chemi-Con products only through our official sales channels. We assume no responsibility for any defects or damages caused by using products purchased from outside our official sales channel or of counterfeit goods. In addition, we will ask the customer to pay the investigation cost for products purchased outside our official sales channel.
- We reserve the right to discontinue production and delivery of products. We do not guarantee that all the products included in this catalog will be available in the future.
The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products
- We continually strive to improve the quality and reliability of our products, but in any case that our product does not meet our published specifications, please stop using it promptly and contact us immediately. As for compensation for non-conforming goods delivered by Chemi-Con, we will limit it only to goods found in non-compliance of our published specifications. This may be accomplished by a no cost replacement of non-conforming individual products, a credit of the piece price paid per each individual non-conforming product, or in other ways deemed necessary.
In addition, we have an established system with enhanced traceability, therefore we will limit the applicable lot items for any potential compensation.

[Part Numbering System](#)[Part Numbering System \(Appendix\)](#)[Standardization](#)[Available Items by Manufacturing Locations](#)[Environmental Measures](#)[Technical Note](#)[Precautions and Guidelines](#)[Recommended Soldering Conditions](#)[Taping, Lead-preforming and Packaging](#)[Available Terminals for Snap-in and Screw Mount Type](#)