

Double-Ended Shear Beam Load Cell

FEATURES

- Capacities 40 klb. & 50 klb.
- Coated Alloy Steel construction (Stainless Steel Available)
- Trade certified for NTEP class IIIL, 10000 divisions.
- IP67 protection

OPTIONAL

FM Approved versions for use in potentially explosive atmospheres

APPLICATIONS

- Truck scales
- Railroad track scales
- Precision tank, bin, and silo weighing.


DESCRIPTION

The Model 65061 is a mid to high capacity, Zinc or Nickel coated Alloy Steel, double ended shear beam load cell.

This product is designed for use in certified truck and railScales and is available in capacities 40 klb. and 50 klb.



OUTLINE DIMENSIONS in mm [inch]



Double-Ended Shear Beam Load Cell


SPECIFICATIONS		
PARAMETER	VALUE	UNIT
Rated capacity—R.C. (E_{max})	40, 50	klb.
NTEP/OIML accuracy class (1)	IIIL	
Maximum no. of intervals (n)	10000	
Y = E_{max}/V_{min}	15000*	
Rated output - R.O.	3.0	mV/V
Rated output tolerance	0.0075	±mV/V
Zero balance	0.0300	±mV/V
Creep, 20 min.	0.03	±% of applied load
Combined error (per NTEP)	0.03	±% of rated output
Temperature effect on zero	0.0027	±% of rated output/°C
Temperature effect on output	0.00144	±% of applied load/°C
Temp. range, compensated	-10 to +40	°C
Temp. range, safe & storage	-20 to +65	°C
Maximum safe central overload	150	% of R.C.
Ultimate central overload	300	% of R.C.
Excitation, recommended	10	VDC or VAC RMS
Excitation, range	5...15	VDC or VAC RMS
Input impedance	686...714	Ω
Output impedance	699...707	Ω
Insulation resistance	>1000	MΩ @50 VDC
Cable length	7.62 (25.0)	m (ft)
Cable type	4 wire, shielded, PU jacket, floating shield	Standard
Construction	Coated Alloy Steel (Stainless Steel available)	
Environmental protection	IP67	

* 65% utilization.

All specifications are subject to change without notice.

Optional Certification Marking:

FM Approval markings (USA and Canada)
 IS Class I, II, III, Division 1, Groups A, B, C, D, E, F and G;
 NI Class I, Division 2, Groups A, B, C, and D;
 DIP, Class II, III, Division 2, Groups F and G;
 T4;
 Ta = -25°C to +66°C

WIRING SCHEMATIC DIAGRAM
(Balanced bridge configuration)



Legal Disclaimer Notice

Vishay Precision Group, Inc.

Disclaimer

ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "VPG"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify VPG's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

VPG makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase. **To the maximum extent permitted by applicable law, VPG disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.**

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on VPG's knowledge of typical requirements that are often placed on VPG products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. You should ensure you have the current version of the relevant information by contacting VPG prior to performing installation or use of the product, such as on our website at vpgsensors.com.

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of VPG.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling VPG products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify VPG for any damages arising or resulting from such use or sale. Please contact authorized VPG personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Copyright Vishay Precision Group, Inc., 2014. All rights reserved.