



Powering Business Worldwide

Eaton 9PX 3000VA 2700W 120V Online Double-Conversion UPS - L5-30P, 6x 5-20R, 1 L5-30R Outlets, Cybersecure Network Card Option, Extended Run, 2U Rack/Tower

MODEL NUMBER: 9PX3000RT



Provides sine wave output, complete battery backup and power protection for mission-critical IT installations, edge networks and other advanced network applications.

Features

3kVA/2.7kW/120V Battery Backup for IT Installations and Edge Networks

This 9PX rack-mount online double-conversion UPS system provides reliable battery backup and AC power protection against blackouts, brownouts, surges and line noise that can damage valuable IT equipment or destroy data. The 9PX3000RT is superlative power management for education, commercial, financial or healthcare networking components, including Cisco switches and servers.

Expandable Internal Battery Backup Keeps You Operational Through Power Outages

The field-replaceable, hot-swappable valve regulated lead acid (VRLA) battery modules allow you to work through short power failures and give you enough time to safely save files and shut down your system in case of a prolonged blackout. Exclusive ABM technology increases battery life by 50 percent and closely monitors battery health to provide advanced notice when batteries need replacing. You can also connect up to four extended battery modules (9PXEBM72RT, sold separately) for hours of extended runtime.

Optional Gigabit Network Interface Offers 24/7 Remote Access

The NETWORK-M3 Gigabit network card (sold separately or as a network card bundle) enables full remote configuration and management, including load shedding, reboots of connected equipment and safe shutdowns. UPS firmware can also be flashed remotely through the NETWORK-M3 without dropping the load, so you don't have to plan for downtime. The card meets both UL 2900-1 and IEC 62443-4-2 standards for cybersecurity, which were developed to address the vulnerability of connected devices to known malware/exploits and to protect business from these risks. The optional Environmental Monitoring Probe Gen 2 (EMPDT1H1C2, sold separately) provides a variety of environmental monitoring capabilities, including temperature and humidity conditions.

NEMA Outlets Protect Your Connected Components

One L5-30R and six 5-20R managed outlets provide connected equipment with pure sine wave AC output and allow you to monitor power consumption down to the outlet group level. Power provided by these outlets is filtered to protect connected equipment against damaging surges and line noise. Four 5-20R outlets are grouped into two load banks that let you shed non-critical loads to extend runtime for critical loads.

Rotating LCD Interface Keeps You Informed at a Glance

Highlights

- Keeps equipment running during outages to allow time for file saves and safe shutdown
- Optional NETWORK-M3 Gigabit network card enables full remote access and control
- NEMA outlets split into separate switched banks for managed load shedding
- Interactive LCD interface keeps you updated on critical load information in real time
- Optional extended battery modules allow extended runtime to keep equipment powered

Package Includes

- 3000VA 2700W 120V 9PX Online Double-Conversion UPS with 7 Outlets
- USB cable
- RS-232 cable
- Rack-mounting hardware
- Tower support stands
- Safety guide
- Quick Start Guide



Powering Business Worldwide

The intuitive front-panel LCD provides control settings and critical information to help diagnose any issues. The interface rotates to accommodate both rack-mount and tower configurations, and it tilts up to 45 degrees for more comfortable viewing.

Advanced Communications Ports Allow for Automatic Saves and Shutdowns

RS-232 and USB ports connect to a serial-enabled device for a variety of communication options (cables are included). A dry-contact relay port can be programmed through the LCD to provide reliable communications to automation and industrial components. The RPO/ROO port permits emergency shutdown or remote restart of all connected equipment.

Versatile Installation Options

You can mount the 9PX3000RT in just 2U of space in an EIA-standard 19-inch rack using the included 4-post rail kit or an optional 2-post rail kit (RK2PC, sold separately). You can also adapt it for tower installation using the included support stands. The eight-foot power cord with NEMA L5-30P plug connects to a compatible AC outlet.

Specifications

OVERVIEW	
UPC Code	743172081285
UPS Type	On-Line
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	24A
Nominal Input Voltage(s) Supported	100V AC; 110V AC; 120V AC
UPS Input Connection Type	L5-30P
UPS Input Cord Length (ft.)	8
UPS Input Cord Length (m)	2.4
Recommended Electrical Service	120V 30A
Maximum Input Amps	24
Input Plug Type	NEMA L5-30P
OUTPUT	
Output Capacity (VA)	3000
Output Capacity (kVA)	3
Output Capacity (Watts)	2700
Output Capacity (kW)	2.7
Power Factor	0.9
Crest Factor	3:1
Nominal Voltage Details	100V, 110V, 120V, 125V
Frequency Compatibility	50 / 60 Hz
Output Circuit Breakers	(3) 20A for (2) 5-20R each



Powering Business Worldwide

Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	100V; 110V; 120V; 125V
Output Receptacles	(6) 5-20R; (1) L5-30R
Individually Controllable Load Banks	Yes
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Runtime Full Load (min.)	5 min. (2700W)
Runtime Half Load (min.)	14 min. (1350W)
Expandable Runtime	Yes
Expandable Runtime Description	Add up to 4 extended battery modules (EBM). Part number <a >9pxebm72rt<="" a="" href="//tripplite.eaton.com/eaton-9px-external-battery-for-9px3000rt-9px3000grt-9px3000glrt-9px2000rt-9px2200grt-2u~9PXEBM72RT">
DC System Voltage (VDC)	72
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	<a >744-a3122<="" a="" href="//tripplite.eaton.com/replacement-battery-for-eaton-9px-3kva-ups~744-A3122">
Battery Replacement Description	Hot-swappable, user replaceable batteries. UPS requires 1 Replacement Battery Cartridge.
Battery Management	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	LCD graphical display
Switches	RPO / ROO
Alarm Cancel Operation	Press ESC to silence the alarm
Audible Alarm	Audible alarm indicates utility failure, low-battery, overload, other UPS/Battery fault or remote shutdown conditions
LED Indicators	4 status-indicating LEDs
SURGE / NOISE SUPPRESSION	
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	190
AC Suppression Response Time	0 ms
PHYSICAL	
Primary Form Factor	Rackmount; Tower
Rack Height	2U
Cooling Method	Fan
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount; Tower



Powering Business Worldwide

Installation Form Factors Supported with Optional Accessories	2 post rackmount (RK2PC)
Minimum Required Rack Depth (cm)	68.58
Minimum Required Rack Depth (inches)	27
Unit Dimensions (hwd / in.)	3.400 x 17.300 x 23.800
Unit Weight (lbs.)	63.100
Unit Weight (kg)	28.62
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-96% non-condensing
AC Mode Efficiency Rating (100% Load)	91.8
AC Economy Mode Efficiency Rating (100% Load)	97.2
Online Mode Heat Dissipation (BTU/Hr) @ Full Load	844
Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	1462
COMMUNICATIONS	
Network Management Cards	Network-M3 ; INDGW-M2 ; RELAY-MS
Communications Interface	RS-232; USB
APPLICATIONS	
UPS Applications	Mission Critical Applications
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; NOM (Mexico); EN 62040-2; EN 55022; ICC-ES AC156 OSHPD Seismic Certified
Product Compliance	FCC Part 15 Class B (USA); CE (Europe); ENERGY STAR Qualified; VCCI (Japan); RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Extended Service Plans	ADVANCED DEPOT EXCHANGE Service Part Number: 9SW5Y-3000UCExpedited parts coverage for 5 yearsParts, electronics and UPS batteries coverageNext business day shippingTechnical support 5-YEAR ON-SITE PLAN (US ONLY) Service Part Number: WFLN75XX-6009UCOn-site parts and labor coverage for years 5Parts, electronics and UPS batteries coverage24x7 on-site labor coverage, next-day responseNext-day shippingTechnical support



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.