

2-Port DVI over Cat5/6 Splitter/Extender, Box-Style Transmitter for Video, Dual-Display DVI-D, 200 ft. (60 m), TAA

MODEL NUMBER: **B140-002-DD**



Split and extend Dual DVI signals from a computer to two sets of Dual Displays

Description

The B140-002-DD splits two PC DVI source video signals to two remote monitors. Passive, non-powered receivers allow distances up to 50 feet (15.2 meters) at 1920 x 1200 resolution, or 100 feet (30.5 meters) at 1024 x 768 resolution, over solid conductor Cat6 cable. Active, powered receivers extend the distance to 150 feet (45.7 meters) at 1920 x 1200 and 200 feet (61 meters) at 1024 x 768 (receivers purchased separately). Additional monitors can be daisy-chained (up to three) on each channel, allowing four monitors per channel, by using the B140-110 Repeater/Extender (sold separately). N202-Series Cat6 cables are designed specifically for these types of devices...pre-terminated, solid conductor Cat6 Ethernet cables up to 200 feet. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Transmits a DVI-D Single-Link signal from a set of Dual DVI inputs to two sets of Dual Displays
- A B140-Series remote receiver is needed at each monitor
- For longer distances: Use a B140-1A0 active receiver to extend a 1920 x 1200 at 60 Hz signal up to 150-ft. (45.7 m) from the transmitter (or a 1024 x 768 at 60 Hz signal up to 200-ft. (61 m) from the transmitter)
- For shorter distances: Use a B140-1P0 passive receiver to extend a 1920 x 1200 at 60 Hz signal up to 50-ft. (15.2 m) from the transmitter (or a 1024 x 768 at 60 Hz signal up to 100-ft. (30.5 m) from the transmitter)
- Use 24 AWG Solid Wire Cat5e/6 cable, such as N202-Series to achieve maximum distance and resolution
- Further expand the range and number of monitors by adding B140-110 remote repeater units
- Add up to three repeaters on each of the B140-002-DD channels, for a total of 4 displays per channel (An active receiver should be the last unit in a channel)
- A 1920 x 1200 at 60 Hz signal can be extended up to 125-ft. (38.1 m) for each repeater added into a channel (or up to 175-ft. (53.3 m) for a 1024 x 768 at 60 Hz signal)
- DVI 1.0 compliant
- HDCP compatible
- Mounting hardware included that allows the unit to be wall-mounted, rack-mounted, or pole mounted
- Plug and play; no software or drivers required

Highlights

- Split and extend Dual DVI signals from a computer to two sets of Dual Displays
- 1920 x 1200 (60Hz) resolution up to 150-ft. (45.72 m)
- Up to 4 displays per channel when using repeaters
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

Package Includes

- B140-002-DD Extender / Splitter Transmitter Unit
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A)
- Mounting Hardware
- Owner's Manual

- Compatible with all operating systems
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332177513
Product Type	Splitter; Extender Kit
Technology	DVI; Cat5/5e; Cat6
Host Connector	HD15 (FEMALE)
VIDEO	
Max Supported Video Resolution	1920 x 1080 (1080p) @ 60Hz
Max 720P Range (ft)	150
Max 1080P Range (ft)	150
Max 1280 x 720 (720p) Range (ft)	150
Max 1920 x 1080 (1080p) Range (ft)	150
Transmitter Video Input	DVI-I
Transmitter - Number of Video Outputs	2
Range Extension using other Tripp Lite product	175 ft. @ 1024 x 768 XGA 125 ft. @ 1920 x 1080 UXGA
Recommended Cabling	N202-Series Cat6 Patch Cable
Other Tripp Lite product used to extend range	B140-110
HDR Support	No
3D Video Supported	Yes
Maximum Signal Range (ft)	200
Maximum Signal Range (m)	61
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.5A
AC Power Adapter Output Specs (V / A)	5V / 2A
AC Power Adapter Cord Length (ft.)	4.5
AC Power Adapter Cord Length (m)	1.4
Bus Powered	No



Powering Business Worldwide

TRIPP LITE
SERIES

POWER	
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P
Power Source	Unit (Included)
Power Over Cable (PoC) Support	No
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A
DC Barrel Plug	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	(2) DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
Side B - Connector 1	(4) RJ45 (FEMALE)
Input x Output	1 x 2
Daisy-chainable / Cascadable	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	RJ45: Green (Connection), Orange (Data Transmission)
PHYSICAL	
Color	Black
Cable Length (ft.)	0
Cable Length (m)	0.00
Number of Displays	2
Form Factor/Mounting Options	Box; Wall-mount
Shipping Dimensions (hwd / in.)	2.17 x 8.43 x 6.46
Shipping Dimensions (hwd / cm)	5.51 x 21.41 x 16.41
Shipping Weight (lbs.)	1.54
Shipping Weight (kg)	0.70
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	3.05 x 12.7 x 9.14
Unit Packaging Type	Box
Unit Weight (lbs.)	0.8
Unit Weight (kg)	0.36
Housing	Metal
Mounting Details	Wallmount
ENVIRONMENTAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0-85% non-condensing
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	200
Max 480P Range (ft)	200
Max 1440 x 900 Range (ft)	150
Max 1080i Range (ft)	150
Max 480i Range (ft)	200
Max 640 x 480 Range (ft)	200
Max 800 x 600 Range (ft)	200
Max 1600 x 1200 Range (ft)	150
EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	Yes
USB Extension Support	No
FEATURES & SPECIFICATIONS	
10/100 Ethernet Extension Support	No
MST Support	No
Built-In Equalizer	No
Driver Required	No
STANDARDS & COMPLIANCE	
External Power Supply Certifications	FCC; PSE; TUV; UL; cUL
Product Compliance	RoHS; REACH; FCC (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.