


## Cisco-Compatible QSFP+ Transceiver - 40GBase-PLR4, Singlemode MPO/MTP, 1310 nm, 10 km (6.2 mi.)

MODEL NUMBER: **N286-40G-PLR4**



Connects a singlemode Gigabit Ethernet fiber cable to a Cisco switch or server's QSFP+ port.

### Features

#### QSFP+ Transceiver Designed for Connection to Your Cisco Network Switch or Server

This QSFP+ transceiver allows you to connect a singlemode fiber optic cable to a 40 Gbps network router, server or switch. It transmits data up to 10 kilometers (6.2 miles) using a 1260 to 1360 nm wavelength. The zinc housing protects against electromagnetic interference (EMI) and excessive power dissipation.

#### Functionally Equivalent to Cisco QSFP-4X10G-LR-S Transceiver Module

The MSA-compliant N286-40G-PLR4 functions just like the equivalent Cisco QSFP-4X10G-LR-S transceiver module and is manufactured to meet or exceed Cisco specifications. You can use this transceiver with any compatible Cisco router, server or switch and receive the same performance as the QSFP-4X10G-LR-S.

#### Hot-Swappable for Installation Without Network Interruption

This input/output device is fully hot-swappable, so you can install it without a potentially costly network shutdown or device reboot. Just plug the QSFP+ end of the transceiver into your Cisco network device. The other end has an MPO/MTP connector to link with singlemode fiber optic cable (sold separately). A push/pull tab connector is easily accessible in high-density data center applications and makes the plug-and-play transceiver easy to install and remove with one hand.

## Specifications

OVERVIEW	
UPC Code	037332279354
Brand Compatibility	Cisco
POWER	
Power Consumption (Watts)	2.00

### Highlights

- QSFP+ transceiver module 100% compatible with Cisco's QSFP-4X10G-LR-S module
- Provides 40 Gbps throughput up to 10 km (6.2 mi.) via singlemode fiber cabling
- MPO/MTP male connector supports 40GBase-LR4 signal at 1260-1360 nm wavelength
- Hot-swappable interface lets you install and uninstall without shutting down
- Meets or exceeds MSA standards and works in all MSA-compliant platforms

### System Requirements

Cisco or other compatible network router, server or switch

### Package Includes

N286-40G-PLR4 QSFP+ Transceiver



Powering Business Worldwide

TRIPP LITE  
SERIES

CONNECTIONS	
Side A - Connector 1	MTP/MPO (FEMALE)
Side B - Connector 1	QSFP+ (MALE)
PHYSICAL	
Color	Silver
Material of Construction	Zinc Alloy
Shipping Dimensions (hwd / in.)	0.70 x 3.10 x 5.70
Shipping Weight (lbs.)	0.11
Unit Dimensions (hwd / in.)	0.330 x 0.530 x 2.680
Unit Dimensions (in.)	0.330 x 0.530 x 2.680
Unit Packaging Type	Box
ENVIRONMENTAL	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	-40° to 185°F (-40° to 85°C)
Operating Humidity Range	5 - 85 % RH
COMMUNICATIONS	
Network Compatibility	40 Gbps
Wavelength	1270nm; 1310nm; 1330nm
Transmission Distance	10 km
FEATURES & SPECIFICATIONS	
Data Transfer Rate	40 Gbps
Multi-Source Agreement (MSA) Compliant	Yes
Optical Port	MPO/MTP
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); MSA SFF-8436; REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



*Powering Business Worldwide*

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

TRIPP LITE  
SERIES

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.