

Duplex Multimode 50/125 Fiber Patch Cable (LC/LC), 4M (13 ft.)

MODEL NUMBER: **N520-04M**



Features

- Constructed with 50/125 micron cable
- Length - 4Meter
- Use on fiber and fibre channel installations
- LC male to LC male connectors
- Higher bandwidth optimized for gigabit and 10Gbps networks
- Backward compatible with 62.5 micron fiber
- Built-in headroom for future applications
- Number of fibers: 2
- Fiber type: all glass graded index
- Core diameter: two 50+-3 microns
- CLAD diameter: 125+-2 microns
- Primary coating diameter: 245+-15 microns
- Primary coating material: acrylate
- Secondary coating diameter: 900+-50 microns

Secondary coating material: PVC Attenuation @850NM: 3.5DB/KM maximum, @1300NM: 1.0DB/KM maximum Bandwidth @850NM: 220 MHz-KM minimum, @1300NM: 600 MHz-KM minimum Numeric aperture: .275 nominal Proof test level: 100,000 PSI Insertion loss testing performed on every connector (0.2db typical) and provided with cable Beveled edge on ends of glass makes insertion of plug a breeze

Specifications

| OVERVIEW | |
|--------------|--------------|
| UPC Code | 037332143907 |
| Technology | Multimode |
| Optical Mode | OM2 |

Highlights

- Premium PVC multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards
- Higher bandwidth optimized for gigabit and 10Gbps networks
- Backward compatible with 62.5 micron fiber
- Built-in headroom for future applications

System Requirements

Any fiber optic hardware or NIC card requiring multimode duplex cable with LC/LC connectors

Package Includes

4meter duplex MMF cable LC/LC
50/125 fiber



Powering Business Worldwide

TRIPP LITE
SERIES

| CONNECTIONS | |
|---------------------------------|------------------------------------|
| Side A - Connector 1 | LC DUPLEX (MALE) |
| Side B - Connector 1 | LC DUPLEX (MALE) |
| Endface Polish | PC |
| PHYSICAL | |
| Cable Jacket Color | Orange |
| Connector Color | Gray |
| Cable Jacket Material | LSZH |
| Cable Jacket Rating | OFNR |
| Clad Diameter (microns) | 125 |
| Core Diameter (microns) | 50 |
| Number of Fibers | 2 |
| Cable Length (ft.) | 13.1 |
| Cable Length (m) | 3.99 |
| Cable Length (in.) | 157.5 |
| Minimum Bend Radius | 20 mm (Dynamic); 10 mm (Static) |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 22.86 x 17.78 x 1.27 |
| Shipping Weight (lbs.) | 0.08 |
| Shipping Weight (kg) | 0.04 |
| Fiber Cable Length | 4M (13.1 ft) |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range | 5% to 85% RH, Non-Condensing |
| Storage Humidity Range | 35% to 65% RH, Non-Condensing |
| COMMUNICATIONS | |
| Network Compatibility | 1 Gbps (Gigabit); 10 Gbps; 25 Gbps |
| Attenuation @ 850NM | 3.0 dB/km |
| Insertion Loss | 0.20 dB |
| FEATURES & SPECIFICATIONS | |
| Push/Pull Tabs | No |
| Breakout | No |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|-------------------------------------|---------------------------|
| Trunk | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; REACH |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.