

## Hardened Gigabit Fiber to Ethernet Media Converter, 10/100/1000 Mbps, RJ45/SC Multimode, -10° to 60°C, 500 m (1640 ft.), TAA

MODEL NUMBER: **N785-H01-SCMM**



Extends a 10/100/1000 Mbps Gigabit Ethernet network connection over SC duplex multimode fiber optic cable up to 500 meters.

### Features

#### Extends a Network Connection up to 500 m over SC Multimode Fiber Optic Cable

This network media converter converts a copper Gigabit Ethernet signal to a multimode fiber optic signal and extends it to a second network device up to 500 meters (1640 feet) away. Because copper Cat5e/6 cables are limited to only 100 meters, it is more effective to couple the N785-H01-SCMM with multimode fiber cable to reach hubs, switches and other network devices located farther away. Auto-negotiation and automatic MDI/MDI-X configuration seamlessly connect devices without crossover cabling.

#### Monitor Your Installation with Link Fault Signaling and Loop Back Functions

Determine the health of your network connection via the Link Fault Signaling (LFS) and Loop Back functions. The LFS LED indicates when a copper or fiber cable has been severed or another cause of disruption in service has occurred. The Local Loop Back (LLB) and Remote Loop Back (RLB) functions ensure copper and fiber cables have been correctly installed. Use the DIP switches to control each function or turn them on or off.

#### LEDs Indicate Installation Performance and Diagnostic Functions

Easy-to-read LEDs on the side of the unit indicate essential status information, including network speed and connection, LFS diagnostics and unit power.

#### Protective Metal Housing Built to Withstand a Variety of Hazards

The hardened aluminum case is designed to operate in extreme temperatures ranging from -10 to 60 degrees Celsius (14 to 140 degrees Fahrenheit). It is protected from electrostatic discharge (ESD), radio frequency interference (RFI) and power surges. Hardware is included for wall or DIN mounting.

#### Works in Tandem with N785-CH12 Chassis

House and power up to 12 media converters, including the N785-H01-SCMM, using the N785-CH12 12-port chassis (sold separately) to create an organized installation.

#### TAA-Compliant for GSA Schedule Purchases

The N785-H01-SCMM is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

### Highlights

- Extends up to 1000 Mbps (1 Gbps) of data to a network device up to 500 m away
- Automatic MDI/MDI-X configuration connects devices without crossover cabling
- Hardened aluminum housing withstands operating temperature range of -10° to 60°C
- LEDs indicate Ethernet connection and various statuses, including data transfer speed
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

- N785-H01-SCMM Media Converter
- L-shaped bracket
- Rubber foot
- SC connector cap
- External power supply with NEMA 1-15P plug (Input: 100-240VAC, 50/60 Hz, 0.5A; Output: 12VDC 1.5A)
- DIN rail kit
- Wall-mounting hardware
- Quick Start Guide

## Specifications

OVERVIEW	
UPC Code	037332267047
Product Type	Fiber to Ethernet
Technology	Cat5/5e; Cat6; Multimode
Mode Type	Multimode
DISPLAY	
Accessories (Included)	External Power Supply (Input: 100-240V, 50/60Hz, 0.5A; Output: 12V/1.5A), Mounting Bracket, Mounting Hardware, DIN Rail, SC Connector Cap, L-Shape Holder, Rubber Foot
NETWORK	
Network Ports	RJ45 (FEMALE); SC (FEMALE)
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.5A
AC Power Adapter Output Specs (V / A)	12V / 1.5A
AC Power Adapter Cord Length (ft.)	3.94
AC Power Adapter Cord Length (m)	1.2
POWER	
Power Source Type	AC Adapter
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 12V, 1.5A
DC Barrel Plug	OD: 5.5 x 2.5 x 11mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	1.80
CONNECTIONS	
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	SC (FEMALE)
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	PWR (Power), ALM (LFS function indicator), Fiber - 1000 (For Ethernet speed 1000Mbps), LNK/ACT (For Fiber port data transmitting/receiving), RJ45 - 1000 (For RJ45 speed 1000Mbps), LNK/ACT (For Copper port data transmitting/rec)
PHYSICAL	
Color	Black
Power Cord Color	Black



Powering Business Worldwide

TRIPP LITE  
SERIES

Unit Dimensions (hwd / in.)	0.920 x 2.910 x 4.300
Unit Dimensions (hwd / cm)	2.34 x 7.38 x 10.92
Unit Packaging Type	Box
Unit Weight (lbs.)	0.5267
Unit Weight (kg)	0.24
Housing	Metal
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 185°F (-40° to 85°C)
Relative Humidity	5% to 95% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Network Compatibility	10 Mbps; 100 Mbps (Fast Ethernet); 1 Gbps (Gigabit)
Network Speed Details	10 Mbps; 100 Mbps; 1000 Mbps
Wavelength	850nm
Transmission Distance	500 m
IEEE Standards Supported	802.3; 802.3ab; 802.3u; 802.3z
Wavelength Division Multiplexing (WDM)	Yes
<b>FEATURES &amp; SPECIFICATIONS</b>	
Data Transfer Rate	1 Gbps; 10 Mbps; 100 Mbps
Mounting Accessory Included	Yes
Auto MDIX Support	Yes
DIN Mountable	Yes
Optical Port	SC
<b>STANDARDS &amp; COMPLIANCE</b>	
External Power Supply Certifications	FCC; LPS; UL; WEEE
Product Compliance	RoHS; CE (Europe); FCC (USA); Trade Agreements Act (TAA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty



*Powering Business Worldwide*

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

TRIPP LITE  
SERIES

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.