

Eaton 9PXM 4-16kVA 208/240V Split-Phase Modular Scalable Online Double-Conversion UPS Cabinet, Hardwired Input / Output, Cybersecure Network Card Option, 14U, TAA

MODEL NUMBER: **9PXM08AAXXX**



Provides sine wave output, complete battery backup and power protection for mission-critical colocation and edge data centers or other advanced network applications.

Features

Modular, Scalable Battery Backup for Edge Data Centers and Industrial/Commercial Applications

This 9PXM online double-conversion UPS cabinet is superlative power management. Rugged enough to stand up to mission-critical applications, the 9PXM08AAXXX's dual network card slots and N+X redundancy make it a valuable UPS system for colocation and edge data centers, as well as industrial/commercial applications, including retail, financial, government and education. It features hardwired input and output connections.

Protects Mission-Critical Equipment against Damage, Downtime and Data Loss

The 9PXM08AAXXX provides reliable power protection against blackouts, brownouts, surges and line noise that can damage valuable IT equipment or destroy data. The 14U cabinet contains eight slots, which accommodate a maximum of four power modules with eight internal battery modules (two per slot) in the remaining four slots. If you choose to install only one power module, you may install up to 14 battery modules in the remaining seven slots.

UPS Has a Power Range up to 16kVA

The UPS cabinet accommodates up to four hot-swappable 4kVA power modules (9PXMSPPM, sold separately) total for 16kVA or 12kVA N+X redundancy that eliminates system-level single point of failure. Power modules may be removed and replaced without powering down the UPS system if it has sufficient redundant capacity. All power modules share the load requirements equally, even if one power module fails or is removed.

Expandable Internal Battery Backup Keeps You Operational Through Power Outages

The UPS cabinet can accept two hot-swappable extended battery modules (9PXMBAT, sold separately) per slot. The valve regulated lead acid (VRLA) battery modules allow you to work through short power failures and give you enough time to safely save files and shut down your system in case of a prolonged blackout. Exclusive ABM® technology increases battery life by 50 percent and closely monitors battery health to provide advanced notice when batteries need replacing.

Optional Gigabit Network Interface Offers 24/7 Remote Access

The NETWORK-M3 Gigabit network card (sold separately) enables full remote configuration and management, including load shedding, reboots of connected equipment and safe shutdowns. UPS

Highlights

- Keeps equipment running during outages to allow time for file saves and safe shutdown
- Exclusive ABM technology with 3-stage charging increases internal battery life by 50%
- Optional NETWORK-M3 Gigabit network card enables full remote access and control
- N+X redundancy for power and logic eliminates system-level single point of failure
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- 9PXM08AAXXX 9PXM 208/240V Online Double-Conversion UPS Cabinet
- Owner's manual



Powering Business Worldwide

firmware can also be flashed remotely through the NETWORK-M3 without dropping the load, so you don't have to plan for downtime. The card meets both UL 2900-1 and IEC 62443-4-2 standards for cybersecurity, which were developed to address the vulnerability of connected devices to known malware/exploits and to protect business from these risks. The optional Environmental Monitoring Probe Gen 2 (EMPDT1H1C2, sold separately) provides a variety of environmental monitoring capabilities, including temperature and humidity conditions.

Intuitive Control Panel Keeps You Informed at a Glance

The UPS control panel includes a graphical LCD, light indicators and function buttons. The control panel provides data and control for the UPS, load status, events, measurements and settings.

Advanced Communications Ports Allow for Automatic Saves and Shutdowns

RS-232 and USB ports connect to a serial-enabled or USB-enabled device for a variety of communication options (cables are included). The RPO and ROO connectors permit emergency shutdown or remote restart of all connected equipment. By adding the optional RELAY-MS interface card (sold separately), a dry-contact relay port can be programmed through the LCD to provide reliable communications to automation and industrial components.

Versatile Installation Options

You can install the 9PXM08AAXXX in 14U of space in an EIA-standard 19-inch rack using the optional rackmount kit (9PXMRK2, sold separately). Leveling feet and a caster tray are included for secure floor installation.

TAA-Compliant for GSA Schedule Purchases

The 9PXM08AAXXX is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	743172091406
UPS Type	On-Line
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	125A
Nominal Input Voltage(s) Supported	110V AC; 120V AC; 127V AC; 208V AC; 220V AC; 240V AC
UPS Input Connection Type	Hardwire
Maximum Input Amps	125
Input Frequency	50-70 Hz
Input Plug Type	Hard-wire
Power Factor (Input)	0.99
THDi	<5% at nominal input voltage, full load and battery fully charged
OUTPUT	
Output Capacity (VA)	16000
Output Capacity (kVA)	16



Powering Business Worldwide

Output Capacity (Watts)	14400
Output Capacity (kW)	14.4
Output Capacity Details	Scalable output capacity from 4kVA to 16kVA
Power Factor	0.9
Crest Factor	3:1
Nominal Voltage Details	110V/220V, 120V/208V, 120V/240V, 127V/220V
Frequency Compatibility	50 / 60 Hz
Output Voltage Regulation (Line Mode)	<5% steady state
Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	110V; 120V; 127V; 208V; 220V; 240V
Output Receptacles	Hardwire
Individually Controllable Load Banks	No
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Expandable Runtime	Yes
Expandable Runtime Description	 9PXMBAT (2 required per slot). Additional extended runtime options are available. See pg. 8 of the 9PXM brochure under Documents & Downloads for more details.
DC System Voltage (VDC)	120 per battery string
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	 9PXMBAT
Battery Replacement Description	Hot-swappable internal batteries and extended battery modules (EBMs)
Battery Management	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	LCD graphical display
Switches	RPO / ROO
Alarm Cancel Operation	Press ESC to silence the alarm
Audible Alarm	Audible alarm indicates utility failure, low-battery, overload, other UPS/Battery fault or remote shutdown conditions
LED Indicators	4 status-indicating LEDs
SURGE / NOISE SUPPRESSION	
EMI / RFI AC Noise Suppression	Yes
AC Suppression Response Time	0 ms



Powering Business Worldwide

PHYSICAL	
Primary Form Factor	Rackmount; Tower
Rack Height	14U
Cooling Method	Fan
Form Factors Supported	Rack/Tower
Installation Form Factors Supported with Included Accessories	Tower
Maximum Device Depth (cm)	88.90
Maximum Device Depth (in.)	35
Maximum Device Depth (mm)	889
Minimum Required Rack Depth (cm)	96.52
Minimum Required Rack Depth (inches)	38
Minimum Required Rack Depth with External Battery Pack (cm)	97
Minimum Required Rack Depth with External Battery Pack (in.)	38
Minimum Required Rack Depth without External Battery Pack (cm)	97
Minimum Required Rack Depth without External Battery Pack (in.)	38
Optional Mounting Accessory Notes	 9PXMRAK2 - Four post rail kit
Primary UPS Depth (mm)	889
Primary UPS Height (mm)	635
Primary UPS Width (mm)	445
Unit Dimensions (hwd / in.)	25.000 x 17.500 x 34.500
Unit Weight (lbs.)	125.000
Unit Weight (kg)	56.70
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	5-95% non-condensing
AC Mode Efficiency Rating (100% Load)	94
AC Economy Mode Efficiency Rating (100% Load)	97
COMMUNICATIONS	
Network Management Cards	NETWORK-M2; INDGW-M2 RELAY-MS



Powering Business Worldwide

Communications Interface	RS-232; USB
FEATURES & SPECIFICATIONS	
High Availability UPS Features	Hot swappable batteries; Hot swappable UPS power module; Remote management
APPLICATIONS	
UPS Applications	Mission Critical Applications
STANDARDS & COMPLIANCE	
Product Certifications	IEC 61000; UL Listed; cUL Listed
Product Compliance	FCC (USA); RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.