

5-Port Unmanaged Industrial Ethernet Switch - 10/100 Mbps, Ruggedized, -40° to 75°C, iQoS, DIN/Wall Mount, TAA

MODEL NUMBER: **NFI-U05A**



Industrial-grade switch expands Ethernet connectivity to factory floors and other environments with space constraints and wide temperature ranges.

Features

5-Port Unmanaged Ethernet Switch Connects Your Devices to a LAN

This space-saving switch with EIP QoS transmits data over an Ethernet network. Five auto-negotiating 10/100 Mbps ports send data only to the devices designated to receive it, which improves the efficiency and potential throughput of the network.

Supports Intelligent QoS for PROFINET, EtherNet/IP and IEC 61850 GOOSE Traffic

Eaton's iQoS (Intelligent Quality of Service) is designed to support PROFINET, Ethernet/IP (EIP) and GOOSE traffic by ensuring reliable and consistent data delivery in industrial networks. Based on the characteristics of aforementioned industrial protocol communication, iQoS automatically recognizes and prioritizes traffic with industrial protocol mentioned to maintain stable network performance under normal operating conditions. This built-in mechanism helps ensure deterministic behavior for critical industrial data streams without requiring user configuration, making it well suited for plug-and-play deployments in OT environments. **Note:** While Eaton devices such as the NFI-U05A support automatic QoS handling through iQoS, they do not provide manual traffic classification or port-level priority configuration. For applications requiring customized traffic policies—managed network switch with advanced QoS functionality should be deployed.

Ruggedized Metal Housing Built to Last in Harsh Environments

The compact NFI-U05A adds 10/100 Mbps Ethernet capacity to your industrial and commercial applications, such as factory floors, warehouse operations and other environments with space constraints and wide temperature ranges. The industrial-grade high-strength case withstands vibration, shock and free fall. It can also operate in extreme temperatures ranging from -40 to 75 degrees Celsius (-40 to 167 degrees Fahrenheit).

Unmanaged Switch Requires Little to No Configuration

Quickly connect your network devices with little to no configuration. LEDs indicate when the switch is powered on and which Ethernet ports are showing activity. The NFI-U05A supports MAC address auto-learning and auto-aging for efficient routing, as well as automatic MDI/MDI-X crossover detection for plug-and-play functionality. IEEE 802.3x flow control allows smooth transmission of large files.

Flexible Mounting Options

The open-type device may be DIN mounted using the pre-installed rail clip, which mounts firmly to any

Highlights

- 5 auto-negotiable 10/100 Mbps RJ45 ports connect devices over a LAN
- Supports Intelligent QoS (iQoS) for PROFINET, EtherNet/IP and IEC 61850 GOOSE traffic
- Industrial-grade switch supports operating temperature range of -40° to 75°C
- Easy-to-read LEDs indicate connection and activity status for all Ethernet ports
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- NFI-U05A 5-Port Unmanaged Industrial Switch
- DIN rail-mounting clip (pre-installed)
- Wall-mounting bracket (pre-installed)
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

standard 35 mm DIN rail. It may also be wall mounted using the rear mounting holes. A 3-pin 12–48VDC terminal block supplies power input. Device power must be supplied by SELV circuit.

TAA-Compliant for GSA Schedule Purchases

The NFI-U05A is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	037332282033
Product Type	Unmanaged Industrial Ethernet Switch with EIP QOS
INPUT	
Maximum Input Amps Details	Maximum of 0.15A DC. The device power shall be supplied by SELV circuit
Voltage Compatibility (VDC)	From 12~48
Power Source	3-Pin Terminal Block
POWER	
Power Consumption (Watts)	3.00
CONNECTIONS	
Number of Ports	5
Ports	5
Ports Detail	5x 10/100Base-T
PoE Supported Ports	0
Network Switch Ports	(5) 10/100 (RJ45)
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	1- PWR(Green): for Power; 2- 100(Green): for Ethernet speed 100Mbps; 3- LNK/ACT(Green): for data transmitting/receiving
PHYSICAL	
Primary Form Factor	DIN-Rail; Wall-mount
Color	Black
Material of Construction	Aluminum casing
Shipping Dimensions (hwd / in.)	2.44 x 5.04 x 9.33
Shipping Dimensions (hwd / cm)	6.20 x 12.80 x 23.70
Shipping Weight (lbs.)	0.68
Shipping Weight (kg)	0.31
Unit Dimensions (hwd / in.)	4.300 x 0.920 x 2.910



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Dimensions (hwd / cm)	10.9 x 2.2 x 7.3
Unit Weight (lbs.)	0.42
Unit Weight (kg)	0.19
ENVIRONMENTAL	
Operating Temperature Range	-40° to 167°F (-40° to 75°C)
Storage Temperature Range	-40° to 185°F (-40° to 85°C)
Relative Humidity	5% to 95% (Non-Condensing)
COMMUNICATIONS	
Network Compatibility	100 Mbps (Fast Ethernet)
Network Compatibility Details	Auto-negotiable
Switching Capacity	1Gbps
Switching Capacity Details	200Mbps Per Port with Full Duplex
FEATURES & SPECIFICATIONS	
Jumbo Frames	0
Console Port	No
MAC Auto Learning	Yes
RMON	No
SNMP	No
Storm Control	No
DHCP Snooping	No
Auto MDI/MDIX Crossover Detection	Yes
Industrial QoS (iQoS)	Yes
STANDARDS & COMPLIANCE	
Product Certifications	NOM (Mexico)
Product Compliance	CE (Europe); FCC (USA); IEEE 802.1p Class of Service (Europe); IEEE 802.3 10Base-T; IEEE 802.3 Auto-Negotiation; IEEE 802.3u 100Base-TX/FX; IEEE 802.3x Flow Control; REACH; RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.