

## OmniSmart 120V 500VA 300W Line-Interactive UPS, Tower, USB port

MODEL NUMBER: OMNISMART500



### Highlights

- 500VA tower 120V line-interactive UPS
- Corrects brownouts and overvoltages from 75V to 147V
- 3 UPS battery supported outlets, 3 surge-only outlets
- USB port, TEL/DSL protection, Front panel status LEDs
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets

### Package Includes

- OMNI SMART 500 UPS System
- USB and RJ11 Phone Cable
- Instruction manual with warranty information

### Features

- OMNISMART500 line interactive UPS system offers voltage regulation and battery support, plus complete AC and dialup/DSL line surge suppression
- Supports entry-level PC systems for up to 30 minutes during power failures to enable a safe system shutdown
- Supports a maximum load of 500VA/300 watts for 4 minutes and a half load of 250VA/150 watts for 14.6 minutes
- Automatic Voltage Regulation (AVR) circuits correct brownouts as low as 75 volts and overvoltages as high as 147 back to normal 120 volt levels without using battery power
- Attractive black tower configuration
- Includes 3 battery supported outlets, plus 3 additional surge suppression-only outlets, 6-ft. (1.83 m) AC line cord (all NEMA 5-15)
- USB port enables data-saving unattended shutdown when used with PowerAlert software, available via FREE download from [triplite.eaton.com/products/power-alert](http://triplite.eaton.com/products/power-alert)
- HID-compliant USB port also enables integration with built-in power management and auto shutdown features of Windows and macOS
- Supports WatchDog Service Monitoring/Rebooting Software (part# WATCHDOGSW)
- Dataline suppression jacks protect a single dialup phone/DSL line
- Audible alarm and 4 front panel LEDs indicate UPS system and line power status
- 500VA/300 watt power handling ability supports a variety of computer, internetworking, telecom and consumer electronics equipment
- Supports battery replacement via built-in access panel
- Compatible with 120V/60 Hz applications for USA, Canada, Mexico and more
- Optional PDUB15 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- Short circuit protection during AC and battery modes

### Specifications



Powering Business Worldwide

TRIPP LITE  
SERIES

OVERVIEW	
UPC Code	037332034137
UPS Type	Line-Interactive
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P; Right-Angled
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Maximum Input Amps	12
OUTPUT	
Output Capacity (VA)	500
Output Capacity (kVA)	0.5
Output Capacity (Watts)	300
Output Capacity (kW)	0.3
Nominal Voltage Details	115v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-18%, +8%
Output Voltage Regulation (Battery Mode)	+/- 5%
UPS Output Receptacles (Surge Suppression Only)	3 UPS outlets, 3 surge-only outlets
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(6) 5-15R
Individually Controllable Load Banks	No
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Runtime Full Load (min.)	4 min. (300W)



Powering Business Worldwide

TRIPP LITE  
SERIES

Runtime Half Load (min.)	14.6 min. (150W)
Expandable Runtime	No
DC System Voltage (VDC)	12
Battery Recharge Rate (Included Batteries)	Less than 3.6 hours from 10% to 90%
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	&nbsp;<a class="productLink" href="//tripplite.eaton.com/UPS-Replacement-Battery-Cartridge-Tripp-Lite-APC-Belkin-Best-Powerware-Liebert-other-UPS-RBC51">RBC51</a>&nbsp;
Battery Replacement Description	Hot-swappable, user replaceable batteries
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 75 to 147
Overvoltage Correction	Input voltages between 128 and 147 are reduced by 12%
Undervoltage Correction	Input voltages between 93 and 107 are boosted by 14%
Severe Undervoltage Correction	Input voltages between 75 and 92 are boosted by 30%
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions
LED Indicators	4 LEDs indicate line power, battery power, overload and battery low/replace status
<b>SURGE / NOISE SUPPRESSION</b>	
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	480
AC Suppression Response Time	Instantaneous
Dataline Suppression	1 line TEL / DSL or 10Base T Ethernet protection
<b>PHYSICAL</b>	
Primary Form Factor	Tower
Rack Height	0U
Installation Form Factors Supported with Included Accessories	Tower
Installation Form Factors Supported with Optional Accessories	Wallmount (&nbsp;<a class="productLink" href="//tripplite.eaton.com/Wall-Mount-Bracket-Installation-Accessories-for-UPS-Systems~UPSWM">UPSWM</a>&nbsp; - tower mounting kit)
Primary UPS Depth (mm)	178
Primary UPS Height (mm)	216
Primary UPS Width (mm)	127



Powering Business Worldwide

TRIPP LITE  
SERIES

Shipping Dimensions (hwd / in.)	9.20 x 7.80 x 12.20
Shipping Dimensions (hwd / cm)	23.37 x 19.81 x 30.99
Shipping Weight (lbs.)	14.10
Shipping Weight (kg)	6.40
UPS Housing Material	PVC
UPS Power Module Dimensions (hwd, cm)	21.59 x 12.70 x 17.78
UPS Power Module Dimensions (hwd, in.)	8.5 x 5 x 7
UPS Power Module Weight (kg)	5.44
UPS Power Module Weight (lbs.)	12
Unit Dimensions (hwd / in.)	8.500 x 5.000 x 7.000
Unit Weight (lbs.)	12.0000
Unit Weight (kg)	5.44
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0-95% non-condensing
AC Mode BTU / Hr. (Full Load)	53
AC Mode Efficiency Rating (100% Load)	95%
<b>COMMUNICATIONS</b>	
PowerAlert Software	For local monitoring via the UPS's built-in USB port, download PowerAlert software at <a href="https://tripplite.eaton.com/products/power-alert">https://tripplite.eaton.com/products/power-alert</a>
Communications Cable	USB cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network UPS Tools (NUT) Compatibility	NUT compatible. See a full list of NUT compatible Tripp Lite UPS systems at <a href="https://networkupstools.org/stable-hcl.html?manufacturer=Tripp%20Lite">https://networkupstools.org/stable-hcl.html?manufacturer=Tripp%20Lite</a>
Network Management Card Description	Network management not supported
Communications Interface	USB (HID enabled)
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	75
High Voltage Transfer to Battery Power (Setpoint)	147
<b>FEATURES &amp; SPECIFICATIONS</b>	



*Powering Business Worldwide*

TRIPP LITE  
SERIES

Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
<b>APPLICATIONS</b>	
UPS Applications	Home/Office Desktop; Retail/Point of Sale; Hospitality
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CSA (Canada); UL 1778
Product Compliance	RoHS; FCC Part 15 Class B (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.