

High Speed HDMI Cable with Ethernet, UHD 4K, Digital Video with Audio (M/M), 25 ft. (7.62 m)

MODEL NUMBER: **P569-025**



Highlights

- 25-ft. (7.62 m) High Speed with Ethernet HDMI cable
- Supports transmission speeds up to 18 Gbps
- Backward compatible to previous HDMI generations
- Video mirroring with iPad2

System Requirements

- HDMI video source and HDMI enabled TV / Monitor

Package Includes

25-ft. (7.62 m) High Speed with Ethernet HDMI Cable

Features

- 25-ft. (7.62 m) High Speed with Ethernet HDMI cable
- Supports transmission speeds up to 18 Gbps
- Backward compatible to previous HDMI generations
- Fully molded cables, with Gold plated connectors assures long life
- Perfect for connecting an iPad2 to an HDTV (video mirroring) to watch movies, play games, surf the web and display presentations

Specifications

| OVERVIEW | |
|--------------------------------|-------------------------|
| UPC Code | 037332160676 |
| Product Type | Passive Cable |
| Technology | HDMI |
| Cable Type | Passive |
| VIDEO | |
| Max Supported Video Resolution | 3840 x 2160 (4K) @ 30Hz |
| Max Supported Color Depth | 48-bit Deep Color |
| HDR Support | No |
| 3D Video Supported | Yes |
| Chroma Sub Sampling | 4:4:4 |
| EDID Support | Yes |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--|-----------------------------|
| Signal Transmission | Bidirectional |
| AUDIO | |
| Audio Specification | ARC |
| CONNECTIONS | |
| Side A - Connector 1 | HDMI (MALE) |
| Side B - Connector 1 | HDMI (MALE) |
| Connector Plating | Gold |
| Contact Plating | Gold |
| Connector Style | Straight |
| Latching or Gripping Connector | No |
| USER INTERFACE, ALERTS & CONTROLS | |
| LED Indicators | 0 |
| PHYSICAL | |
| Color | Black |
| Material of Construction | PVC |
| Cable Jacket Color | Black |
| Connector Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Cable Outer Diameter (OD) | 7.3 mm |
| Wire Gauge (AWG) | 28 |
| Cable Length (ft.) | 25 |
| Cable Length (m) | 7.62 |
| Cable Length (in.) | 300 |
| Ferrite Core | No |
| Minimum Bend Radius | 36.5mm |
| Shipping Dimensions (hwd / in.) | 12.00 x 10.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 30.48 x 25.40 x 1.27 |
| Shipping Weight (lbs.) | 1.22 |
| Shipping Weight (kg) | 0.55 |
| Unit Dimensions (hwd / in.) | 12.000 x 10.000 x 0.500 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 14° to 122°F (-10° to 50°C) |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--|------------------------------|
| Storage Temperature Range | 5° to 140°F (-15° to 60°C) |
| Operating Humidity Range | 0% to 90% RH, Non-Condensing |
| Storage Humidity Range | 0% to 90% RH, Non-Condensing |
| COMMUNICATIONS | |
| EDID Compatible | Yes |
| Consumer Electronics Control (CEC) Supported | Yes |
| FEATURES & SPECIFICATIONS | |
| EMI/RFI Line Noise Protection | No |
| MST Support | No |
| Antibacterial | No |
| IP68 Rated | No |
| IP20 Rated | No |
| Armored Cable | No |
| Ethernet Support | Yes |
| HDCP Specification | 1.4; 2.2 |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; REACH |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.