


## Rolling TV/Monitor Cart - for Flat/Curved 32" to 70" TVs and Monitors

MODEL NUMBER: **DMCS3270XP**



Height-adjustable mobile TV stand hangs a flat- or curved-panel television or monitor and peripherals, such as a Blu-ray player, laptop and webcam.

### Description

The DMCS3270XP Mobile TV Cart allows you to mount a flat- or curved-panel television, monitor or other display and move it from room to room for best viewing or against a wall out of the way when not in use. Recommended for classrooms, lecture halls, offices, auditoriums and conference rooms, the height-adjustable mobile stand fits most displays from 32 to 70 inches.

You can adjust this heavy-duty rolling TV stand's height from 47 to 81.5 inches. You can also rotate the display for viewing in portrait or landscape modes. Roll the unit with little effort to the proper viewing location and angle on sturdy three-inch swivel casters that move smoothly through doorways and over thresholds. All four casters lock to keep the stand securely in position.

A shelf mounted above the display holds projectors, webcams and laptops. A lower shelf supports up to 11 lbs (4.9 kgs) and holds other audio/video components, such as a Blu-ray player. Durable aluminum and steel construction supports up to 150 lbs (68 kgs). The adapter brackets can be adjusted to conform to VESA-compliant displays with any of the following mounting hole patterns: 200 x 200, 200 x 300, 200 x 400, 300 x 200, 300 x 300, 300 x 400, 400 x 200, 400 x 300, 400 x 400, 500 x 200, 500 x 300, 500 x 400, 600 x 300 and 600 x 400.

### Features

**Height Adjustable Display Stand Rolls from Room to Room**Mobile mount for flat/curved-panel TVs, monitors and other displaysRecommended for classrooms, lecture halls, offices, auditoriums and conference roomsFits most displays from 32 to 70 in.

**Flexible Features That Meet Your Specifications**Height adjusts from 47 to 81.5 in.Rotates for viewing in portrait or landscape modes

**Rolls on Sturdy Metal Casters**3 in. swivel casters move smoothly through doorways and over thresholdsAll casters lock to hold stand securely in position while at rest

**Durable Construction**Made from aluminum and steelUpper shelf holds projectors, webcams and laptopsLower shelf holds A/V components, such as Blu-ray playerSupports up to 150 lbs (68 kgs) Laptop shelf holds up to 11 lbs (4.9 kgs)

**VESA Compliance**Supports the following VESA mounting hole patterns: 200 x 200, 200 x 300, 200 x 400, 300 x 200, 300 x 300, 300 x 400, 400 x 200, 400 x 300, 400 x 400, 500 x 200, 500 x 300, 500 x 400, 600 x 300 and 600 x 400

### Highlights

- Fits most flat or curved panel displays from 32 to 70 in.
- Designed for portrait or landscape mounting
- Height adjusts from 47 to 81.5 in.
- Locking 3 in. swivel casters for easy movement
- Supports up to 150 lbs (68 kgs) Laptop shelf holds up to 11 lbs (4.9 kgs)

### Package Includes

- Middle base
- Left leg
- Right leg
- Left cover
- Right cover
- Support plate
- Universal plate
- (2) Plastic covers
- (2) Adapter brackets
- Column
- Plastic handle
- Top cover
- Connecting plate
- Camera shelf
- DVD shelf
- (8) Washers
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M8 x 20 screws
- (4) M6 x 30 screws
- (4) M8 x 30 screws
- (4) M8 x 50 screws
- (8) M6 x 16 screws
- (3) M6 x 25 screws
- (7) M4 x 6 screws
- (2) M6 x 14 screws
- (6) M6 x 8 screws
- (4) M8 x 25 screws
- (2) M5 x 8 screws
- (8) Small spacers
- (8) Big spacers
- Allen wrench

- Wrench
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332203328
Device Compatibility	Monitor/HDTV; Projector
PHYSICAL	
Color	Black; Silver
Material of Construction	Aluminum, Steel
VESA Pattern (mm)	200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400; 500x200; 500x300; 500x400; 600x300; 600x400
Motion	Full
Mounting Location	Floor
Degrees of Motion	360° Rotate
Minimum Screen Size (in.)	32
Minimum Screen Size (cm)	81.28
Maximum Screen Size (in.)	70
Maximum Screen Size (cm)	177.8
Maximum Weight Capacity (lbs.)	150
Maximum Weight Capacity (kg)	68
Number of Displays	1
Shipping Dimensions (hwd / in.)	9.65 x 20.87 x 44.72
Shipping Dimensions (hwd / cm)	24.51 x 53.01 x 113.59
Shipping Weight (lbs.)	59.00
Shipping Weight (kg)	26.76
Unit Dimensions (hwd / in.)	81.500 x 32.600 x 27.600
Unit Weight (lbs.)	46.2
Unit Weight (kg)	20.96
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes



*Powering Business Worldwide*

TRIPP LITE  
SERIES

Security Lock	No
Built-in Cable Management	No
Pre-Installed Casters	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.