


Pop-Out Video Wall Mount w/Security for 45" to 70" TVs and Monitors - Flat Screens, UL Certified

MODEL NUMBER: **DMVWSC4570XUL**



Pop-out wall mount supports use of 45" to 70" flat screen TVs or monitors in video walls. Included lock deters theft.

Features

Pop-Out Display Mount is Designed for Video Wall Installations A pop-out feature and micro-adjustability make the DMVWSC4570XUL landscape wall mount a purpose-built solution for video walls in home theaters, offices, conference centers, medical facilities, airports, hotels, bars, restaurants and security stations. Designed for use with flat screens from 45 to 70 inches, this wall mount is function- and weight-tested to 154 pounds (69.8 kilograms) in accordance with UL Standard 2442.

Pop-Out Feature Supports Convenient Cable Access and Screen Adjustments To unlock the pop-out mechanism, press lightly on the front of your display and pull it toward you. It can extend anywhere from 3.7 to 11 inches from the wall, providing space to access cables or make adjustments. This is especially helpful in video wall installations, where adjacent screens may limit access. The extension also makes it easier to replace a display.

Multi-Directional Micro-Adjustments Provide Exact Alignment You can move the display left or right, adjust the screen level from -3° to +3° and adjust the tilt from -2° to +4°. For exact positioning in a video wall, there are six micro-adjustments for tilt, height and depth (user-supplied hex key required). When the display is in the perfect position, insert the included plastic locks in the brackets to prevent unintentional movement.

Included Combination Lock Deters Display Theft A three-position combination lock (included) secures the display bracket to the wall plate to deter theft, which can be a concern in public areas with unguarded traffic. Deterring display theft also protects the mount, which is often damaged beyond repair when a display is stolen. The heavy-duty steel frame withstands the stress of frequent adjustments, and the black powder-coated finish offers durability and scratch resistance. Your display hides the mount and the padlock, maintaining a professional look.

VESA-Compliant Mounting Ensures Display Compatibility VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this mount supports the following VESA mounting hole patterns: 200 x 200, 200 x 300, 200 x 400, 300 x 200, 300 x 300, 300 x 400, 400 x 200, 400 x 300, 400 x 400, 500 x 200, 500 x 300, 500 x 400, 600 x 300 and 600 x 400. Mounting hardware is included.

Highlights

- Accommodates most landscape displays with flat screens from 45 to 70 in.
- Pop-out design provides access for adjustments during installation and maintenance
- Micro-adjustments allow creation of a uniform look in a video wall
- Combination lock secures brackets to help deter theft of your display
- Function- and weight-tested up to 154 lb. in accordance with UL Standard 2442

Applications

- Group multiple landscape mounts to create a large video wall for digital signage in a lobby, conference room, bar or restaurant
- Deter theft of displays in a video wall located in a hotel, library or other public area
- Adjust a screen in a video wall without disturbing other displays

Package Includes

- All DMVWSC4570XUL components (some assembly required)
- Assembly and mounting fasteners
- Display mounting fasteners
- Three-position combination lock
- Owner's manual

Specifications



Powering Business Worldwide

TRIPP LITE
SERIES

OVERVIEW	
UPC Code	037332240545
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400; 500x200; 500x300; 500x400; 600x300; 600x400
Motion	Fixed
Mounting Location	Wall
Minimum Screen Size (in.)	45
Minimum Screen Size (cm)	114.3
Maximum Screen Size (in.)	70
Maximum Screen Size (cm)	177.8
Maximum Weight Capacity (lbs.)	154
Maximum Weight Capacity (kg)	70
Min/Max Arm Extension (in.)	3.7 min to 11.2 max
Min/Max Arm Extension (cm)	9.4 min to 28.4 max
Number of Displays	1
Shipping Dimensions (hwd / in.)	5.40 x 10.70 x 29.50
Shipping Dimensions (hwd / cm)	13.72 x 27.18 x 74.93
Shipping Weight (lbs.)	24.80
Shipping Weight (kg)	11.25
Unit Dimensions (hwd / in.)	26.400 x 11.200 x 20.600
Unit Dimensions (hwd / cm)	67.6 x 28.45 x 52.32
Unit Weight (lbs.)	25.1
Unit Weight (kg)	11.39
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	Yes
STANDARDS & COMPLIANCE	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Certifications	UL 2442
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.