


## DisplayPort Cable with Latching Connectors (M/M), 8K 60 Hz, HDR, HBR3, 4:4:4, HDCP 2.2, 20 ft. (6.1 m), Black

MODEL NUMBER: **P580-020-8K6**



8K DisplayPort cable connects your source and display devices to transmit enhanced 8K Ultra HD audio/video with HDR and 4:4:4 chroma.

### Features

#### DisplayPort 1.4 Cable Gets Your Gaming, Home Theater or Digital Signage Setup 8K-Ready

This high-speed DisplayPort (DP) cable (M/M) securely connects source and display devices compatible with DP 1.4 audio/video signals. Backward compatible with all your existing DisplayPort devices, including Blu-ray players, game consoles and 4K televisions, the P580-020-8K6 is ideal for future-proofing your high-definition or Ultra HD application in anticipation of an 8K upgrade.

#### Enjoy the Clarity of 4K/8K Video with Multi-Channel Audio and 4:4:4 Color

The P580-020-8K6 supports 8K Ultra HD resolutions up to 7680 x 4320 at 60 Hz with multi-channel sound. It's compatible with DisplayPort 1.4 standards for HDR, providing a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks. HDCP 2.2 compliance allows you to stream 4K content with no complications. This BT.2020-compatible cable also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

#### Invest in Quality Construction for Reliable Performance

You're expecting this 8K cable to last a long time, which is why it has been constructed with high-quality materials, such as a rugged PVC jacket. Contacts and connectors are gold-plated to resist corrosion. The male connectors latch securely to help prevent the cable from becoming accidentally disconnected and disrupting a continuous audio/video signal. Double shielding reduces line noise (EMI/RFI) that can disrupt signals traveling through the DisplayPort cord.

## Specifications

OVERVIEW	
UPC Code	037332290953
Product Type	Passive Cable
Technology	DisplayPort

### Highlights

- Supports UHD resolutions up to 8K @ 60 Hz (4:4:4) for state-of-the-art video quality
- Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy
- Complies with HDCP 2.2 standards to display up-to-date 8K video content
- Plug-and-play operation with no software required for easy, immediate installation

### System Requirements

Both source and display devices must be compatible with 8K standards to watch 8K video

### Package Includes

P580-020-8K6 DisplayPort Cable (M/M), 8K 60 Hz, 20 ft. (6.1 m)



Powering Business Worldwide

TRIPP LITE  
SERIES

Cable Type	Passive
<strong>VIDEO</strong>	
Video Input	DISPLAYPORT (MALE)
Video Output	DISPLAYPORT (MALE)
Max Supported Video Resolution	7680 x 4320 (8K) @ 60Hz
Max Supported Color Depth	24-bit True Color
HDR Support	Yes
3D Video Supported	No
Chroma Sub Sampling	4:4:4
Signal Transmission	Bidirectional
Bandwidth	32.4 Gbps
DisplayPort Alt Mode	No
<strong>CONNECTIONS</strong>	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DISPLAYPORT (MALE)
Connector Plating	Gold
Contact Plating	Gold
Connector Style	Straight
Latching or Gripping Connector	Yes
<strong>PHYSICAL</strong>	
Color	Black
Material of Construction	PVC
Cable Jacket Color	Black
Connector Color	Blue
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	7.3MM
Wire Gauge (AWG)	26
Cable Length (ft.)	20
Cable Length (m)	6.10
Cable Length (in.)	240
Shipping Dimensions (hwd / in.)	17.00 x 14.00 x 0.50
Shipping Weight (kg)	0.39
Unit Dimensions (hwd / in.)	17.000 x 14.000 x 0.500
Unit Packaging Type	Polybag



Powering Business Worldwide

TRIPP LITE  
SERIES

Unit Weight (lbs.)	0.86
Unit Weight (kg)	0.39
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% TO 90% RH, NON-CONDENSING
Storage Humidity Range	0% TO 90% RH, NON-CONDENSING
<b>COMMUNICATIONS</b>	
EDID Compatible	No
Consumer Electronics Control (CEC) Supported	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
EMI/RFI Line Noise Protection	No
Integrated/Removable Cable	No
MST Support	No
Antibacterial	No
Fully Molded Connector Ends	No
Ohms	No
Integral Strain Relief	No
Impedance-Matched Twisted-Pair Construction	No
Scaler Function	No
IP67 Rated	No
Armored Cable	No
Displayport Specification	1.4
HDCP Specification	2.2
Driver Required	No
DIN Mountable	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	CE (Europe); RoHS; UKCA; WEEE
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

TRIPP LITE  
SERIES

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.