

## Swivel/Tilt Wall Mount for 37" to 70" TVs and Monitors

MODEL NUMBER: **DWM3770X**



Hangs a flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants. Swivels and tilts to provide optimal viewing angles.

### Description

The VESA-compliant DWM3770X Swivel/Tilt Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants, it fits most flat-panel displays from 37 to 70 inches.

The articulating arm has six pivots that adjust independently for angle to give you maximum flexibility in positioning your display to fit your environment and comfort level. A 120° swivel, -15° to +15° tilt and -3° to +3° screen level adjustment capability minimizes glare and provides comfortable viewing from multiple angles.

Durable all-metal frame with scratch-resistant powder-coated finish supports up to 165 lbs (74.8 kgs). Mounting hardware included. Built-in bubble level allows accurate display leveling. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 100 x 100 mm, 100 x 200 mm, 200 x 100 mm, 200 x 200 mm, 200 x 300 mm, 200 x 400 mm, 300 x 200 mm, 300 x 300 mm, 300 x 400 mm, 400 x 200 mm, 400 x 300 mm, 400 x 400 mm, 500 x 200 mm, 500 x 300 mm, 500 x 400 mm, 600 x 300 mm and 600 x 400 mm

### Features

**Mounts Your TV or Monitor to the Wall!** Fits most flat-panel televisions, monitors and other displays from 37 to 70 in. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants. Articulated arm with 6 pivots adjusts independently for angle. Mounting hardware included.

**Convenient One-Touch Adjustment** 120° swivel, -15° to +15° tilt and -3° to +3° screen level adjustment capability provides comfortable viewing from multiple angles.

**Durable Metal Construction** Supports up to 165 lbs (74.8 kgs). Scratch-resistant powder-coated finish blends with any décor. Built-in bubble level allows accurate display leveling.

**VESA Compliance** Supports the following VESA mounting hole patterns: 100 x 100 mm, 100 x 200 mm, 200 x 100 mm, 200 x 200 mm, 200 x 300 mm, 200 x 400 mm, 300 x 200 mm, 300 x 300 mm, 300 x 400 mm, 400 x 200 mm, 400 x 300 mm, 400 x 400 mm, 500 x 200 mm, 500 x 300 mm, 500 x 400 mm, 600 x 300 mm and 600 x 400 mm

### Highlights

- Fits most flat-panel displays from 37 to 70 in.
- One-touch adjustment for comfortable viewing
- 120° swivel, -15° to +15° tilt and -3° to +3° screen adjustment
- Supports up to 165 lbs (74.8 kgs)

### Package Includes

- Wall mount
- Mounting template
- (2) Adapter brackets
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 20 screws
- (4) M8 x 30 screws
- (4) Washers
- (8) Small spacers
- (4) Big spacers
- (6) Anchor bolts
- (6) Concrete anchors
- (6) D6 washers
- Owner's manual

## Specifications



Powering Business Worldwide

TRIPP LITE  
SERIES

OVERVIEW	
UPC Code	037332187437
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	100x100; 100x200; 200x100; 200x200; 200x300; 200x400; 300x200; 300x300; 300x400; 400x200; 400x300; 400x400; 500x200; 500x300; 500x400; 600x300; 600x400
Motion	Full
Mounting Location	Wall
Degrees of Motion	-15/+15 Tilt; 120 Swivel; -3/+3 Level Adjustment
Minimum Screen Size (in.)	37
Minimum Screen Size (cm)	93.98
Maximum Screen Size (in.)	70
Maximum Screen Size (cm)	177.8
Maximum Weight Capacity (lbs.)	165
Maximum Weight Capacity (kg)	75
Min/Max Arm Extension (in.)	4.57 min to 20.63 max
Min/Max Arm Extension (cm)	116 (.) 524 (.)
Number of Displays	1
Shipping Dimensions (hwd / in.)	4.40 x 9.50 x 27.90
Shipping Dimensions (hwd / cm)	11.18 x 24.13 x 70.87
Shipping Weight (lbs.)	20.60
Shipping Weight (kg)	9.34
Unit Dimensions (hwd / in.)	17.320 x 23.620 x 20.620
Unit Dimensions (hwd / cm)	44.0 x 60.1 x 52.4
Unit Weight (lbs.)	17.38
Unit Weight (kg)	7.88
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No



*Powering Business Worldwide*

TRIPP LITE  
SERIES

**STANDARDS & COMPLIANCE**

Product Compliance	RoHS; RoHS3; REACH
--------------------	--------------------

**WARRANTY & SUPPORT**

Product Warranty Period (Worldwide)	5-year limited warranty
-------------------------------------	-------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.