

## 5.5kW Single-Phase Local Metered PDU, 208/230V Outlets (16 C13 & 2 C19), L6-30P, 12 ft. (3.66 m) Cord, 2U Rack-Mount, TAA

MODEL NUMBER: PDUMH30HV



### Highlights

- Local metered single phase 24A 208/230V 2U horizontal rackmount PDU
- Two built-in meters report output current in amps for each load bank
- Attached 12 ft. (3.7 m) cord with NEMA L6-30P input plug
- 18 total outlets (16 C13, 2 C19); Compatible with Eaton Tripp Lite power cords
- Reversible housing, 2U 208/230V rackmount local metered PDU
- TAA Compliant

### Package Includes

- 2U rack PDU
- Mounting brackets
- Plug retention plates
- User manual

### Features

- 30A single phase 208/230V Local Metered Power Distribution Unit / rack PDU (rPDU) (Agency derated to 24A continuous)
- Set of two lighted meters report PDU output current in amps for each 9 outlet load bank
- Attached NEMA L6-30P 30A 208/230V input plug and 12-ft. (3.66 m) cord
- 2U horizontal rackmount format installs in two rack spaces
- 18 output receptacles (16 C13, 2 C19)
- Outlets are arranged in two 9 outlet load banks, each with separate 20A breaker and current metering
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Mounting ears are reversible for front or rear facing rackmount installation
- Cord retention brackets keep vital equipment plugs connected
- Grounding lug
- Compliant with the Federal Trade Agreements Act(TAA) for GSA Schedule purchases

### Specifications

OVERVIEW	
UPC Code	037332159021
PDU Type	Local Metered
INPUT	
Input Phase	Single-Phase
PDU Input Voltage	208; 230



Powering Business Worldwide

TRIPP LITE  
SERIES

Recommended Electrical Service	Single-phase 30A 208/230V service
Maximum Input Amps	24
Maximum Input Amps Details	Agency de-rated to 24A continuous
PDU Plug Type	NEMA L6-30P
Input Cord Length (ft.)	12
Input Cord Length (m)	3.66
<b>OUTPUT</b>	
Output Capacity Details	5.5kW (230V), 5kW (208V) total capacity / 30A max (Agency de-rated to 24A), 20A max per breaker outlet bank; 16A max per C19 outlet; 12A max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacle Details	Compatible with Eaton Tripp Lite Power Cords
Output Receptacles	(16) C13; (2) C19
Output Nominal Voltage	208/230V
Overload Protection	Two 20A breakers protect 9 outlets each
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Set of 2 digital meters continuously report output current for breaker load banks 1 & 2 (Bank 1: upper row of 9 outlets / Bank 2: lower row of 9 outlets)
<b>SURGE / NOISE SUPPRESSION</b>	
Automatic Shut-Off	No
<b>PHYSICAL</b>	
Material of Construction	Metal
Rack Height	2U
Form Factors Supported	2U rackmount; mounting accessories included
Minimum Required Rack Depth (cm)	40.64
Minimum Required Rack Depth (inches)	16
PDU Form Factor	Horizontal (2U)
Shipping Dimensions (hwd / in.)	7.80 x 16.70 x 19.80
Shipping Dimensions (hwd / cm)	19.81 x 42.42 x 50.29
Shipping Weight (lbs.)	15.80
Shipping Weight (kg)	7.17
Unit Dimensions (hwd / in.)	3.500 x 17.500 x 12.500
Unit Dimensions (hwd / cm)	8.8 x 44.4 x 31.8
Unit Weight (lbs.)	13.7
Unit Weight (kg)	6.21



*Powering Business Worldwide*

TRIPP LITE  
SERIES

ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-22° to 122°F (-30° to 50°C)
Relative Humidity	5% to 95% non-condensing
Operating Elevation	0-10000 ft. (0-3000 m)
FEATURES & SPECIFICATIONS	
Grounding	Grounding lug
STANDARDS & COMPLIANCE	
Product Certifications	NOM (Mexico); UL 62368-1
Product Compliance	RoHS; FCC Part 15 Class A (USA); UKCA; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.