

# Specifications

Photo is representative

## Eaton 1164B-200

Eaton 60 Series Photoelectric Sensor Head, Photoelectric, 1.25 diameter, Forward Viewing, Sensor distance: 159 Ft., Aluminum enclosure, Thu-Beam, 9 Ft. ( 2.7m )

### General specifications

<b>PRODUCT NAME</b>	Eaton 60 series photoelectric sensor
<b>CATALOG NUMBER</b>	1164B-200
<b>UPC</b>	782113819631
<b>PRODUCT LENGTH/DEPTH</b>	1.13 in
<b>PRODUCT HEIGHT</b>	4 in
<b>PRODUCT WIDTH</b>	1.13 in
<b>PRODUCT WEIGHT</b>	0.5 lb
<b>WARRANTY</b>	3 year
<b>COMPLIANCES</b>	Contact Manufacturer

## Product specifications

<b>CABLE TYPE</b>	Polyvinyl Chloride (PVC)
<b>ENCLOSURE MATERIAL</b>	Aluminum
<b>OPERATING MODE</b>	Thru-beam
<b>SENSOR TYPE</b>	Through beam
<b>SWITCH TYPE</b>	Photoelectric
<b>CORD LENGTH</b>	108 ft
<b>OPERATING TEMPERATURE - MAX</b>	158 °F
<b>OPERATING TEMPERATURE - MIN</b>	-40 °F
<b>ENVIRONMENTAL RATING</b>	NEMA 3, NEMA 4, NEMA 6, NEMA 12, NEMA 13

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - 1164B-200](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

