


## SmartRack 21U Low-Profile Switch-Depth Wall-Mount Half-Height Rack Enclosure, Clear Acrylic Window

MODEL NUMBER: **SRW21UG**



Wall-mount cabinet secures and organizes 21U of 19-inch rack equipment in network closets, classrooms and other locations with limited floor space. Clear acrylic window allows you to monitor equipment without unlocking door.

### Description

The SRW21UG SmartRack® 21U Low-Profile Switch-Depth Wall-Mount Rack Enclosure Cabinet is ideal for storing EIA-standard 19-inch rack equipment in network closets, retail locations, classrooms and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 200 pounds (90.7 kilograms).

The front door features a shatter-resistant clear acrylic window that lets you monitor equipment without unlocking the enclosure. Not only does the window help prevent equipment tampering and reduce acoustic noise, but it also adds visual flair to your IT installation.

To ensure your valuable equipment stays secure, the side panels and front door lock. The top, bottom and removable side panels are vented, which allows air to flow freely through the cabinet to keep equipment cool. The reversible front door can open left or right by rotating the cabinet 180 degrees before mounting. Convenient top and bottom ports allow easy cable routing through the cabinet.

The SRW21UG comes fully assembled and ready to mount to the wall or use the optional SRCASTER caster kit (sold separately) to make it a mobile rolling rack. Square and 12-24 threaded mounting holes and numbered rack spaces make equipment installation easy. The vertical mounting rails adjust in 7/8-inch increments to accommodate equipment up to 16.5 inches deep, such as network switches and patch panels.

### Features

#### Saves Valuable Workspace

- Perfect for network closets, retail locations, classrooms and other areas with limited floor space where you need equipment to be secure, organized and out of the way
- Houses EIA-standard 19 in. rack equipment in 21U of space
- Maximum load capacity of 200 pounds (90.7 kg)

#### Shatter-Resistant Clear Acrylic Front Window

- Lets you monitor equipment without unlocking the enclosure
- Prevents equipment tampering
- Reduces acoustic noise

### Highlights

- Maximum load capacity of 200 lbs (90.7 kgs)
- Front door includes shatter-resistant clear acrylic window
- Locking steel cabinet vented at sides, top and bottom
- Secures 21U of 19 in. rack equipment up to 16.5 in. deep
- Mounts to wall or rolls on floor (with optional SRCASTER)

### Package Includes

- SRW21UG SmartRack 21U Low-Profile Switch-Depth Wall-Mount Rack Enclosure Cabinet
- (44) M6 screws
- (44) M6 cage nuts
- (44) M6 cup washers
- (44) 12-24 screws
- Removable mounting plate
- (3) Mounting plate screws
- (2) Keys
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

- Provides extra visual flair

#### Keeps Important Equipment Secure

- Side panels and front door lock securely
- Vented panels allow generous airflow that keeps equipment cool
- Rotate cabinet 180° before mounting to open reversible front door left or right
- Convenient ports with removable covers allow cable routing through top and bottom

#### Easy Enclosure and Equipment Installation

- Ships fully assembled for quick installation
- Mounts to wall or rolls on floor with optional SRCASTER caster kit
- Wall-mounting holes spaced 16 in. apart to accommodate standard wall stud placement
- Vertical mounting rails adjust in 7/8 in. increments to house equipment up to 16.5 in. deep
- Rails support square-hole or 12-24 threaded-hole mounting
- Rack spaces numbered for easy reference

#### Meets Payment Card Industry Standards

- Provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

## Specifications

| OVERVIEW                               |                                  |
|----------------------------------------|----------------------------------|
| UPC Code                               | 037332187338                     |
| Device Compatibility                   | Patch Panel; Network Switch; UPS |
| Rack Type                              | Half-Height Enclosure            |
| PHYSICAL                               |                                  |
| Color                                  | Black                            |
| Rack Height                            | 21U                              |
| Rack Depth                             | Shallow                          |
| Maximum Device Depth (cm)              | 41.91                            |
| Maximum Device Depth (in.)             | 16.5                             |
| Maximum Device Depth (mm)              | 419                              |
| Minimum Device Depth (cm)              | 7.62                             |
| Minimum Device Depth (in.)             | 3                                |
| Minimum Device Depth (mm)              | 76                               |
| Cable Access Hole Measurement (inches) | 9.812 x 2.35 (l x w)             |
| Shipping Dimensions (hwd / in.)        | 46.10 x 18.70 x 24.50            |
| Shipping Dimensions (hwd / cm)         | 117.09 x 47.50 x 62.23           |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                            |
|--------------------------------------|----------------------------|
| Shipping Weight (lbs.)               | 68.00                      |
| Shipping Weight (kg)                 | 30.84                      |
| Unit Dimensions (hwd / in.)          | 40.870 x 23.630 x 17.720   |
| Unit Dimensions (hwd / cm)           | 103.81 x 60.02 x 45.01     |
| Unit Weight (lbs.)                   | 51.2                       |
| Unit Weight (kg)                     | 23.22                      |
| Weight Capacity - Stationary (kg)    | 91                         |
| Weight Capacity - Stationary (lbs.)  | 200                        |
| Number of Vertical Mounting Rails    | 2                          |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                            |
| Grounding Details                    | Front and Back door frames |
| Pre-Installed Casters                | No                         |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                            |
| Product Certifications               | UL 60950-1                 |
| Product Compliance                   | RoHS; EIA/ECA-310-E; UKCA  |
| <b>WARRANTY &amp; SUPPORT</b>        |                            |
| Product Warranty Period (Worldwide)  | 5-year limited warranty    |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.