



10-Port USB 2.0 Hub, Black

MODEL NUMBER: **U223-010**

Description

The U223-010 10-port USB 2.0 hub allows you to connect up to ten USB devices to a single USB port on your computer. This unit meets or exceeds USB 2.0 specifications for data transmission rates up to 480 Mbps. While the hub will function in virtually all cases without needing external power, a compact, multi-voltage AC adapter (100-240V) has been provided for the rare circumstance when connecting a power-hungry device. This device is backwards compatible with both USB 2.0 and USB 1.1 devices. Over-current protection safeguards connected equipment from over voltages.

Features

- USB 2.0 10-Port Hub
- Supports data transfer rates up to 480Mbps
- Connect up to 10 USB devices to a single USB port on your computer
- Compact design is ideal for use with a laptop/notebook computer
- Does not require external power, software, or complicated set-up procedures
- Plug-and-play/hot-swappable allows you to add or remove a device at any time
- Per-port overcurrent protection
- Bus-powered or self-powered
- Supports USB 2.0 spec up to 500mA per port
- On bus-power, 500mA from the USB 2.0 computer port is shared between the hub ports
- The included external power supply provides 4A of power, to be shared between the hub ports (up to 500mA per port)
- Compact, multi-voltage power supply (100-240V) provided
- Compatible with all major operating systems

Specifications

OVERVIEW	
UPC Code	037332185396
Product Type	Hub

Highlights

- Connects up to 10 USB 2.0 devices
- Bus powered or optional AC adapter
- Compatible with all major operating systems

System Requirements

- USB 2.0 Computer Port
- USB Peripherals

Package Includes

- U223-010 USB 2.0 Hub
- User's Manual
- USB 2.0 Mini B male to USB 2.0 A male cable
- External Power Supply with NEMA 1-15P Plug (Input: AC100-240V, 50/60Hz, 1.5A; Output: 5V, 4A)



Powering Business Worldwide

TRIPP LITE
SERIES

Technology	USB 2.0 (High Speed)
Host Connector	USB A (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DisplayPort Alt Mode	No
DATA	
Data Ports	(10) USB A (FEMALE)
Data Ports Details	(10) USB-A - USB 2.0
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.9A
AC Power Adapter Output Specs (V / A)	5V / 4A
AC Power Adapter Cord Length (ft.)	4
AC Power Adapter Cord Length (m)	1.2
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
Bus Powered	No
Product Length (in.)	8.6
Product Length (cm.)	21.84
Product Length (ft.)	0.72
Product Length (m)	0.22
POWER	
Power Source Type	AC Adapter
DC Barrel Plug	OD: 3.5 x 1.35 x 8mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	0.55
CONNECTIONS	
Number of Ports	10
Side A - Connector 1	USB A (FEMALE)
Side B - Connector 1	(10) USB A (FEMALE)
Connector Plating	Nickel



Powering Business Worldwide

TRIPP LITE
SERIES

USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (Power)
PHYSICAL	
Color	Black
Material of Construction	ABS
Shipping Dimensions (hwd / in.)	2.20 x 3.20 x 9.10
Shipping Weight (lbs.)	0.70
Unit Dimensions (hwd / in.)	0.600 x 8.600 x 1.300
Unit Dimensions (hwd / cm)	21.84 x 1.52 x 3.3
Unit Packaging Type	Box
Unit Weight (lbs.)	0.2
Unit Weight (kg)	0.09
ENVIRONMENTAL	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	14° to 194°F (-10° to 90°C)
Relative Humidity	10% to 90 % RH, Non-Condensing
BTUs	1.9 BTU/Hr
Power Provided to Connected Device(s)	5V 0.5A (2.5W) Output per USB port
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	10
USB Specification	USB 2.0 (up to 480 Mbps)
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
External Power Supply Certifications	DOE; FCC; UL
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

TRIPP LITE
SERIES

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.