

## Device Drivers

A driver CD-ROM is no longer included with this product. The latest drivers for Windows, macOS, Android, Chrome OS and Ubuntu are available from the DisplayLink website. Please visit <https://www.displaylink.com/downloads>.

## USB to DVI Dual-Display External Video Graphics Card Adapter - USB 3.2 Gen 1, VGA Adapter, 512 MB SDRAM, 1080p

MODEL NUMBER: U344-001-R



Adds a DVI-enabled monitor, television or projector to your computer or laptop's USB-A port.

## Features

### Connects a Larger Display to Your Notebook or Laptop Computer

This external video adapter allows you to reproduce the image on your laptop screen on a larger display. Just connect the U344-001-R's detachable USB cable to your computer's USB port, and connect the adapter's DVI port to a DVI-enabled monitor, HDTV or projector with a user-supplied DVI cable (sold separately). A DVI-to-VGA adapter is included for connecting the adapter to a display's VGA port.

### Swap Video to a Second Display Without the Hassle of Function Keys

You can extend video across both screens, do multiple presentations from a single computer, or play video on one display while working on another. You can use up to six U344-001-R adapters at the same time, adding as many as six additional displays and extending a video signal across all of them.

### Supports High-Definition 1080p Video

The U344-001-R supports HD video resolutions up to 2048 x 1152, including 1080p, at 60 Hz. Featuring 512 MB DDR2 SDRAM of memory, the plug-and-play adapter is bus-powered, so no external power adapter is required. It supports USB 3.2 Gen 1 data transfer rates up to 5 Gbps, and is backward compatible with USB 2.0.

### Broadly Compatible with Most Major Operating Systems

The U344-001-R works with Windows 7 and later (32- and 64-bit), Intel Mac OS X 10.8.5 and later, Mac 10.11 (32- and 64-bit), and Surface tablets running non-RT Windows 8, 8.1 and 10. Check the owner's manual for system requirements when using multiple adapters or using the add-on monitor for DVD playback.

## Highlights

- Supports USB 3.2 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Supports high-definition video resolutions up to 2048 x 1152 @ 60 Hz
- Connect up to 6 adapters at the same time to extend video across multiple displays
- Plug-and-play operation with no external power required for immediate installation
- Compatible with both Windows and macOS operating systems

## System Requirements

- Compatible with Windows 7 and later. Supports both 32- and 64-bit.
- Supports Surface tablets running non-RT Windows 8, 8.1 and 10.
- Supports Google Chromebook R51 and later.
- Compatible with Intel Mac OS X 10.8.5 and later, Mac 10.11. Supports both 32- and 64-bit.
- Reference the owner's manual for system requirements when using multiple adapters or when using the add-on monitor for DVD playback.

## Package Includes

- U344-001-R USB to DVI Dual-Display External Video Graphics Card Adapter
- Detachable USB-B to USB-A cable
- DVI to VGA adapter
- Owner's manual

## Specifications



*Powering Business Worldwide*

TRIPP LITE  
SERIES

OVERVIEW	
UPC Code	037332174215
Technology	DVI; VGA/SVGA
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	DVI-I (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	4.40 x 4.30 x 1.80
Shipping Dimensions (hwd / cm)	11.18 x 10.92 x 4.57
Shipping Weight (lbs.)	0.37
Shipping Weight (kg)	0.17
Unit Dimensions (hwd / in.)	0.812 x 1.875 x 3.750
Unit Dimensions (hwd / cm)	na
STANDARDS & COMPLIANCE	
Product Certifications	EN 55032; EN 55035
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.