



6	PIN	1	Be Cu	GOLD
5	INSULATOR	1	TEFLON	NONE
4	BODY	1	BRASS	GOLD
3	WASHER	2	Be Cu	None
2	GASKET	2	SILICONE	NONE
1	SHELL	2	Brass	GOLD
NO	Description	Q'ty	Material	Finish

UNLESS OTHERWISE SPECIFIED  
1.REMOVE ALL BURRS.  
2.BREAK ALL CONNERS &  
EDGES CO.15 MAX.  
3.CHAMFER 1ST & LAST  
THREADS 45°.  
4.DIAMETERS ON COMMON  
CENTERS.  
TO BE CONCENTRIC  
WITHIN 0.1 T.I.R.  
5.ALL DIMENSIONS ARE  
AFTER PLATING.

\* MAJOR DIMENSION  
UNLESS OTHERWISE  
NOTED TOLERANCES  
0.5-6=±0.2  
6-30=±0.4  
30-120=±0.6  
120-315=±1.0  
ANGLES=±1°  
SCALE 3/1 UNIT MM

APPROVED  
HF  
CHECKED  
HF  
Andrew

**Siretta**  
Enabling Industrial IoT  
TITLE  
SMA MALE TO REVERSE POLARITY SMA MALE  
DRAWING NO.  
ADAPT/SMAM/SMAM/RP