




REV.	DATE	ECR NO.	DESCRIPTION
NC	03/13/00	—	INITIAL RELEASE
A	02/25/08	—	UPDATE DRAWING FORMAT
B	12/07/08	—	ADD CRIMP NOTES/ REMOVE "BULKHEAD" FROM PART DESCRIPTION



RECOMMENDED CABLE
STRIPPING DIM'S



NOTES:

1. CRIMPED FERRULE HEX CRIMP SIZE .151" [3.83]
2. CONTACT PIN TO SOLDER.

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex					
8					DRAWN	G.R.S.	12/07/08							
7					CHECKED									
6									PART DESCRIPTION F CRIMP JACK (FOR RG-179 DOUBLE BRAID CABLE)					
5	FERRULE	BRASS	TIN LEAD		1	ISSUED								
4	INSULATOR	P.P.	NATURAL		1				PART NO. 222167					
3	CONTACT PIN	BER. COPPER	BRT. TIN		1	SHEET	1 OF 1							
2	INSULATOR	P.P.	NATURAL		1				DWG. NO. 222167.DWG					
1	BODY	BRASS	TIN LEAD	1										
DESCRIPTION				MATERIAL	FINISH	QTY	C:/222/222167.DWG		REV.	B	SIZE	A	SCALE	NA