




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED
A	NEW RELEASE		12/Nov./09	
A1	ADD LENGTH 1.25FT.		16/Sept./10	
A2	Revised DWG NO.		01/Nov/2019	



NOTES:

1. CABLE:[26AWG(7/0.16±0.008mm)*1C +BRAID(16*4/0.12±0.008mm)]TINNED COPPER INSULATION:PE OD= 1.52±0.07mm ;COLOR:TRANSPARENT JACKET:HALF MATTE PVC LOW TOXIC;OD=Ø2.54±0.10mm COLOR:UL813 BLACK.
 - MARKING:RG-174/U COAXIAL CABLE RoHS
 - 2.CONNECTOR:SMA Male RA GOLD-PLATING
 - 3.OPEN/SHORT MISS WIRE TEST 100%
 - 4.CONDUCTOR RESISTANCE ≅150Ω/km
 - 5.INSULATION RESISTANCE ≅2MΩ DC300V 0.01Sec
- ALL MATERIALS SHALL ACCORD WITH RoHS STANDARD.

SECTION A-A

LENGTH & P/N Table

LENGTH	CUSTOMER P/N
6 INCH(152±15mm)	CO-174RASMAX2-000.6
1FT(305±20mm)	CO-174RASMAX2-001
1.25FT(381±20mm)	CO-174RASMAX2-001.25
1.5FT(457±20mm)	CO-174RASMAX2-001.5
2.5FT(762±30mm)	CO-174RASMAX2-002.5
3FT(914±30mm)	CO-174RASMAX2-003
5FT(1524±30mm)	CO-174RASMAX2-005

PIN OUT:

CENTER	CENTER
SHELL	SHELL



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:				Amphenol Cables on Demand			
DECIMALS		ANGLES		20 VALLEY ST. ENDCOTT, NY 13760			
.X	±.X	±X°		DATE			
.XX	±.XX			DRAWN L.F	16/Sept./10		
.XXX	±.XXX			CHECKED BA	16/Sept./10		
THIRD ANGLE PROJECTION				RESP ENG	RG174/U SMA RA Male / SMA RA Male		
				MFG ENG			
					SIZE A	DWG. NO. CO-174RASMAX2-XXX	REV. A2

NOTES: UNLESS OTHERWISE SPECIFIED

4

3

2

1

SCALE

SHEET

OF