

Technical data sheet

PUR feedback cables · C-track compatible · shielded

LÜTZE SUPERFLEX® PLUS (C) PUR FEEDBACK

Feedback cables for Bosch-Rexroth and other systems

For highest requirements in drive technology



halogen free
flame retardant



LÜTZE SUPERFLEX®
connected



Low Capacitance



Identification

Type	SU+ (C) PUR FB (2x0,5+4x2x0,25) 300V
Part No.	111780
INK Description*	INK-0448*

Product version

Datasheet version	00
-------------------	----

Use/Application/Properties

Application	<ul style="list-style-type: none">Incremental encoder cable, termination cable for tacho sensor, brake sensor, speed sensorThrough full PUR jacket and TPE conductor insulation optimally suited for c-tracks, extremely harsh operating conditions and aggressive coolants and lubricantsEspecially for industrial environments in mechanical and system engineering
Properties	<ul style="list-style-type: none">High protection against electromagnetic interferences (EMI)Braided shield optimised for continuous flexing useVery good alternating bending strengthLow adhesion, abrasion-resistant, nick-resistant, tear-resistantHydrolysis-resistant, microbe-resistant, and rot-resistantWeathering, ozone and UV resistant (normal lighting conditions)Industrial and salt water resistantExcellent coolant and lubricant resistanceLargely resistant to oils, greases, alcohol-free benzines and keroseneSilicone free

Construction

Description	SUPERFLEX® PLUS (C) PUR FEEDBACK
Number of conductors/cross-section	(2x0.5+4x2x0.25)
Number of conductors	10
Cross-section, metric	0.5 mm ²

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0
www.lutze.com • sales.gb@lutze.co.uk

Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt
Tel. +49 (0)7151 6053-0
www.luetze.de • info@luetze.de

31.03.2025 • Subject to technical modification

Part No. [111780](#) • Datasheet version: 00

page 1 of 4

Technical data sheet

PUR feedback cables · C-track compatible · shielded

Jacket material	PUR
Jacket color	orange similar to RAL 2003
Outer Ø	8.5 mm
Outer Ø	0.335 inch
Surface	adhesion-free
Weight	10 kg/100 m
Weight	67 Lbs/Mft
Cu-Index	5.9 kg/100 m
Cu-Index	40 Lbs/Mft

Construction Element 1

Element construction	2x0.5
Conductor	CU-wire bare
Conductor category	IEC 60228, Class 6 Superfinely stranded DIN VDE 0295 Class 6
Conductor marking	According to system manufacturer
Conductor insulation	Special TPE
Stranding	Conductors twisted without mechanical stress Layer pitch optimised

Construction Element 2

Element construction	4x2x0.25
Conductor	CU-wire bare
Conductor category	IEC 60228, Class 6 Superfinely stranded DIN VDE 0295 Class 6
Conductor marking	According to system manufacturer
Conductor insulation	Special TPE
Stranding	Conductors stranded in pairs Layer pitch optimised Conductors twisted without mechanical stress

Overall construction

Overall stranding	Layered construction around core Elements stranded together Layer pitch optimised Conductors twisted without mechanical stress
Overall wrapping	Non-woven material
Overall shield	Braid shield Tinned copper wires Optical cover approx. 85 %

Technical data sheet

PUR feedback cables · C-track compatible · shielded

Jacket characteristics	Flame-retardant
	Oil resistant
	Grease-resistant
	Petrol-resistant (alcohol-free)
	Kerosene-resistant
	Silicone free
	Halogen free

Technical data

Rated voltage	300 V
Test voltage type	AC 2000 V
Temperature range moving	-25 °C ... +80 °C
Temperature range fixed	-40 °C ... +80 °C
Minimum bending radius moving	7.5×D
Minimum bending radius fixed	5×D
Bending cycles	≥10 Mio
Speed	≤5 m/s
Acceleration	≤50 m/s ²
Torsion	± 30°/m

Technical Data Element 1

Element construction	2×0.5
Insulation resistance at 20 °C	≥200 MΩ×km
Operating capacitance wire-wire	approx.57 pF/m
Operating capacitance wire-shield	approx.103 pF/m

Technical Data Element 2

Element construction	4×2×0.25
Insulation resistance at 20 °C	≥200 MΩ×km
Operating capacitance wire-wire	approx.57 pF/m
Operating capacitance wire-shield	approx.103 pF/m

Certifications/Standards

Certifications	cURus
UL style	AWM 20233
Conformity	CE RoHS REACH TSCA
Burning behavior according to	IEC 60332-1 DIN EN 60332-1-2 VDE 0482 322-1-2 UL 1581 part 1080 VW-1 UL FT1
Halogen free according to	DIN EN 60754-1 IEC 60754-1

Technical data sheet

PUR feedback cables · C-track compatible · shielded

General

Note

CE These products are in conformity with the EU Low Voltage Directive 2014/35/EU