

High-Density Fiber Adapter Panel (MMF/SMF), 6 SC Duplex Connectors, Black

MODEL NUMBER: **N492-06D-SC**



Toolless pass-through fiber panel snaps easily into Tripp Lite wall-mount fiber enclosures to complete singlemode or multimode fiber connections.

Description

The N492-06D-SC High-Density Fiber Adapter Panel (MMF/SMF) is designed specifically for use with N492-WM2-BK or N492-WM4-BK Wall-Mount Fiber Enclosures. The pass-through panel features six SC duplex connectors that work with both multimode and singlemode applications. It's easy to install—just snap the panel into the enclosure with no tools required. It's made from heavy-duty 1.2 mm cold-rolled steel that will last a lifetime. Dust caps are included to protect unused connectors from debris or damage.

Features

High-Density Fiber Adapter Panel for Pass-Through Applications

- Recommended for multimode or singlemode fiber connections
- Simple snap-in installation with no tools required
- 6 SC duplex connectors
- Heavy-duty 1.2 mm cold-rolled steel construction
- Dust caps protect unused connectors from debris and damage
- Compatible with N492-WM2-BK or N492-WM4-BK Wall-Mount Fiber Enclosures

Specifications

OVERVIEW	
UPC Code	037332202956
Product Type	Adapter
Technology	Multimode; Singlemode
CONNECTIONS	
Number of Ports	6

Highlights

- Simple installation with no tools required
- Made from heavy-duty 1.2 mm cold-rolled steel
- Includes dust caps to protect unused connectors
- Works with multimode and singlemode fiber
- Features 6 SC duplex connectors

System Requirements

- N492-WM2-BK or N492-WM4-BK wall-mount fiber enclosure

Package Includes

- N492-06D-SC High-Density Fiber Adapter Panel (MMF/SMF)
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	SC DUPLEX (FEMALE)
Side B - Connector 1	SC DUPLEX (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	1.40 x 5.50 x 2.10
Shipping Dimensions (hwd / cm)	3.56 x 13.97 x 5.33
Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
ENVIRONMENTAL	
Operating Temperature Range	-40° to 140°F (-40° to 60°C)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.