

Wall-Mount Fiber Optic Distribution Enclosure, 4-Panel Capacity

MODEL NUMBER: **N492-WM4-BK**



Convenient, secure and fully sealed wall-mount fiber optic enclosure for managing and protecting your fiber terminations. Compatible with Tripp Lite high-density fiber adapter panels.

Description

The N492-WM4-BK Wall-Mount Fiber Optic Distribution Enclosure manages and protects your fiber terminations where space is at a premium. It locks using the included key to keep your connections safe from tampering. The doors open wide to reveal plenty of room for splicing and patching your fiber cabling. It supports up to four fiber adapter panels, such as high-density LC (N492-08D-LC), SC (N492-06D-SC) and ST (N492-08S-ST) panels. Cable manager rings, cable ties and a labeling sticker help you keep your cables neatly organized inside the fully sealed enclosure. Made from heavy-duty cold-rolled steel, the N492-WM4-BK mounts on any solid surface.

Features

Fully Sealed Enclosure Manages and Protects Your Fiber Terminations

- Patch and splice cabling in a single enclosure
- Mounts securely on any solid surface
- Locks with included key to protect connections against tampering
- Heavy-duty cold-rolled steel construction
- Cable manager rings, cable ties and label included for organized cable management
- Supports up to 4 fiber adapter panels, including N492-08D-LC, N492-06D-SC and N492-08S-ST

Specifications

OVERVIEW	
UPC Code	037332202925
Technology	Multimode; Singlemode
Country/Region	Global
PHYSICAL	

Highlights

- Mounts securely on any solid surface
- Locks with included key to protect connections against tampering
- Made from heavy-duty cold-rolled steel
- Includes rings, ties and label for organized cable management
- Supports up to 4 fiber adapter panels

Package Includes

- N492-WM4-BK Wall-Mount Fiber Optic Distribution Enclosure, 4-Panel Capacity
- (4) Cable manager rings
- (5) Cable ties
- Cable lock post
- Label
- (2) Keys
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE
SERIES

Color	Black
Total Number of Ports	0
Shipping Dimensions (hwd / in.)	6.70 x 18.70 x 14.50
Shipping Dimensions (hwd / cm)	17.02 x 47.50 x 36.83
Shipping Weight (lbs.)	12.80
Shipping Weight (kg)	5.81
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	29 x 36.3 x 10.7
Panel Style	Cassette Type
ENVIRONMENTAL	
Operating Temperature	-40 to 140 F (-40 to 60 C)
FEATURES & SPECIFICATIONS	
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.