

Technical data sheet

Cable fittings and accessories

LÜTZE CABLEFIX X

Cable Entry System for cables



Identification

Type	CABLEFIX X 12
Part-No.	606550

Product version

Datasheet version	00
-------------------	----

Use/Application/Properties

Application	• Feed-through system for unassembled cables
Properties	• Simple and quick to install: cables are inserted by pushing the end through the seal from the front. • Bolt-mounted design is compatible with all enclosures. • Provides up to 80 % time savings compared to using individual cable glands. • Protects up to UL Type 4X, 12, 13 and IP 65 • Compact design with improved cable density: up to 50 % space savings compared to individual cable glands • Wide clamping ranges allow for use with cables with various outer diameters • Entry points are sealed by default, eliminating the need for blanking plugs. • Entry points open without any tools when inserting the cable from the front. • Acc. to UL 50E and 508A

Technical data

Dimensions (w × h × d)	148.0 mm × 60.0 mm × 13.5 mm
Number of cables × cable diameter	12 × 5 – 13 mm
Number of cables	12

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2
www.lutze.com • sales.gb@lutze.co.uk

Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt
Tel. +49 (0)7151 6053-0 • Fax +49 (0)7151 6053-277(-288)
www.luetze.de • info@luetze.de

Technical data sheet

Cable fittings and accessories

Temperature range	-40 °C ... +80 °C
Protection class	IP65

Construction

Description	LÜTZE CABLEFIXX 12
Material	PA 6 glass fiber reinforced
Material spacer	Chloroprene rubber
Material membrane	Rubber
Color	black RAL 9005

General

PU (units)	1
------------	---


Certifications/Standards

Certifications	UL Type 4X ($\varnothing$ 5 – 13 mm) UL Type 12/13 ($\varnothing$ 4 – 13 mm) UL CCN NITW2 NITW8
Burning behavior according to	UL 94 HB
Oil resistant according to	UL/NEMA Typ 13

Explanation

C	130 mm
E	5 mm
D	32 mm
Cut-out (B×H)	112 × 36 mm

Dimensions



Drawing