

Technical data sheet

Power supply · LEPOS Low Power, 1-phase, regulated, 100 W

Primary switchmode power supply, Single-phase

Input: wide-range input AC 90–264 V, DC 127–370 V

Output: DC 24 V / 4 A, adjustable



Identification

Type	LEPOS-LP-100-24
Part No.	722709

Product version

Datasheet version	02
-------------------	----

Input

Number of phases	1
Rated voltage U_N	AC 100/240 V
Operation voltage range	AC 90–264 V / DC 127–370 V
Frequency range	47 Hz – 63 Hz
Rated current I_N	1.3 A @ AC 115 V 0.8 A @ AC 230 V
Inrush current	30 A @ AC 115 V / 60 A @ AC 230 V
Internal fuse	T3,15 A / AC 250 V
External protection	Mini-circuit breaker: C 16 A

Output

Output voltage/current	DC 24 V/4 A
Rated voltage U_N	DC 24 V
Rated current I_N	4 A
Max. output current	>5.2 A, >3 s
Power Dissipation	< 1 W in standby mode
Setting range $U_{out\ min.}/U_{out\ max.}$	DC 24–28 V
Accuracy	±2 %

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0
www.lutze.com • sales.gb@lutze.co.uk

Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt
Tel. +49 (0)7151 6053-0
www.luetze.de • info@luetze.de

15.09.2025 • Subject to technical modification

Part No. [722709](#) • Datasheet version: 02

page 1 of 4

Technical data sheet

Power supply · LEPOS Low Power, 1-phase, regulated, 100 W

Load regulation	±1 %
Line regulation	±1 %
Rise time	3000 ms (setUp), 50 ms (switch-on time) @ AC 230 V (at full load) / 3000 ms (setUp), 50 ms (switch-on time) @ AC 115 V (at full load)
Temperature coefficient	±0.03 % / °C
Ripple and noise	≤150 mV pp
Hold up time	50 ms @ AC 230 V 20 ms @ AC 115 V (at full load)
Parallel / redundant mode	Yes/via external decoupling diode e.g. 722999
Efficiency	86 %
Over voltage protection	31.2–36 V, switch-off in case of overvoltage, switch-on again after input voltage reset
Rated over load protection	150 % for 3 s, then shutdown with auto-reset
Short circuit	Hiccup

Status indication

Status indication DC ON LED green DC 22-28 V

Monitoring

DC ON Control (Rdy)	N/O contact
Switching voltage	AC/DC 30 V
Switching current	AC/DC 1 A
Switching capacity	30 VA / 30 W
Isolation voltage	AC 500 V

General

Insulation voltage input / output	AC 3.0 kV _{eff}
Insulation voltage input / ground	AC 2.0 kV _{eff}
Insulation voltage output / ground	AC 500 V / DC 500 V
Insulation resistance at DC 500 V	100 MΩ
Derating	>40 °C: -1.9 W/°C
Cooling	Air convection, 5 mm distance right/left, 40 mm top, 20 mm bottom
Housing material	Plastic
Mounting	DIN rail mountable TS35 (EN 60715)
Max. altitude operation	2000 m
Installation position	Vertical
MTBF	>450,000 h, MIL-HDBK-217 (25 °C)
Degree of protection	IP20
Protection class	II
Weight/unit	0.4 kg
Connection type	Screw terminal 0.20 mm ² – 2.0 mm ² AWG 24 – AWG 14
Dimensions (w × h × d)	55.0 mm × 92.0 mm × 100.0 mm
PU (units)	1

Technical data sheet

Power supply · LEPOS Low Power, 1-phase, regulated, 100 W


General ambient conditions

Operation temperature range	-10 °C ... +60 °C
Storage temperature range	-40 °C ... +85 °C
Over voltage category	II
Degree of pollution	2
Relative air humidity	20 % – 90 %, without condensation

Certifications/Standards

Conformity	CE
Certifications	cULus (E249179)
Standards	EN 55032:2015+A11:2020 EN 55035:2017+A11:2020 EN 62368-1:2014/AC:2015 EN IEC 62368-1:2020+A11:2020 EN IEC 61000-3-2:2019+A1:2021 EN 61000-3-3:2013+A1:2019+A2:2021 UL 508

Dimensions



Use

Application of DC OK active signal


Contact Close	PSU turns on / DC OK.
Contact Open	PSU turns off / DC Fail.
Contact Ratings (max.)	30V/1A resistive load.

Technical data sheet

Power supply · LEPOS Low Power, 1-phase, regulated, 100 W

Derating

Deduction curve and temperature



Characteristic

Minus output and input voltage curve

