

## M12 X-Code Cat6a 10G F/UTP CMR-LP Shielded Ethernet Cable (Right-Angle M/M), IP68, PoE, Blue, 3 m (9.8 ft.), TAA

MODEL NUMBER: NM12-6A3-03M-BL



Connects 10G Ethernet network equipment in industrial and other harsh environments subject to vibration, humidity and extreme temperatures.

### Features

#### Cat6a M12 Cable Recommended for Industrial and Other Harsh Environments

This M12 X-Code cable connects 10 GbE networks in wet/humid environments, places subject to vibration and other areas where protection from harsh elements is essential, such as factories, warehouses, recycling plants, airports, railways and machine shops. The circular M12 connectors with 12-millimeter locking thread are especially designed for washdown and corrosive applications, including agriculture, alternative energy, communications, factory automation, measurement and control, robotics, transportation and food/beverage facilities.

#### IP68 Rating Denotes Resistance to Dust and Water

The IP68 rating means the M12 cable is not only 100% protected against dust, but also able to endure immersion in 1.5 meters of water for up to 60 minutes with no damage or decline in performance.

#### Supports Power over Ethernet to Save You Money and Give You More Installation Choices

Because this Cat6a cable supports high-power 60W PoE, it can supply the power to operate compatible data, voice, security and audio/video PoE devices, such as surveillance cameras, VoIP telephones and access control devices. This saves you the expense and effort of purchasing, connecting and installing individual power supplies for each device, as well as installing separate power and data cables. It also helps you install PoE devices in areas far away from AC outlets, such as poles or ceilings.

#### CMR-LP Certified for Cable Installations with Increased Power Levels

UL's Limited Power (LP) certification indicates the NM12-6A3-03M-BL has been evaluated to handle the marked current under installation scenarios without exceeding the temperature rating of the cable. This CMR-LP-certified cable provides a simple way to prepare installations for increased power levels without having to worry about susceptible issues caused by excessive heat.

#### Right-Angle Plug Makes Connecting in Tight Spaces Easier

One M12 connector is designed at a space-saving right angle, making it easy to install in confined spaces, such as a crowded equipment rack or a network device located flush against a wall. The right-angle construction also relieves strain on the cable and connector and prevents the cable from bending awkwardly.

#### Colored Blue to Avoid Misidentification That Can Cause Costly Downtime

### Highlights

- Designed to withstand vibration, moisture and extreme temperatures in harsh environments
- IP68-rated to resist dust and endure immersion in 1.5 m of water up to 60 min.
- Supports 60W PoE to save you expense and effort of powering PoE devices individually
- UL CMR-LP certified to meet high-temperature safety standards in PoE applications
- Right-angle M12 end relieves cable strain and allows easy connection in tight spaces

### Package Includes

NM12-6A3-03M-BL M12 X-Code Cat6a 10G Ethernet Cable, M/M, Blue, 3 m (9.8 ft.)



Powering Business Worldwide

TRIPP LITE  
SERIES

This Cat6a F/UTP copper cable features a blue PVC jacket that allows easy, fast identification in field devices, controllers and switches and helps prevent the cable from becoming inadvertently disconnected.

## Specifications

| OVERVIEW                    |                                       |
|-----------------------------|---------------------------------------|
| UPC Code                    | 037332265586                          |
| Technology                  | Cat6a                                 |
| CONNECTIONS                 |                                       |
| PoE Capability              | 60W (802.3bt)                         |
| Side A - Connector 1        | M12 X CODE (MALE)                     |
| Side B - Connector 1        | M12 X CODE (MALE)                     |
| Crossover Wiring            | No                                    |
| Contact Plating             | Gold                                  |
| PoE Type                    | Type 3 PoE++/UPoE (60W, IEEE 802.3bt) |
| Connector Type              | Snagless                              |
| Wiring Configuration        | EIA/TIA 568B                          |
| Angled Connector            | No                                    |
| PHYSICAL                    |                                       |
| Cable Jacket Color          | Blue                                  |
| Cable Jacket Material       | PVC                                   |
| Cable Jacket Rating         | CMR-LP                                |
| Cable Shielding             | F/UTP                                 |
| Cable Outer Diameter (OD)   | 7.3 mm                                |
| Number of Conductors        | 4 Pair                                |
| Conductor Material          | Solid Copper                          |
| Conductor Gauge             | 23 AWG                                |
| Wire Gauge (AWG)            | 23                                    |
| Cable Length (ft.)          | 9.8                                   |
| Cable Length (m)            | 2.99                                  |
| ENVIRONMENTAL               |                                       |
| Operating Temperature Range | 14° to 140°F (-10° to 60°C)           |
| Storage Temperature Range   | -4° to 158°F (-20° to 70°C)           |
| Operating Humidity Range    | 0% to 90% RH, Non-Condensing          |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                       |                                                                                |
|---------------------------------------|--------------------------------------------------------------------------------|
| Storage Humidity Range                | 0% to 90% RH, Non-Condensing                                                   |
| Power Provided to Connected Device(s) | 51W (60W @ SOURCE, 51W @ DEVICE)                                               |
| <b>COMMUNICATIONS</b>                 |                                                                                |
| Bandwidth per TIA Standard            | 500 MHz                                                                        |
| Maximum Bandwidth as Tested           | 600 MHz                                                                        |
| Network Compatibility                 | 10 Gbps                                                                        |
| IEEE Standards Supported              | 802.3bt                                                                        |
| <b>FEATURES &amp; SPECIFICATIONS</b>  |                                                                                |
| Antibacterial                         | No                                                                             |
| IP68 Rated                            | Yes                                                                            |
| Snagless Connector                    | Yes                                                                            |
| Angled Plug                           | Yes                                                                            |
| <b>STANDARDS &amp; COMPLIANCE</b>     |                                                                                |
| Protection Rating                     | IP68                                                                           |
| Product Certifications                | UL Listed; cUL Listed                                                          |
| Product Compliance                    | CE (Europe); RoHS; IEEE 802.3bt PoE++; REACH; UKCA; Trade Agreements Act (TAA) |
| <b>WARRANTY &amp; SUPPORT</b>         |                                                                                |
| Product Warranty Period (Worldwide)   | Lifetime limited warranty                                                      |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.