

IEC 309 to C19, Heavy-Duty Extension Cord - 16A, 250V, 16 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: **P070-010**



IEC 309 (2P+G) to C19 extension cord connects a high-output device with a C20 power inlet to an IEC 309 connector on a PDU.

Features

Heavy-Duty Extension Cable for Network Devices That Require a Heavy-Gauge Connection This heavy-duty extension cord features 16 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This cord can be used to connect a server, router, network switch or blade server enclosure to a PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The 10-ft. (3.05 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Highlights

- Recommended for powering servers, routers and other high-output network devices
- 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
- Heavy-duty extension cord replaces or upgrades standard manufacturer power cord
- 16 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect high-output devices like servers and routers to a PDU up to 10-ft. (3.05 m) away in your data center
- Extend an existing power connection up to 10-ft. (3.05 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P070-010 IEC 309 to C19, Heavy-Duty Extension Cord, 10-ft. (3.05 m), Black

Specifications

| OVERVIEW | |
|-----------------------------|--|
| UPC Code | 037332160706 |
| Device Compatibility | Server; Router; Network Switch; PDU; UPS |
| Country/Region | North America |
| INPUT | |
| Maximum Input Amps | 16 |
| Voltage Compatibility (VAC) | 250 |
| CONNECTIONS | |
| Side A - Connector 1 | IEC-320-C19 |
| Side B - Connector 1 | IEC-309 16A 2P+E |



Powering Business Worldwide

TRIPP LITE
SERIES

| PHYSICAL | |
|------------------------------------|--------------------------------|
| Plug Color | Blue; White |
| Cable Jacket Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Power Cord Jacket Type | SJT |
| Cable Outer Diameter (OD) | 8.4mm |
| Number of Conductors | 3 |
| Wire Gauge (AWG) | 16 |
| Wire Gauge (OD - mm ²) | 1.29 |
| Cable Length (ft.) | 10 |
| Cable Length (m) | 3.05 |
| Shipping Dimensions (hwd / in.) | 12.80 x 8.90 x 0.50 |
| Shipping Dimensions (hwd / cm) | 32.51 x 22.61 x 1.27 |
| Shipping Weight (lbs.) | 1.20 |
| Shipping Weight (kg) | 0.54 |
| Unit Dimensions (hwd / in.) | 12.800 x 8.900 x 0.500 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 14° to 140°F (-10° to 60°C) |
| Storage Temperature Range | 14° to 140°F (-10° to 60°C) |
| Operating Humidity Range | 35% to 85% RH, Non-Condensing |
| Storage Humidity Range | 35% to 85% RH, Non-Condensing |
| FEATURES & SPECIFICATIONS | |
| Antibacterial | No |
| Angled Plug | No |
| High Voltage | Yes |
| Locking Plug | No |
| Coiled Power Cord | No |
| STANDARDS & COMPLIANCE | |
| Product Certifications | cUL Listed; UL Listed |
| Product Compliance | CE (Europe); REACH; RoHS; UKCA |
| WARRANTY & SUPPORT | |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|-------------------------------------|---------------------------|
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
|-------------------------------------|---------------------------|

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.