

## Technical data sheet

Interface Technology · LCIS analogue/analogue converter

---

**Input: 0–10 V**

**Output: 4–20 mA**

**Insulation: 2.5 kV, 3-way isolation**



---

### Identification

|          |                             |
|----------|-----------------------------|
| Type     | LCIS-WAA-0532-62-S          |
| Part No. | <a href="#">750532.0000</a> |

---

### Product version

|                   |     |
|-------------------|-----|
| Hardware revision | 1.0 |
| Software version  | 1.1 |
| Datasheet version | 03  |

---

### Input

|                        |                       |
|------------------------|-----------------------|
| Input signal           | 0–10 V                |
| Galvanic isolation I/O | 3-way isolation       |
| Zero /Span             | Production comparison |
| Input resistance       | >330 kΩ               |

---

### Output

|                                 |                                                                                                                 |
|---------------------------------|-----------------------------------------------------------------------------------------------------------------|
| Output signal                   | 4–20 mA                                                                                                         |
| Output current limit            | Min. 3.6 mA or all output ranges 4 – 20 mA<br>Max. 21.6 mA for all output ranges with nominal upper limit 20 mA |
| Max. load impedance at I-output | 500 Ω                                                                                                           |
| Output voltage                  | <16 V                                                                                                           |
| Residual ripple                 | <20 mV <sub>eff</sub>                                                                                           |

---

### Operating data

|          |                   |
|----------|-------------------|
| Accuracy | 0.1 % FSR @ 23 °C |
|----------|-------------------|

---

#### United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park  
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU  
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2  
[www.lutze.com](http://www.lutze.com) • [sales.gb@lutze.co.uk](mailto:sales.gb@lutze.co.uk)

#### Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt  
Tel. +49 (0)7151 6053-0 • Fax +49 (0)7151 6053-277(-288)  
[www.luetze.de](http://www.luetze.de) • [info@luetze.de](mailto:info@luetze.de)

14.03.2024 • Subject to technical modification

Part No. [750532.0000](#) • Datasheet version: 03

page 1 of 4



SYSTEMATIC TECHNOLOGY

## Technical data sheet

### Interface Technology · LCIS analogue/analogue converter

---

|                             |                  |
|-----------------------------|------------------|
| Linearity error             | 0.05 % FSR       |
| Rise time (10-90%)          | 6 ms             |
| Build-up time (Accuracy 1%) | 17 ms            |
| Temperature coefficient     | <150 ppm / K FSR |
| Critical frequency          | 30 Hz @ 3 dB     |

---

#### General

---

|                                   |                                                                                                                                                                                        |
|-----------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Rated voltage $U_N$               | AC/DC 24 V                                                                                                                                                                             |
| Current Consumption               | 22 mA                                                                                                                                                                                  |
| Status indication                 | LED green                                                                                                                                                                              |
| Input/output protection           | Overvoltage, short circuit-proof output                                                                                                                                                |
| Insulation voltage input / output | 2.5 kV <sub>eff</sub>                                                                                                                                                                  |
| Housing material                  | PA 6.6 (UL 94 V-0, NFF I2, F2)                                                                                                                                                         |
| Color of the housing              | RAL 7012<br>Basalt grey                                                                                                                                                                |
| Mounting                          | DIN rail mountable TS35<br>(EN 60715)                                                                                                                                                  |
| Degree of protection              | IP20                                                                                                                                                                                   |
| Installation position             | Any                                                                                                                                                                                    |
| Connection type                   | Screwed terminal<br>Single wire<br>0.25 mm <sup>2</sup> – 2.5 mm <sup>2</sup> / AWG 24–14<br>Fine stranded wire with ferrule<br>0.25 mm <sup>2</sup> – 1.5 mm <sup>2</sup> / AWG 24–16 |
| Strip length                      | 6 mm                                                                                                                                                                                   |
| Dimensions (w × h × d)            | 6.2 mm × 93.0 mm × 73.0 mm                                                                                                                                                             |
| Weight/unit                       | 0.029 kg                                                                                                                                                                               |
| PU (units)                        | 1                                                                                                                                                                                      |

---

#### General ambient conditions

---

|                             |                              |
|-----------------------------|------------------------------|
| Operation temperature range | -25 °C ... +60 °C            |
| Storage temperature range   | -40 °C ... +80 °C            |
| Relative air humidity       | 20 – 90 % RH, not condensing |
| Vibration resistance        | 0.7 g acc. to EN 60068-2-6   |

---

#### Failure Rate Prediction (MTBF)

---

|                        |                                                                                                                                                                                            |
|------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Standards              | Electronic components – Reliability – Reference conditions for failure rates and stress models for conversion: EN/IEC 61709<br>Failure Rates of Components – Expected values: SN 29500     |
| Failure rate at +45 °C | 504 fit                                                                                                                                                                                    |
| Failure rate at +45 °C | 1983891 h<br>1 fit equals one failure per 10 <sup>9</sup> component hours<br>The indicated temperature is the mean component ambient temperature.                                          |
| Comments               | The results are valid under following conditions:<br>Automotive environment or industrial areas without extreme dust levels and harmful substances<br>Continuous operation 8760 h per year |


## Technical data sheet

### Interface Technology · LCIS analogue/analogue converter


#### Certifications/Standards

|                |                                                                                     |
|----------------|-------------------------------------------------------------------------------------|
| Conformity     | CE<br>UKCA                                                                          |
| Certifications | cULus (E135145)<br>DNV (TAA000024Y)                                                 |
| Standards      | EN 60947-1<br>EN 60947-5-1<br>EN 61000-6-2<br>EN 61000-6-4<br>UL 508<br>DNV-CG-0339 |

#### Dimensions



#### PIN assignment



## Technical data sheet

### Interface Technology · LCIS analogue/analogue converter

---

#### Use

