


1.92kW Single-Phase Local Metered PDU with ISOBAR Surge Protection, 120V, 3840 Joules, 28 NEMA 5-15/20R Outlets, L5-20P Input, 15 ft. Cord, 0U Vertical, TAA

MODEL NUMBER: PDUMV20-ISO



Delivers 120V single-phase AC power to multiple loads while also protecting connected equipment from dangerous surges and spikes.

Features

Single-Phase 120V PDU Distributes and Monitors Network-Grade Power to Multiple Loads

This local metered rack PDU (rPDU) is an ideal unit for telecom, security, audio/video and a wide variety of general portable and stationary rack-mount applications. Recommended for network-grade IT environments, the PDUMV20-ISO provides real-time monitoring of load levels via its built-in digital current metering. A 15-foot (4.6-meter) cord with L5-20P input plug (5-20P adapter included) connects to your facility's AC power source, generator or protected UPS system to distribute power to connected loads.

Digital Load Meter Helps Prevent Potentially Expensive Overloads

The PDUMV20-ISO features 28 NEMA 5-15/20R outlets for delivering power to equipment. A digital ammeter reports the total input current in real time. Monitoring amperage helps ensure load levels remain well below maximum capacity with no danger of overload that could lead to costly downtime or damaged equipment. Maintaining proper load levels can keep your TCO (total cost of ownership) low.

3840 Joules per Load Bank Fight Back Against Unexpected Power Surges

Protecting your valuable electronics is ISOBAR® network-grade AC surge and noise suppression. A 3840-joule surge protection rating defends your sensitive electronic components against even the strongest power surges, spikes and line noise. The PDUMV20-ISO covers full normal (H-N) and common (N-G/H-G) protection modes. A green LED confirms your connected equipment is protected.

Up-to-Date Safety Features Protect Your Vital Equipment

All outlets are protected by a resettable 20A circuit breaker that shuts down the PDU in the event of a power load to safeguard connected equipment. A transparent cover protects the lighted on/off switch to help prevent an accidental shutdown that could lead to costly downtime.

Versatile Installation Options Give You Plenty of Choices

The 0U PDU mounts vertically using the included hardware. Vertical 0U mounting reduces cable clutter and permits efficient airflow through the rack. You can also install the long-lasting all-metal housing on a wall, raceway or a similar flat surface.

Highlights

- Local metered PDU ideal for telecom, security, A/V and other small network applications
- Digital ammeter for on-site load monitoring helps prevent power overloads
- 3840 joules protect your valuable electronics against dangerous surges and spikes
- 28 NEMA 5-15/20R outlets distribute AC power to connected equipment
- Flexible installation options include 0U rack, under counter and on wall

Package Includes

- PDUMV20-ISO 1.92kW 120V Single-Phase Local Metered PDU
- L5-20P to 5-20P plug adapter
- Mounting hardware
- Owner's manual

Specifications

| OVERVIEW | |
|-------------------------------------|---|
| UPC Code | 037332255884 |
| PDU Type | Local Metered |
| INPUT | |
| Input Phase | Single-Phase |
| PDU Input Voltage | 120V |
| Recommended Electrical Service | Single-phase 20A 120V service |
| Maximum Input Amps | 16 |
| Maximum Input Amps Details | Agency de-rated to 16A continuous |
| PDU Plug Type | NEMA 5-20P; NEMA L5-20P |
| Input Cord Length (ft.) | 15 |
| Input Cord Length (m) | 4.57 |
| OUTPUT | |
| Output Capacity (kW) | 1.92 |
| Output Capacity Details | 1.92kW (120V) / 16A total capacity; 16A max per outlet |
| Frequency Compatibility | 50 / 60 Hz |
| Output Receptacles | (28) 5-15/20R |
| Output Nominal Voltage | 120V |
| Overload Protection | 20A circuit breaker |
| USER INTERFACE, ALERTS & CONTROLS | |
| Front Panel LCD Display | Digital meter reports PDU output current in amps |
| Switches | Lighted on/off switch with integrated transparent safety cover |
| LED Indicators | 3 diagnostic LEDs continuously report status for LINE OK (green), suppressor or wiring FAULT (red) and PROTECTION PRESENT (green) |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 3840 |
| AC Suppression Response Time | NM = 0 ns. CM = <1 ns |
| Protection Modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| Clamping Voltage (RMS) | 140 |
| AC Suppression Surge Current Rating | 60,000 amps |
| EMI / RFI Filtering | 40-80 dB |
| Immunity | Conforms to IEEE 587 / ANSI C62.41 |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|-------------------------------------|--|
| Automatic Shut-Off | No |
| PHYSICAL | |
| Material of Construction | Aluminum |
| Rack Height | 0U |
| Form Factors Supported | Vertical |
| PDU Form Factor | Vertical (0U) |
| Receptacle Color | Black |
| Shipping Dimensions (hwd / in.) | 2.56 x 4.72 x 63.98 |
| Shipping Weight (kg) | 4.10 |
| Unit Dimensions (hwd / in.) | 60.430 x 1.500 x 3.140 |
| Unit Dimensions (hwd / cm) | 153.59 x 3.81 x 4.17 |
| Unit Weight (lbs.) | 5.39 |
| Unit Weight (kg) | 2.44 |
| Mounting Details | Mounting Buttons |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32° to 104°F (0° to 40°C) |
| Storage Temperature Range | -22° to 122°F (-30° to 50°C) |
| Relative Humidity | 5-95% non-condensing |
| Operating Elevation | 0-6562 ft. (0-2000 m) |
| STANDARDS & COMPLIANCE | |
| Product Certifications | CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 62368-1 (Canada); NOM (Mexico); RETIE (Colombia); UL 1363; UL 1449; UL 62368-1 |
| Product Compliance | RoHS; Trade Agreements Act (TAA) |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 2-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.