

## Technical data sheet

### Flexible Electronic Cable PLTC PVC · Unshielded

#### LUTZE ELECTRONIC PLTC PVC For Stationary Applications



#### Identification

Type LiYY PLTC PVC 8×AWG16  
Part No. [A3031608](#)

#### Product version

Datasheet version 00

#### Use/Application/Properties

- |             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
|-------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Application | <ul style="list-style-type: none"><li>• Multi-conductor industrial grade PLTC electronic cable</li><li>• Machine tools, machine and plant construction, HVAC technology, refrigeration as well as many other areas of use.</li><li>• Compliant with NFPA 79 requirements</li><li>• PLTC for installation in cable trays</li></ul>                                                                                                                                                                                           |
| Properties  | <ul style="list-style-type: none"><li>• Flexible for easy installation</li><li>• Easy strip design</li><li>• Color coded conductors</li><li>• Specially formulated jacket for oil resistance</li><li>• Ecolab certified resistance to common cleaning agents and chemicals used in food and beverage washdown procedures</li><li>• Premium durability</li><li>• Extended temperature range</li><li>• Sunlight resistant</li><li>• Gas/vapor-tight sheath per UL 1277 and 13</li><li>• Talc free and silicone free</li></ul> |

#### Construction

|                                    |                     |
|------------------------------------|---------------------|
| Description                        | ELECTRONIC PLTC PVC |
| Number of conductors/cross-section | 8×AWG16             |
| Number of conductors               | 8                   |
| Cross-section, metric              | 1.5 mm <sup>2</sup> |
| Cross-section AWG                  | AWG 16              |
| Jacket material                    | PVC                 |

#### United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park  
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU  
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2  
[www.lutze.com](http://www.lutze.com) • [sales.gb@lutze.co.uk](mailto:sales.gb@lutze.co.uk)

#### Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt  
Tel. +49 (0)7151 6053-0 • Fax +49 (0)7151 6053-277(-288)  
[www.luetze.de](http://www.luetze.de) • [info@luetze.de](mailto:info@luetze.de)

## Technical data sheet

### Flexible Electronic Cable PLTC PVC · Unshielded

|              |                          |
|--------------|--------------------------|
| Jacket color | grey similar to RAL 7001 |
| Outer Ø      | 10.3 mm                  |
| Outer Ø      | 0.407 inch               |
| Weight       | 119 Lbs/Mft              |
| Cu-Index     | 65 Lbs/Mft               |

#### Construction Element 1

|                        |                                                              |
|------------------------|--------------------------------------------------------------|
| Element construction   | AWG16/8C                                                     |
| Conductor construction | AWG 16 (26/30)                                               |
| Conductor              | AWG conductor<br>CU-wire tin-plated                          |
| Conductor category     | fine wire                                                    |
| Conductor marking      | black · red · white · green · orange · blue · brown · yellow |
| Conductor insulation   | SR-PVC                                                       |

#### Overall construction

|                        |                                                   |
|------------------------|---------------------------------------------------|
| Jacket characteristics | Flame-retardant<br>Oil resistant<br>Silicone-free |
|------------------------|---------------------------------------------------|

#### Technical data

|                              |                    |
|------------------------------|--------------------|
| Rated voltage UL             | 300 V              |
| Temperature range fixed      | -40 °C ... +105 °C |
| Minimum bending radius fixed | 4×D                |

#### Technical Data Element 1

|                      |          |
|----------------------|----------|
| Element construction | AWG16/8C |
|----------------------|----------|

#### Certifications/Standards

|                               |                                                                                                                                                                          |
|-------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Certifications                | PLTC<br>UL Type CM<br>AWM I/II A/B FT1<br>Meets NEC 392,800<br>NEC 725<br>Class I and II, Div. 2 and Class I<br>Zone 2 per NEC 501, 502, 505<br>(PLTC use only)<br>UL 13 |
| UL style                      | AWM 2464                                                                                                                                                                 |
| Conformity                    | CE<br>RoHS<br>REACH<br>TSCA                                                                                                                                              |
| Burning behavior according to | UL VW-1<br>UL FT4                                                                                                                                                        |
| Oil resistant according to    | Oil Res II                                                                                                                                                               |

## Technical data sheet

### Flexible Electronic Cable PLTC PVC · Unshielded

---

#### General

---

Note

CE These products are in conformity with the EU Low Voltage Directive 2014/35/EU