

## Important Note

UL1363a, Paragraph 14.1(d) states, "The SPRPT shall be permanently attached to the medical equipment by a means such that it is only removable with the use of a tool." To achieve compliance, one must use the PSCLAMP.

# Safe-IT UL 1363A Medical-Grade Power Strip for Patient-Care Vicinity, 4 Hospital-Grade Outlets, 15 ft. Right-Angle Cord

MODEL NUMBER: PS-415-HG-OEMRA



Delivers power to devices attached to IV poles, crash carts and mobile workstations in operating rooms and other patient care vicinities.

## Features

**4-Outlet Medical-Grade Power Strip with Long 15 ft. Cord Approved for Patient Care Vicinities** PS-415-HG-OEMRA supplies power to movable plug-connected components mounted to IV poles, mobile carts, crash carts and mobile medical workstations inside and outside patient care vicinities when properly mounted. This includes operating rooms, therapy rooms, imaging environments and administrative areas. Compliant with UL 1363A specifications, this 120V power strip features four NEMA 5-15R-HG hospital-grade outlets.

**Exclusive Antimicrobial Protection Fights Healthcare-Acquired Infections (HAIs)** The power strip is protected by a patented antimicrobial powder coating with EPA-registered and FDA-compliant silver ionic technology. The antimicrobial surface protection is 99.9 percent effective in inhibiting the growth of bacteria and reducing the risk of HAIs in hospitals and other medical environments. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

**Premium Safety Features Help Ensure Proper Power Connections** With no central power switch, this power strip presents no danger of accidental shutoff and cutting off power to essential devices. Two resettable 15-amp circuit breakers will shut down all AC input if the power strip determines the connected equipment load is drawing too much power. Four locking plastic safety covers are included to block access to unused outlets.

**Ready for Installation in Demanding Medical Environments** The power strip with 15-foot (4.6-meter) cord also includes a space-saving right-angle NEMA 5-15P-HG plug that helps you connect to a wall outlet located behind furniture that is placed flush against the wall. Built-in mounting flanges and integrated keyhole slots let you install the durable all-metal housing on any mobile cart or IV pole for distributing power to movable rack-, table- and pedestal-mounted equipment.

## Highlights

- UL 1363A power strip for use inside and outside patient care vicinities
- Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew
- Right-angle 5-15P-HG plug permits connection in confined or hard-to-reach spaces
- 15 ft. (4.6 m) power cord allows flexibility in placing power strip in relationship to AC outlet
- Complies with NFPA 99
- Switchless design helps prevent accidental shutdown of essential equipment

## Applications

- Supply safe medical-grade power to lab, imaging and other electric components mounted to an IV pole or crash cart in a patient care area

## Package Includes

- PS-415-HG-OEMRA Medical-Grade Power Strip, 4 Outlets, 15-ft. (4.57 m) Cord
- (4) Outlet safety covers
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

## Specifications

| OVERVIEW                           |                                                                     |
|------------------------------------|---------------------------------------------------------------------|
| UPC Code                           | 037332239389                                                        |
| INPUT                              |                                                                     |
| Nominal Input Voltage(s) Supported | 120V AC                                                             |
| Recommended Electrical Service     | 15A 120V                                                            |
| Input Plug Features                | Right-Angle Hospital Grade Plug                                     |
| Input Cord Gauge Type              | 14 gauge; SJT                                                       |
| Voltage Compatibility (VAC)        | 120                                                                 |
| Input Plug Type                    | NEMA 5-15P-HG                                                       |
| Input Cord Length (ft.)            | 15                                                                  |
| Right-Angle Plug                   | Yes                                                                 |
| Input Cord Length (m)              | 4.57                                                                |
| Integrated Cord Clip               | No                                                                  |
| OUTPUT                             |                                                                     |
| Frequency Compatibility            | 50 / 60 Hz                                                          |
| Output (Watts)                     | 1800                                                                |
| Output Receptacles                 | (4) 5-15R-HG                                                        |
| Circuit Breaker (amps)             | 15                                                                  |
| Overload Protection                | 2 x 15amp breakers (1 line, 1 neutral)                              |
| Transformer Accommodation          | (2) Yes                                                             |
| Outlet Orientation                 | Single row of 4                                                     |
| Right-Angle Outlets                | No                                                                  |
| USER INTERFACE, ALERTS & CONTROLS  |                                                                     |
| Switches                           | No power switch                                                     |
| PHYSICAL                           |                                                                     |
| Color                              | White                                                               |
| Material of Construction           | Metal                                                               |
| Power Cord Color                   | White                                                               |
| Form Factors Supported             | IV poles, mobile carts, crash carts and mobile medical workstations |
| Housing Color                      | White                                                               |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                                   |                                                                             |
|---------------------------------------------------|-----------------------------------------------------------------------------|
| Mounting Holes or Slots                           | Yes                                                                         |
| Slot or Hole Mount Measurement (Center to Center) | Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45mm |
| Outlets Measurement (Center to Center)            | Inner outlets = 1.27 in.                                                    |
| Receptacle Color                                  | White                                                                       |
| Shipping Dimensions (hwd / in.)                   | 2.40 x 9.70 x 6.30                                                          |
| Shipping Dimensions (hwd / cm)                    | 6.10 x 24.64 x 16.00                                                        |
| Shipping Weight (lbs.)                            | 2.90                                                                        |
| Shipping Weight (kg)                              | 1.32                                                                        |
| Unit Dimensions (hwd / in.)                       | 1.730 x 2.500 x 8.540                                                       |
| Unit Dimensions (hwd / cm)                        | 21.97 x 6.35 x 3.81                                                         |
| Unit Weight (lbs.)                                | 2.25                                                                        |
| Unit Weight (kg)                                  | 1.02                                                                        |
| Mounting Details                                  | Includes flanges                                                            |
| <b>ENVIRONMENTAL</b>                              |                                                                             |
| Operating Temperature Range                       | 32° to 104°F (0° to 40°C)                                                   |
| Storage Temperature Range                         | 14° to 122°F (-10° to 50°C)                                                 |
| Operating Humidity Range                          | 10% to 90% RH                                                               |
| Storage Humidity Range                            | 5% to 95% RH                                                                |
| <b>FEATURES &amp; SPECIFICATIONS</b>              |                                                                             |
| Rotatable Outlets                                 | No                                                                          |
| Antimicrobial                                     | Yes                                                                         |
| Built-In Circuit Breaker                          | Yes                                                                         |
| Antibacterial                                     | No                                                                          |
| Built-in Cable Management                         | No                                                                          |
| <b>STANDARDS &amp; COMPLIANCE</b>                 |                                                                             |
| Product Certifications                            | UL 1363A                                                                    |
| Product Compliance                                | NFPA 99: 10.2.3.6; RoHS                                                     |
| <b>WARRANTY &amp; SUPPORT</b>                     |                                                                             |
| Product Warranty Period (Worldwide)               | Lifetime limited warranty                                                   |



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.