

Specifications



Photo is representative

Eaton E51KF2A2

Eaton E51 Series Glass Fiberoptic Cable, Sensor distance: Depends on controller used, Right Angle, PVC enclosure, Fiberoptic, Thru-beam

General specifications

PRODUCT NAME	Eaton E51 NEMA limit switch photoelectric sensor fiber optic cable
CATALOG NUMBER	E51KF2A2
UPC	786685012155
PRODUCT LENGTH/DEPTH	2.5 in
PRODUCT HEIGHT	24 in
PRODUCT WIDTH	0.82 in
PRODUCT WEIGHT	0.1209 lb
WARRANTY	3 year
CERTIFICATIONS	UL Listed CSA Certified

Product specifications

ENCLOSURE MATERIAL	PVC
OPERATING MODE	Thru-beam Fiber-optic
SENSOR TYPE	Fiberoptic
OPERATING TEMPERATURE - MAX	221 °F
OPERATING TEMPERATURE - MIN	-40 °F
ENVIRONMENTAL RATING	NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6, NEMA 6P, NEMA 12, NEMA 13, IP67

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - E51KF2A2
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

